AK3AAIG

Request Samples (>)



Check Inventory



3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant** MSL Level = N/A

ESD Sensitive (Pb)



Features

- AEC-Q200 Qualified
- Automotive Grade 1: -40°C to +125°C Available
- TS16949 Production Line Certified, PPAP Available Upon Request
- Exceptionally Low RMS Jitter: 83fs Typ (LVDS @ 156.25MHz)
- Based on 3rd overtone, quartz crystal technology
- Available in industry standard frequencies between 100MHz and 200MHz
- 2.5V, 3.3V, 2.25V to 3.63V Continuous supply voltage options
- LVPECL, LVDS, HCSL differential output logic

Applications

- Optical Transceivers and Modules
- Data Centers, Storage, and Servers
- Networking switches and gateways
- 100G/200G/400G/800G Ethernet
- Fibre Channel/SONET/SDH/PCIe
- Industrial and FPGA applications
- Test & measurement

Key Electrical Specifications

Parameters		Min.	Тур.	Max.	Unit	Notes
Frequency Range		100		200	MHz	
Standard Available Frequencies		100.000, 114.285, 122.880. 125.000, 148.500, 150.000, 155.520, 156.250 & 200.000		MHz	Contact Abracon for availability of frequencies not listed	
Di e di		2.97	3.3	3.63		Option "A"
Supply Voltage (Vdd) [Note 1]		2.375	2.5	2.625	V	Option "B"
		2.375		3.63		Option "D"
	LVPECL		40	60		@ 200MHz; @ Vdd=3.3V
Supply Current (Idd)	LVDS		17	35	mA	@ 200MHz; @ Vdd=3.3V
	HCSL		27	40	1	@ 200MHz; @ Vdd=3.3V
		-20		70		Option "D"
Operating Temperature Range	e	-40		85	°C	Option "F" or "Q"
	operating reinperature range			105	1	Option "X"
		-40		125	1	Option "A"
Storage Temperature		-55		125	°C	
Frequency Tolerance [Note 2]	Frequency Tolerance [Note 2]		< ±5	10	ppm	
Frequency Stability over [Note 3,4]		-15	<±10	15		Option "D" (-20°C to +70°C)
		-20	<±15	20	1	Option "Q" (-40°C to +85°C)
Operating Temperature Range		-25	<±20	25	ppm	Option "F" (-40°C to +85°C)
		-50	< ±45	50	1	Option "X" (-40°C to +105°C)
		-50	< ±45	50	1	Option "A" (-40°C to +125°C)
First Year Aging		-3		3	ppm	At 25°C
All-Inclusive Frequency Accuracy		-40		40		Option "D" (-20°C to +70°C)
		-45		45		Option "Q" (-40°C to +85°C)
(Total Stability) [Notes 5]		-50		50	ppm	Option "F" (-40°C to +85°C)
process]	Inotes of			100	1	Option "X" (-40°C to +105°C)
		-100		100		Option "A" (-40°C to +125°C)



REVISED: 11-28-23

AK3AAIG

Request Samples (>)



Check Inventory



3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant** MSL Level = N/A



Key Electrical Specifications Cont.

Rise (Tr) / Fall (Tf) Time [Notes 6]	LVPECL		0.2	0.4		@ Vdd=3.3V, R_L =50 Ω
	LVDS		0.2	0.4		@ Vdd=3.3V, R_L =100 Ω
			0.2	0.4	ns	@ Vdd=2.5V, R_L =100 Ω
	HCSL		0.5	0.8		@ Vdd=3.3V, R_L =50 Ω to GND
	IICSL		0.5	0.8		@ Vdd=2.5V, R_L =50 Ω to GND
Duty Cycle		45		55	%	
Start-up Time [Note 3]			< 2	5	ms	

Supply voltage (Vdd) = 2.5V and 2.375~3.63V options not available with LVPECL output

Note 2: Frequency Accuracy (Initial Set-Tolerance), at time of shipment (pre-reflow), relative to carrier frequency, @ +25°C

Note 3: Relative to initial measured frequency @ +25°C

Note 4: Option Q only available in select frequencies. Please contact Abracon for availability

Includes post reflow frequency accuracy, temperature stability, load pulling, power supply variation, and 10-year aging Note 5:

Note 6: Measured over 20% to 80% of waveform

Paramete	Min.	Тур.	Max.	Unit	Notes		
	LVPECL	VoH	V _{dd} -1.025	V _{dd} -0.95	V_{dd} -0.88		$R_I = 50\Omega$ to $V_{dd} = 2.0V$
Differential	LVIECE	Vol	V _{dd} -1.81	V_{dd} -1.7	V _{dd} -1.62		RL-3032 to V _{dd} -2.0 V
Output High Voltage (VOH)	LVDS	Voh		1.43	1.60	V	R _L =100Ω between
Output Low Voltage (VOL)	LVDS	Vol	0.90	1.10			both outputs
	HCSL	Voh	0.50	0.74	0.85		R_L =50 Ω to ground
	HCSL	Vol	-0.15	0.00	0.15		on each output
			0.400				LVPECL
Output Voltage Swing (Vopp)	Output Voltage Swing (Vopp)			0.350	0.450	V	LVDS
				0.700	0.850		HCSL
Output Enable & Disable Cont	ro1		0.7*(V _{dd})			V	Output Enable or No Connect
Output Enable & Disable Cont	101				0.3*(V _{dd})		Output Disable (High Impedance)
Output Enable Time	Output Enable Time			< 1	5.0	ms	
Output Disable Time					0.2	μs	
Output Disable Current Consumption					10	μΑ	$OE \le 0.3V$
RMS Phase Jitter (12kHz to 20MHz from Carrier)			Se	ee Table 1 belo	ow		Vdd, output logic type and Carrier frequency dependent



AK3AAIG

Request Samples (>)



Check Inventory



3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant** MSL Level = N/A





Key Electrical Specifications Cont.

Table 1 RMS Phase Jitter 12kHz - 20MHz BW, Vdd=3.3V [Note 7, 8, 9]

RIVIS I hase sitter 12kHz = 20MHz BW, Vuu-3.5V							
Fragueray (MUz)	Output	RMS Jitter					
Frequency (MHz)	Output	Typ. (fs)	Max (fs)				
	LVDS	184	200				
100	LVPECL	166	200				
	HCSL	152	175				
	LVDS	118	150				
125	LVPECL	94	125				
	HCSL	90	115				
	LVDS	83	125				
156.25	LVPECL	64	100				
	HCSL	71	100				
	LVDS	55	100				
200	LVPECL	75	100				
	HCSL	70	100				

Guaranteed by characterization; RMS Phase Jitter specifications are inclusive of any spurs Note 7:

Note 8: Phase jitter measured with Keysight E5052B Signal Source Analyzer

Note 9: Refer to the next section for phase noise test setup and representative phase noise plots

Absolute Maximum Ratings [Note 10]

Parameters	Min.	Тур.	Max.	Unit	Notes
Supply Voltage	Vss-0.5		5	V	
Input Voltage	Vdd-0.5		V _{DD} +0.5	V	
Output Voltage	Vdd-0.5		V _{DD} +0.5	V	
Maximum Junction Operating Temperature			150	°C	
Ambient Operating Temperature Range	-40		125	°C	Automotive
Ambient Operating Temperature Range	-20		70	°C	Extended Commercial
Reflow Temperature			260	°C	See Reflow Profile
ESD Protection	4kV HBM	I, 300V MM,	2kV CDM		

Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability. The data sheet limits are not guaranteed if the device is operated beyond the recommended operating conditions.



AK3AAIG

Request Samples (>)




Check Inventory (>)



3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant** MSL Level = N/A

Options and Part Identification [Note 11]



Part Number Example:

AK3AAIGPAF1-156.2500 AK3AAIGPAF1-156.2500T AK3AAIGPAF1-156.2500T3

Contact Abracon for non-standard part number configurations and/or requests with carrier frequency callouts up to 5 & 6 digit accuracy after the decimal



AK3AAIG

Request Samples (>)



Check Inventory




3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant** MSL Level = N/A





Typical Frequency vs. Temperature Characteristics





AK3AAIG

Request Samples (>)



Check Inventory (>)


ESD Sensitive (Pb)




3.2 x 2.5 x 1.0 mm RoHS/RoHS II Compliant MSL Level = N/A

Differential Output Waveform

LVPECL: Output Wave Form (Duty, Tr, Tf)



LVDS: Output Wave Form (Duty, Tr, Tf, VOH, VOL, VOpp)





AK3AAIG

Request Samples (>)




Check Inventory



3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant** MSL Level = N/A

HCSL: Output Wave Form (Duty, Tr, Tf, VOH, VOL, VOpp)



Duty Cycle =
$$\frac{T_{WH}}{T_{WH} + T_{WL}} \times 100\%$$



AK3AAIG

Request Samples (>)



Check Inventory



3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant**

MSL Level = N/A


ESD Sensitive Pb




Recommended Test Circuit [Note 12]

LVPECL


LVDS





Vdd= 3.3V: R1=R3=127Ω; R2=R4=82.5Ω

HCSL



Note 12: Recommended test circuit images are representative of when the OE Function is located on Pin 1; when the OE Function is located on Pin 2, then Pin 1=No Connect & Pin 2=OE or No Connect.



AK3AAIG

Request Samples (>)



Check Inventory


ESD Sensitive (Pb)




3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant**

MSL Level = N/A

Mechanical Dimensions





BOTTOM VIEW

Recommended Land Pattern 0.035 0.012 0.90 0.30 0.094 2.40

Case 1 Pin #1=Output Enable/Disable Function where OE is Active HIGH			Case 2 Pin #2=Output able/Disable Function tre OE is Active HIGH
Pin	Description	Pin	Description
# 1	Output Enable = Logic High, "1", Vdd	# 1	No Connect
# 1	Output Disable = Logic Low, "0", GND	# 2	Output Enable = Logic High, "1", Vdd
# 2	No Connect	# 2	Output Enable = Logic Low, "0", GND
# 3	GND	# 3	GND
# 4	Output	# 4	Output
# 5	Complementary output	# 5	Complementary output
# 6	Supply Voltage (Vdd)	# 6	Supply Voltage (Vdd)

Dimensions: inches [mm]



REVISED: 11-28-23

AK3AAIG

Request Samples (>)



Check Inventory



3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant**

MSL Level = N/A





Reflow Profile [JEDEC J-STD-020]




Table 1 **SnPb Eutectic Process** Classification Temperatures (Tc) Volume mm³ Package Thickness <350 <u>></u>350 <2.5 mm 235 °C 220 °C ≥2.5 mm 220 °C 220 °C

Pb-Free Process Classification Temperatures (T _c)						
Package Thickness	Volume mm³ <350	Volume mm ³ 350-2000	Volume mm³ >2000			
<1.6 mm	260 °C	260 °C	260 °C			
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C			
>2.5 mm	250 °C	245 °C	245 °C			

REVISED: 11-28-23

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T _{smin})	100°C	150°C
Temperature maximum (T _{smax})	150°C	200°C
Time (T _{smin} to T _{smax}) (t _s)	60 - 120 sec.	60 - 120 sec.
Average ramp-up rate (T _{smax} to T _P)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T _L)	183°C	217°C
Time at liquidous (t _L)	60 - 150 sec.	60 - 150 sec.
Peak package body temperature (T _P)*	see Table 1	see Table 2
Time (t _p)** within 5°C of the specified classification temperature (T _C)	20 sec.	30 sec.
Ramp-down rate (T _p to T _{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

^{*}Tolerance for peak profile temperature (T_P) is defined as a supplier minimum and a user maximum.



^{**}Tolerance for time at peak profile temperature (t_p) is defined as supplier minimum and a user maximum.

AK3AAIG

Request Samples (>)



Check Inventory


ESD Sensitive (Pb)




3.2 x 2.5 x 1.0 mm **RoHS/RoHS II Compliant** MSL Level = N/A

Packaging

Blank = BulkT = Tape & Reel 1,000 units/reel T3= Tape & Reel 3,000 units/reel



FEEDING (PULL) DIRECTION



Dimensions: mm

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



10,90