

## Datasheet

## LoRa 868MHz

Outdoor / Indoor



Stick Antenna

Features:

It's made of fiberglass with high performing LoRa antenna with N-type connector for out / indoor applications, also certified with IP67

Applications:

- CPE Router, Set top boxes & Gateway
- IoT devices
- Sigfox
- LoRa
- LPWAN
- RFID
- Remote Monitoring
- Healthcare



## Electrical Specifications

## Antenna Characteristics


Antenna Type	Radiation Pattern	Polarization	Max. Input Power	Impedance
Stick Antenna	Omni	Linear	200W	50Ω
Frequency (GHz)		863~873		
Return Loss (dB)		< -14		
Peak Gain (dBi)		2.2		
Average Gain (dB)		-0.8		
Efficiency (%)		82		

Mechanical Specifications	
Mechanical	
Dimension (mm)	240.6
Connector Type	N-type (Plug)
Material	Glass fiber
Weight (g)	210.0


Environmental	
Temperature Range (°C)	-40 to 60
IP Rating	IP67
RoHS Compliant	

Mechanical Drawing

Unit : mm




## Charts In Free Space




ST0626-41-302-B

Test setup, measurement performed in 3D anechoic chamber.




Blue background represents frequency response.




## Radiation Pattern - Free Space


### XY - Plane



### YZ - Plane



### XZ - Plane



Revisions				
Rev.	Description	Date	ECN	Approval
A	Initial Release	2023-03-15	ST0626-41-302-B-RA00	ATC

NOTICE - These drawings, specifications, or other data ( 1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.