

# ELEMENT 30/220-240/12 G2

# ELEMENT G2 12V | Constant Voltage - Non dimmable



#### Product family features

- Linear form factor
- Power factor: >0.95 at full load
- Total Harmonic Distortion (THD): < 15%
- Output voltage tolerance: < 3%
- Up to 30,000 h @ T  $_{\rm c}$  max / up to 50,000 h @ T  $_{\rm c}$  -10 °C
- Lifetime: up to 30,000 h (temperature at max. t<sub>c</sub>)

# **Product family benefits**

- High efficiency (up to 91 %)
- Higher quality of light thanks to < 3% output ripple current
- Excellent price/performance ratio
- Class II design for wide application
- 3 years guarantee

## Areas of application

- Decorative lighting in hospitality, restaurants and Shops
- Shelf lighting
- Cove lighting
- Under cabinet lighting


#### Technical data

## **Electrical data**

Nominal input voltage	220240 V
Mains frequency	5060 Hz
Input voltage AC	198264 V
Power factor λ	> 0.95
Efficiency in full-load	86 % 1)
Device power loss	4.9 W <sup>2)</sup>
Inrush current	<13.2 A <sup>3)</sup>
Max. ECG no. on circuit breaker 10 A (B)	29
Max. ECG no. on circuit breaker 10 A (C)	46
Max. ECG no. on circuit breaker 16 A (B)	47
Max. ECG no. on circuit breaker 16 A (C)	73
Max. ECG no. on circuit breaker 25 A (B)	74
Surge capability (L-N)	1 kV
Nominal output voltage	12.5 V
Nominal output power	30 W
Maximum output power	30 W
U-OUT (working voltage)	12.125 V ~ 12.875 V
Surge capability (L/N-Ground)	2 kV

 $<sup>^{1)}</sup>$  at 230 V, 50 Hz

# **Dimensions & weight**



Product weight	100.00 g
Cable cross-section, input side	0.751.5 mm²
Cable cross-section, output side	0.51.5 mm <sup>2</sup>

<sup>&</sup>lt;sup>2)</sup> At Full load, 230 V, 50 Hz

 $<sup>^{3)}</sup>$  Max, th = 200 $\mu$ s

## Product datasheet

Wire preparation length, input side	5.0 mm
Length	145.0 mm
Width	40.0 mm
Height	26.5 mm

#### Colors & materials

Casing material	Plastic
-----------------	---------

## Temperatures & operating conditions

Ambient temperature range	-20+50 °C
Maximum temperature at tc test point	75 °C
Max.housing temperature in case of fault	110 °C
Temperature range at storage	-40+85 °C
Permitted rel. humidity during operation	585 % <sup>1)</sup>

 $<sup>^{1)}</sup>$  Maximum 56 days/year at 85 %

#### Lifespan

ECG lifetime 30000 h 1)	
-------------------------	--

<sup>1)</sup> At maximum T =  $75^{\circ}$ C / 10% failure rate / At maximum T =  $65^{\circ}$ C / 10% failure rate

## **Capabilities**

Dimmable	No
Short-circuit protection	Yes
Intended for no-load operation	No
Suitable for fixtures with prot. class	1/11
Number of channels	1

# Certificates & standards

Approval marks – approval	BIS / CCC / CE / MM / RCM / UKCA
Standards	Acc. to EN 61347-1/Acc. to EN 61347-2-13/Acc. to EN 55015/Acc. to EN 61547/Acc. to EN 60598-1/Acc. to EN 62384/Acc. to CISPR 15/Acc. to EN 61000-3-2/IEC 61000-3-2
Type of protection	IP20

## Logistical data

Commodity code	85044083900

#### **Environmental information**

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACh)

## Product datasheet

Date of Declaration	16-05-2023	
Primary Article Identifier	4062172277846	
Candidate List Substance 1	Lead	
CAS No. of substance 1	7439-92-1	
Safe Use Instruction	The identification of the Candidate List substance is sufficient to allow safe use of the article.	
Declaration No. in SCIP database	e2b90eda-fe30-4c3d-80b6-ea0098b06c18	

#### Download Data

File



User instruction ELEMENT G2

## Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172277846	ELEMENT 30/220-240/12 G2	Shipping carton box 40	421 mm x 315 mm x 96 mm	12.73 dm³	4559.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.