Bleed, Hard Seat & Soft Tip



800/850 SERIES

- Bleed valves provide a convenient means to relieve process pressures trapped between a shut off valve and the instrument
- Uses the same bonnet assemblies of the 100/150 Series mini valves with an integrated single threaded body for insertion in vent port
- Soft tip valves feature a patented Delrin® non-rotating soft tip stem, and a back-up metal-to-metal seal (U.S. Patent 6,820,857)
- 100% helium leak tested to 1 x 10⁻⁴ ml/s for performance and reliability
- Available in Zinc-Nickel plated Steel, electropolished Stainless Steel, and Brass
- FKM o-ring seal and PTFE back-up ring below the stem threads to protect from corrosion and galling; PTFE or Graphite (800 Series only) packing optional
- · All stem threads are rolled for strength and ease of operation
- 0.159" bleed port
- Patented body-to-bonnet, metal-to-metal seal is designed to significantly increase the pressure range of the valve (U.S. Patent 7,758,014)

SPECIFICATIONS				
Materials	Zinc-Nickel plated Steel, electropolished 316 Stainless Steel*, 360 Brass			
Connections	1/4" & 1/2" NPT			
Hard seat pressure ratings**	Brass: 6,000 psi @ 200 °F Steel: 10,000 psi @ 200 °F Stainless Steel: 10,000 psi @ 200 °F			
Soft tip pressure ratings	Brass: 6,000 psi @ 200 °F Steel: 6,000 psi @ 200 °F Stainless Steel: 6,000 psi @ 200 °F			
Bleed port	0.159"			
Stem seal & type	All 316 Stainless Steel stems with FKM o-ring and PTFE back-up ring below the threads, PTFE or Graphite (800 Series only) packing optional			
Options	Panel mountings, o-ring materials, handles, packings, regulating stem and stem tips			
Weight	Approximately 0.4 lb.			

All 316SS products meet the requirements of NACE MR0175/ISO 15156-3.

For NOSHOK Valves with Brass & Steel valve types:



WARNING: This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

For NOSHOK Valves with Stainless Steel valve types:




WARNING: This product can expose you to chemicals including Chromium (VI) and Nickel, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

^{**} If a packing option is chosen, maximum pressure rating is 6,000 psi. Refer to the "Pressure vs. Temperature: Packing Style with Compatible Fluid" chart at the back of this catalog.

SERIES	8	800/850 Series, hard sea	/soft t	p		
CONNECTION SIZES	02	Hard seat 1/4" NPT			52	Delrin® soft tip 1/4" NPT
	04	Hard seat 1/2" NPT			54	Delrin® soft tip 1/2" NPT
VALVE TYPES	MC	Male, Steel	MS	Male, Stainless Steel	MB	Male, Brass

Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.



To meet all of your specific application requirements, the following **additional options** are available for these needle valves. To order all or any of these options, simply add them to the part number as shown in the diagram below.

NOTE 1: The example shown includes ALL possible additional options. Please include ONLY the options required for your application when building your part number. (EXAMPLE: 802-MC-EM1)

NOTE 2: When a packing option is selected, an o-ring option is NOT available.

ORDERING INFORMATION - ADDITIONAL OPTIONS						
PACKINGS [†]	P1	PTFE	P2	Graphite		
STEM TIPS	T1	Non-rotating (316 Stainless)	T4	PEEK***	T7	Ball (ceramic)**
	T2	Delrin® (Acetal)***	T5	Ball (440C Stainless)**	T8	Ball (Monel)**
	T3	PCTFE***	T6	Ball (carbide)**		
O-RINGS*	EM1	EPDM	KZ1	FFKM (Kalrez® 3018 or equivalent)	NB1	NBR
HANDLES	HL2	2-1/2" "T"**	HL4	1-3/8" Phenolic**		
	HL3	1" Round knurled	HL5	1-3/4" Phenolic**		

Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.

Please note that the standard o-ring in all the NOSHOK valves is FKM and the standard handles are 1" round knurled handles (HL3) on Brass, and 1-3/8" mini "T" handles (HL7) on Stainless Steel and Steel.

The handle material will always match the material of the valve, unless otherwise specified. For example, the mini "T" handle (HL7) on the 802-MC will be Steel. When only the standard configuration is needed, no additional designations are necessary. Please consult the factory for special application requests.

EXAMPLE with Ac	Iditional Options	8 02 - MC - P1 - T1 - HL5
Series	800/850 hard seat/soft tip	
Connection size	Hard seat 1/4" NPT	
Valve type	Male, Steel	
Packing	PTFE	/_/
Stem tip	Non-rotating	
Handle	1-3/4" Phenolic	

[†] If a packing option is chosen, maximum pressure rating is 6,000 psi. Refer to the "Pressure vs. Temperature: Packing Style with Compatible Fluid" chart at the back of this catalog.


^{*} Other o-ring materials available on request.


^{**} For 800 Series only.


^{***} For 850 Series only.

Dimensions

1/4" Bleed Valve









1/2" Bleed Valve










Bleed, Hard Seat

Option With Packing, Hard Seat

Option With Packing, Soft Tip







- 1 Valve body
- 2 FKM o-ring 3 PTFE back-up ring
- 4 Mini valve stem
- 5 Mini valve bonnet
- 6 Set screw
- 7 Mini "T" handle

- 1 Mini valve packing stem
- 2 Mini valve packing bonnet 3 Packing washer 4 Packing

- 5 Packing washer
- 6 Jam nut
- 7 Packing adjustment screw

- 1 Soft tip packing stem
 2 Mini valve packing bonnet
 3 Packing washer
- 4 Packing
- 5 Packing washer
- 6 Jam nut
- 7 Packing adjustment screw