## Industrial Pressure Transmitters & Transducers Voltage Output



## **200** SERIES

- Ranges from vacuum to 0 psig to 15,000 psig; absolute ranges from 0 psia to 15 psia through 0 psia to 300 psia
- · Voltage output
- · 316 and 17-4PH Stainless Steel wetted parts
- · CE compliant to suppress RFI, EMI and ESD

	SPECIFICATIONS						
Output signals	0 Vdc to 5 Vdc, 3-wire; 0 Vdc to 10 Vdc, 3-wire; 1 Vdc to 5 Vdc, 3-wire; 1 Vdc to 6 Vdc, 3-wire; 1 Vdc to 11 Vdc, 3-wire						
Pressure ranges	Vacuum through 0 psig to 15,000 psig Absolute from 0 psia to 15 psia through 0 psia to 300 psia						
Accuracy	$\pm 0.5\%$ full scale (BFSL); optional $\pm 0.25\%$ full scale (BFSL); (Includes the effects of non-linearity, hysteresis, non-repeatability, zero point and full scale errors)						
Stability	$\leq \pm 0.2\%$ full scale per year, non-accumulating						
Adjustment	±10% full scale for zero and span						
Response time	≤ 1 ms (between 10% and 90% full scale)						
Service life	> 100,000,000 load cycles						
Temperature ranges	Compensated 32 °F to 176 °F (0 °C to 80 °C) Effect ±0.017% full scale/ °F for zero and span Media -22 °F to 212 °F (-30 °C to 100 °C) Ambient -40 °F to 185 °F (-40 °C to 85 °C) Storage -40 °F to 212 °F (-40 °C to 100 °C)						
Power requirement*	10 Vdc to 30 Vdc (0 Vdc to 5 Vdc, 3-wire, 1 Vdc to 5 Vdc, 3-wire, 1 Vdc to 6 Vdc, 3-wire) 14 Vdc to 30 Vdc (0 Vdc to 10 Vdc, 3-wire, 1 Vdc to 11 Vdc, 3-wire)						
Load limitations	≥ 5,000 Ω for 0 Vdc to 5 Vdc, 1 Vdc to 5 Vdc, and 1 Vdc to 6 Vdc outputs; ≥10,000 Ω for 0 Vdc to 10 Vdc and 1 Vdc to 11 Vdc outputs. Current consumption 8 mA						
Proof pressure	3 times full scale for ranges 0 psi to 5 psi through 0 psi to 200 psi 1.75 times full scale for ranges 0 psi to 300 psi through 0 psi to 10,000 psi 1.5 times full scale for 0 psi to 15,000 psi						
Burst pressure	3.8 times full scale for ranges 0 psi to 5 psi through 0 psi to 200 psi 4 times full scale for ranges 0 psi to 300 psi through 0 psi to 10,000 psi 3 times full scale for 0 psi to 15,000 psi						
Measuring element	316 Stainless Steel for vacuum through 300 psi; 17-4PH Stainless Steel for ≥500 psi						
Connection	316 Stainless Steel						
Housing material	316 Stainless Steel						
Environmental rating	IP65						
Electromagnetic rating	CE compliant to EMC norm EN 61326:2014/A1:1998 RFI, EMI and ESD protection						
Electrical protection	Reverse polarity, over-voltage and short circuit protection						
Shock	1,000 g's according to IEC 60068-2-27						
Vibration	20 g's according to IEC 60068-2-6						
Weight	Approximately 3.5 oz.						

\* Unregulated



WARNING: This product can expose you to chemicals including Nickel, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

## **APPLICATIONS**

- HVAC
- Hydraulics & pneumatics
- Injection molding machines
- Railroad equipment
- Stamping & forming presses



				ORDERI	NG INI	FORMATION				
SERIES	200									
PRESSURE RANGES	30vac	-30 inHg to 0 psig	30/300	-30 inHg to 300 psig	200	0 psig to 200 psig	3000	0 psig to 3,000 psig	15A	0 psia to 15 psia
	30/15	-30 inHg to 15 psig	5	0 psig to 5 psig	300	0 psig to 300 psig	4000	0 psig to 4,000 psig	30A	0 psia to 30 psia
	30/30	-30 inHg to 30 psig	10	0 psig to 10 psig	500	0 psig to 500 psig	5000	0 psig to 5,000 psig	60A	0 psia to 60 psia
	30/45	-30 inHg to 45 psig	15	0 psig to 15 psig	600	0 psig to 600 psig	6000	0 psig to 6,000 psig	100A	0 psia to 100 psia
	30/60	-30 inHg to 60 psig	30	0 psig to 30 psig	750	0 psig to 750 psig	7500	0 psig to 7,500 psig	150A	0 psia to 150 psia
	30/100	-30 inHg to 100 psig	60	0 psig to 60 psig	1000	0 psig to 1,000 psig	10000	0 psig to 10,000 psig	200A	0 psia to 200 psia
	30/150	-30 inHg to 150 psig	100	0 psig to 100 psig	1500	0 psig to 1,500 psig	15000	0 psig to 15,000 psig	300A	0 psia to 300 psia
	30/200	-30 inHg to 200 psig	150	0 psig to 150 psig	2000	0 psig to 2,000 psig				
				psig = gauge pressure	psia =	absolute pressure Oth	ner ranges a	available on request		
ACCURACIES	1	±0.5% full scale (BFSL)			2	±0.25% full scale (BFS	SL)			
OUTPUT SIGNALS	2	0 Vdc to 5 Vdc, 3-wire	3	1 Vdc to 5 Vdc, 3-wire	4	1 Vdc to 6 Vdc, 3-wire	5	0 Vdc to 10 Vdc, 3-wire	6	1 Vdc to 11 Vdc, 3-wire
PROCESS	1	1/8" NPT male	3	SAE J1926-3:7/16-20 a	djustab	e	10	G1/4 male		
CONNECTIONS	2	1/4" NPT male	9	SAE J1926-1:7/16-20						
ELECTRICAL CONNECTION	1	DIN EN 175301-803 Form C w/ 36" Cable			6	6 1/2" NPT conduit ( with 36" cable)			25	M12 x 1 (4-pin)
	2	4-pin Bayonet			7	7 DIN EN 175301-803 Form C			36	Integral cable 36"
	3	6-pin Bayonet								
		NOTE: 0 Vdc to 5 Vdc a	nd 0 Vdc	to 10 Vdc outputs are als	so availa	able in 4-wire configurat	tions for u	se with other electrical sy	stems.	
OPTION	ST8	Threaded Orifice								

Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.

EXAMPLE	200 - 500 - 1 - 2 - 2 - 7 - ST8
Series	
Pressure range	0 psig to 500 psig
Accuracy	±0.5% full scale (BFSL)
Output signal	0 Vdc to 5 Vdc, 3-wire
Process connection	
Electrical connection	DIN EN 175301-803 Form C
Option	Threaded Orifice

0.72"

(18.2 mm)



200 Series Wiring

CONNECTION TYPE (CODE)

DIN EN 175301-803 Form C (7)

DIN EN 175301-803 Form C w/ Cable (1)

4 or 6-Pin Bayonet (2 or 3)

1/2" NPT Conduit w/ Cable (6)

M12 x 1, 4-Pin (25)

Integral Cable (36)

1/2" NPT Conduit with 36" jacketed cable

\* 6 pin Bayonet

V+

1

Red

А

Red

1

Red

0-5 Vdc, 1-5 Vdc, 1-6 Vdc, 0-10 Vdc, 1-11 Vdc

2

Black

В

Black

3

Black

COMMON OUTPUT

3

White

С

White

4

White

\* 4 pin Bayonet



0.72"

(18.2 mm)





65