ABS & Steel Case, Dry



100 SERIES

- · General purpose non-fillable dry gauge
- Vacuum and compound ranges through 0 psi to 15,000 psi
- 1-1/2", 2", 2-1/2" and 4" gauge sizes
- · Standard impact-resistant ABS & Steel case
- · Copper alloy and Brass wetted parts

OPERATING SPECIFICATIONS

- 1. Working Pressure Limitations
 - a. Dynamic Pressure
 The working pressure should be limited to 60% of the dial range.
 - b. Static Pressure
 The working pressure, where no sharp fluctuations occur, should be limited to 90% of the dial range

APPLICATIONS

- Hydraulics & pneumatics
- Medical
- Pumps & compressors
- Refrigeration controls
- Utilities
- Water management

	SERIES	SPECIFICATIONS				
Pressure ranges	100 Series (all)	Vacuum and compound ranges through 0 psi to 15,000 psi				
Accuracy	15-100, 15-110, 15-120, 20-100, 20-110, 20-120, 20-148, 25-100, 25-110, 25-120	±2.5% full scale				
	40-100	±1.6% full scale				
Temperature ranges*	100 Series (all)	Media -4 °F to 140 °F (-20 °C to 60 °C) Ambient -40 °F to 140 °F (-40 °C to 60 °C)				
Measuring element	100 Series (all)	Copper alloy Bourdon tube				
Connection	15-100, 15-110, 15-120, 20-100, 20-110	1/8" NPT, Brass				
	20-148	1/8" NPT/10-32 Female, Brass				
	20-100, 20-110, 20-120, 25-100, 25-110, 25-120, 40-100	1/4" NPT Brass SAE J1926-3:7/16-20				
Case	15-100, 15-110, 20-100, 20-110, 20-148, 25-100, 40-100	ABS (Acryl Nitril Butadien Styrol)				
	15-120, 20-120, 25-120	Black painted Steel with chrome triangular bezel and U-clamp				
Bezel	15-110, 20-110, 25-110	Built-in bezel, molded as an integral part of the case for ease of panel mounting.				
	15-120, 20-120, 25-120	Chrome-plated Steel triangular bezel				
Lens	100 Series (all)	Acrylic				
Pointer	100 Series (all)	Molded plastic				
Dial	100 Series (all)	White background with black primary scale & red secondary scale. UV resistant.				
Movement	100 Series (all)	Brass & nylon, or all-Brass with highly polished bearing surfaces				

^{*} For every 18 °F (10 °C) shift in temperature from which the gauge is calibrated, the user can experience up to $\pm 0.4\%$ additional error.

For details on accuracy/standard dial configuration and dial layouts, see pages 56-61.



				ORDERING INFORMATION				
GAUGE SIZES	15	1-1/2"	20	2"	25	2-1/2"	40	4"
CASE TYPES	100	ABS, bottom connection	120	Steel case panel mount				
	110	ABS, back connection	148	Square ABS, panel mount (2" only	y)			
PRESSURE RANGES	30vac	-30 inHg vacuum to 0 psi	30/300	-30 inHg to 0 to 300 psi	200	0 psi to 200 psi	2000	0 psi to 2,000 psi
	30/15	-30 inHg to 0 to 15 psi	15	0 psi to 15 psi	300	0 psi to 300 psi	3000	0 psi to 3,000 psi
	30/30	-30 inHg to 0 to 30 psi	30	0 psi to 30 psi	400	0 psi to 400 psi	5000	0 psi to 5,000 psi
	30/60	-30 inHg to 0 to 60 psi	60	0 psi to 60 psi	600	0 psi to 600 psi	6000	0 psi to 6,000 psi
	30/100	-30 inHg to 0 to 100 psi	100	0 psi to 100 psi	1000	0 psi to 1,000 psi	10000	0 psi to 10,000 psi
	30/160	-30 inHg to 0 to 160 psi	160	0 psi to 160 psi	1500	0 psi to 1,500 psi	15000	0 psi to 15,000 psi
	30/200	-30 inHg to 0 to 200 psi						
				Other ranges available on request	t			
SCALE OPTIONS***	psi	psi single scale	psi/kPa	psi/kPa dual scale	psi/kg/cm²	psi/kg/cm² dual scale	psi/bar	psi/bar dual scale
CONNECTION SIZES	1/8	1/8" NPT	SST	SAE J1926-3:7/16-20 Adjustable	1/4	1/4" NPT		
OPTIONS	PMC	Panel Mount Clamp	SSC	Stainless Steel Case	LL	Polycarbonate Lens	ST	Stainless Steel Tagging
	SSB	Polished Stainless Steel Bezel	CRC	Chrome Case	GL	Glass Lens*	CPO	Brass Sintered Orifice 20 Micron
	BLRF	Black Rear Flange	FAC	Flat Sided ABS Case	SG	Safety Glass Lens*	BP1	Brass Press Fit Orifice 0.1 mm
	BLFF	Black Front Flange - ABS Case	BCR	Black Cover Ring**	HL	Homalite Lens*	BP3	Brass Press Fit Orifice 0.3 mm
	CFF	Chrome Front Flange – ABS Case	SSCR	Stainless Steel Cover Ring**	SP	Red Set Pointer**	BP8	Brass Press Fit Orifice 0.8 mm
	SBFF	Black Front Flange - Steel Case	CCR	Chrome Cover Ring**	MIP	Maximum Indicating Poi	nter	
	SCFF	Chrome Front Flange – Steel Case	PCCR	Polished Chrome Cover Ring**	SDM	Silicone Dampened Mov	/ement	
	BSC	Black Steel Case	CAR	Chrome Adapter Ring*	LM	Laser Marking		


Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.

NOTES: Refer to 100 Series options & accessories chart on page 50 for availability by part number.

Cleaning for Oxygen Service (O2) is available only for dry or HL filled gauges


- * A Steel, Stainless or chrome case & cover ring must be additionally ordered when lenses other than acrylic are utilized on all 100 Series.
- ** Only 110 Series require a Steel, Stainless or chrome case & cover ring to be additionally ordered when utilizing a set pointer or cover ring. Please consult factory when a set pointer is to be utilized on a 120 Series.

*** Other scales available on request





Dimensions



0.55"

(14 mm)

1.04"

(26.5 mm)

0.55"

(14 mm)

8

120°

1.04" (26.5 mm)

