
Hard Seat & Soft Seat





- Available in block, single flange, or double flange connection for remote or direct installation
- Designed for use with differential pressure transmitters incorporating two isolation valves and an equalizing valve in differential pressure measurement
- 3110 Series soft seat valves also feature a replaceable Delrin[®] seat, and straight through porting for bidirectional, high capacity flow and easy roddable cleaning
- Blow-out proof stem provides a secondary stem seal in the full open position
- FKM o-ring seal and PTFE back-up ring below the stem threads to protect from corrosion and galling; PTFE or Graphite packing optional
- · All stem threads are rolled for strength and ease of operation
- One-piece bonnet with a metal-to-metal seal to the valve body below the bonnet threads
- · Slotted spring pin to prevent accidental loosening
- · Color coded vinyl dust caps for bonnets and stems (non-packing)

Flow Schematic



SPECIFICATIONS Zinc-Nickel plated Steel, electropolished 316 Stainless Steel*	
electropolished 316 Stainless Steel*	
EL G AIGHAIDT G	
Flange-flange, 1/2" NPT-flange, 1/2" NPT-1/2" NPT	
Hard seat: 10,000 psi @ 200 °F Soft seat: 6,000 psi @ 200 °F	
0.187"	
Hard seat: C _V 0.44 Soft seat: C _V 0.76	
All 316 Stainless Steel stems with FKM o-ring and PTFE back-up ring below the threads, PTFE or Graphite packing optional	
Panel mountings, o-ring materials, handles, packings, regulating stem and stem tips	
Approximately 4.0 lb. without flange, Approximately 5.0 lb. with flange	

^{*} All 316SS products meet the requirements of NACE MR0175/ISO 15156-3.

For NOSHOK Valves with Steel valve types:



WARNING: This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

For NOSHOK Valves with Stainless Steel valve types:



WARNING: This product can expose you to chemicals including Chromium (VI) and Nickel, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

^{*} If a packing option is chosen, maximum pressure rating is 6,000 psi. Refer to the "Pressure vs. Temperature: Packing Style with Compatible Fluid" chart at the back of this catalog.

SERIES	3 3-	-valve				
SEATS	0 Ha	ard seat	1	Soft seat		
PROCESS TYPE	1 Di	ifferential pressure				
CONNECTION	0 1/2	/2" NPT standard or flange				
VALVE TYPES	MFC Fla	lange-Female, Steel	MFS	Flange-Female, Stainless Steel	MMC	Flange-Flange, Steel
	FFC Fe	emale-Female, Steel	FFS	Female-Female, Stainless Steel	MMS	Flange-Flange, Stainless Steel

Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.

EXAMPLE		3110 - MFC
		JIII T
Series	3-valve _	////
Seat	Soft seat	/// /
Process type	Differential pressure	////
Connection	1/2" NPT standard or flange	///
Valve type	Flange-female, Steel _	

To meet all of your specific application requirements, the following **additional options** are available for these manifold valves. To order all or any of these options, simply add them to the part number as shown in the diagram below.

- NOTE 1: The example shown includes ALL possible additional options. Please include ONLY the options required for your application when building your part number. (EXAMPLE: 3110-MFC-P1)
- NOTE 2: When a packing option is selected, an o-ring option is NOT available.
- NOTE 3: The standard o-ring in all the NOSHOK manifold valves is FKM and T1 hard non-rotating (316SS standard) stem tip is the only option available on the 3110 Series soft seat version.

ORDERING INFORMATION - ADDITIONAL OPTIONS						
SOFT SEATS***	PK1	PEEK	KF1	PCTFE		
PACKINGS [†]	P1	PTFE	P2	Graphite**		
STEM TIPS	T1	Non-rotating (316 Stainless)	T6	Ball (carbide)**	T8	Ball (Monel)**
	T5	Ball (440C Stainless)**	T7	Ball (ceramic)**	Т9	Non-rotating regulating (316 Stainless)**
O-RINGS*	EM1	EPDM	KZ1	FFKM (Kalrez® 3018 or equivalent)	NB1	NBR
HANDLES	HL1	1-13/16" Mini "T"	HL4	1-3/8" Phenolic		
	HL3	1" Round knurled	HL5	1-3/4" Phenolic		

Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.

- † If a packing option is chosen, maximum pressure rating is 6,000 psi. Refer to the "Pressure vs. Temperature: Packing Style with Compatible Fluid" chart at the back of this catalog.
- * Other o-ring materials available on request.
- ** For 3010 only.


Please note that the standard o-ring in all the NOSHOK valves is FKM and the standard handles are "T" handles (HL2).

The handle material will always match the material of the valve, unless otherwise specified. For example, the "T" handle (HL2) on the 3110-MFC will be Steel. When only the standard configuration is needed, no additional designations are necessary. Please consult the factory for special application requests.


EXAMPLE with Addition	nal Options	3 1 1 0 - MEC - PK1 - P1 - T1
Sarias	3-valve]]]]
	Soft seat	
	Differential pressure	
	1/2" NPT standard or flange	//////
Valve type	Flange-female, Steel	_////
Soft seat	PEEK ₋	_///
Packing	PTFE -	
Stem tip	Non-rotating _	

Dimensions


Flange-Flange




Top View




Side View




Flange-Female



Top View




Side View




Dimensions


Female-Female




Top View



Side View



Hard Seat Soft Seat



- 1 Valve body
- 2 Blue dust cap
- 3 Plug 4 Gasket ring
- 5 Slotted spring pin
- 6 PTFE back-up ring
- 7 Valve bonnet
- 8 Green dust cap
- 9 Valve "T" handle
- 10 Set screw
- 11 Valve stem
- 12 FKM o-ring
- 13 Head bolt

- 1 Valve body
- 2 Blue dust cap
- 3 Plug
- 4 Gasket ring
 5 Slotted spring pin
 6 Delrin® seat
- 7 FKM o-ring
- 8 Valve bonnet
- 9 Green dust cap
- 10 Valve "T" handle
- 11 Set screw
- 12 Valve stem
- 13 PTFE back-up ring
- 14 Head bolt