0462-201-1631 ACTIVE

DEUTSCH | DEUTSCH Common Contact

TE Internal #: 0462-201-1631 Automotive Terminals, Socket, Pin Diameter 1.59 mm [.063 in], 20 -16 AWG Wire Size, .5 – 1.3 mm² Wire Size, DEUTSCH Common Contact

View on TE.com >

Terminals & Splices > Automotive Terminals > DEUTSCH Solid Contacts



Terminal Type: Socket Mating Pin Diameter: 1.59 mm [.063 in] Terminal Transmits: 0 – 24 A (Low Power) Wire Size: .5 – 1.3 mm²

All DEUTSCH Solid Contacts (46)

Features

Product Type Features

Sealable

Primary Locking Feature

= TEconnectivity

No

On the Terminal

Contact Features

Contact Size	Size 16
Contact Fabrication	Solid
Wire Contact Termination Area Plating Material	Gold
Typical Current Rating	13 A
Crimp Type	Indent
Terminal Type	Socket
Mating Pin Diameter	1.59 mm[.063 in]
Interface Plating	Gold (Au)
Termination Features	
Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire
Dimensions	
Wire Size	.5 – 1.3 mm²
Wire Size Search	16 AWG, 17 AWG, 18 AWG, 19 AWG, 20 AWG

C For support call+1 800 522 6752

Automotive Terminals, Socket, Pin Diameter 1.59 mm [.063 in], 20 – 16 AWG Wire Size, .5 – 1.3 mm² Wire Size, DEUTSCH Common Contact



Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 145 °C, 150 ° C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][293 °F] [302 °F]
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
Operation/Application	
Compatible With Wire Base Material	Copper
Packaging Features	
Packaging Quantity	2500
Packaging Method	Carton
Other	
Customer Preferred Contact	Yes
Terminal Transmits	0 – 24 A (Low Power)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU Compliant with Exemptions Compliant with Exemptions EU ELV Directive 2000/53/EC China RoHS 2 Directive MIIT Order No 32, 2016 Restricted Materials Above Threshold Current ECHA Candidate List: JUNE 2023 EU REACH Regulation (EC) No. 1907/2006 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (1.2% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free Solder Process Capability Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

Automotive Terminals, Socket, Pin Diameter 1.59 mm [.063 in], 20 – 16 AWG Wire Size, .5 – 1.3 mm² Wire Size, DEUTSCH Common Contact



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-onreach

Compatible Parts




Automotive Terminals, Socket, Pin Diameter 1.59 mm [.063 in], 20 – 16 AWG Wire Size, .5 – 1.3 mm² Wire Size, DEUTSCH Common Contact






Also in the Series | DEUTSCH Common Contact



Customers Also Bought



Documents

Product Drawings SOC, SOLID, SIZE 16, 16-20AWG, AU

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_0462-201-1631_99_c-0462-201-1631-99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_0462-201-1631_99_c-0462-201-1631-99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_0462-201-1631_99_c-0462-201-1631-99.3d_stp.zip

C For support call+1 800 522 6752

Automotive Terminals, Socket, Pin Diameter 1.59 mm [.063 in], 20 – 16 AWG Wire Size, .5 – 1.3 mm² Wire Size, DEUTSCH Common Contact



English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages CONNECTOR SELECTOR

English

Product Specifications

Engineering Report

English