

Generic photo of the product

Main technical characteristics of this part number

	Lugaria	
Family	XCK-M	
Type of head	Roller lever	
Operator head	Angular	
Operating head	With thermoplastic roller lever	
Head control device (continued)	-	
Action of angular movement	Right and left	
Operator	By cam 30°	
Speed of attack max	1.5m/s	
Min torque	0.1 Nm	
Connection	Screw clamps	
Output display	Without	
Material - case	Metal	
Dimensions of body (mm)	63 x 64 x 30	
Mounting method	Body	
Type of body	Fixed	
Cable entry	3 for PG 11	
Contact to operate	Snap action	
Positive complete product	Yes	
Contact unit	N/O+N/C	
Form of contact	Zb	
No. of steps	1	
Mechanical conformity	-	
Degree of protection	IP66	
Temperature of operation	-25+70°C	

Generic description of the product

Osiswitch Classic XCKM-XCKL-XCKML limit switch

Metal products dimensions 63x64x30 or 52x72x30 or 81x77x30 heavy duty 15 to 20 million operations enhanced tightness IP66.