

Junior Timer

TE Internal #: 963063-1 PCB Mount Header, Horizontal, Wire-to-Board, 55 Position, 5 mm [. 196 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Signal, Junior Timer

View on TE.com >

Connectors > PCB Connectors > PCB Headers & Receptacles > High Pin Count Header



Connector System: Wire-to-Board

Number of Positions: 55

Centerline (Pitch): 5 mm [.196 in]

Sealable: No

PCB Mount Orientation: Horizontal

All High Pin Count Header (95)



Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Header Type	Fully Shrouded
Connector System	Wire-to-Board
Sealable	No
Configuration Features	
Number of Sections	1
Number of Signal Positions	55
Number of Positions	55
PCB Mount Orientation	Horizontal
Number of Rows	3

PCB Mount Header, Horizontal, Wire-to-Board, 55 Position, 5 mm [.196 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Signal, Junior Timer



Body Features

Primary Product Color	Black
Connector & Keying Code	8
Contact Features	
Contact Size	1.6mm, 3mm
Contact Type	Tab
Mating Tab Width	3 mm[.118 in]
Mating Tab Thickness	.8 mm[.031 in]
Contact Mating Area Plating Material	Tin
Termination Features	
Termination Method to Printed Circuit Board	Through Hole - Solder
Mechanical Attachment	
Mounting Holes	With
Mating Retention	With
Mating Alignment	With
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Mating Retention Type	Locking Interface
Housing Features	
Centerline (Pitch)	5 mm[.196 in]
Dimensions	
Connector Length	137 mm[5.39 in]
Connector Width	26.3 mm[1.03 in]
Profile Height from PCB	35 mm[1.37 in]
Operation/Application	
Shielded	No
Circuit Application	Signal
Packaging Features	
Packaging Type	Carton
Packaging Quantity	10

PCB Mount Header, Horizontal, Wire-to-Board, 55 Position, 5 mm [.196 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Signal, Junior Timer



Other

Interface Number	963534
Product Compliance For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts


TE Part # 962099-1 55P GEH F JUN-TIMER

Also in the Series | Junior Timer

C For support call+1 800 522 6752


PCB Mount Header, Horizontal, Wire-to-Board, 55 Position, 5 mm [.196 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Signal, Junior Timer





Customers Also Bought





Documents

Product Drawings 55P JUN-TIMER GEH

English

CAD Files Customer View Model ENG_CVM_963063-1_15.3d_igs.zip English Customer View Model ENG_CVM_963063-1_15.3d_stp.zip English Customer View Model ENG_CVM_963063-1_15.2d_dxf.zip English 3D PDF

English

3D PDF

S For support call+1 800 522 6752

PCB Mount Header, Horizontal, Wire-to-Board, 55 Position, 5 mm [.196 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Signal, Junior Timer



3D

Customer View Model ENG_CVM_CVM_963063-1_G.2d_dxf.zip English Customer View Model ENG_CVM_CVM_963063-1_G.3d_igs.zip English Customer View Model ENG_CVM_CVM_963063-1_G.3d_stp.zip English

Datasheets & Catalog Pages

Datasheet

English