



Part Number : [1200070475](#)

Product Description : Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 0.34mm² Black PVC Cable, 3.0m (9.84') Length

Series Number : 120007

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 884030E03M030



Documents & Resources

Drawings

[Drawing 1200070475_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Compliant with Exemption 3 per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Contains Lead; Lead monoxide per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 120007 |
| Description | Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 0.34mm ² Black PVC Cable, 3.0m (9.84') Length |
| IP Rating | IP67 |
| Product Family | Brad Micro-Change (M12) Connectors |
| Product Name | Micro-Change (M12) |
| Protocol | N/A |
| Region | Europe |
| Type | Double Ended |
| UPC | 883906073565 |

Agency

| | |
|----|---------|
| UL | E152210 |
|----|---------|

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 60V |

Physical

| | |
|----------------------|--------------------|
| Cable Diameter | 5.40mm (.213") |
| Cable Length | 3.0m (9.84') |
| Color - Cable Jacket | Black |
| Connector End A | Micro-Change (M12) |
| Connector End B | Micro-Change (M12) |
| Coupling Style | Threaded |

| | |
|-------------------------------|----------------------|
| Gender | Female-Male |
| Keyway | Single |
| LED Indicator | No |
| Material - Cable Jacket | PVC |
| Material - Connector Body | PUR |
| Material - Contact | Copper Alloy |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - O-Ring | Fluoro-elastomer |
| Material - Plating Mating | Gold |
| Net Weight | 159.100/g |
| Orientation | Straight to Straight |
| Poles | 4 |
| Temperature Range - Operating | -30° TO +80°C |
| Wire/Cable Type | UL 2464 |
| Wire Size (AWG) | 22 |