

NSYSFN181040P

Floor standing modular electrical enclosure,
PanelSeT SFN, decarbonized steel, mounting
plate, 1800x1000x400mm, IP55



Main

Range	PanelSeT
Extended range	PanelSeT SFN
Application	Multi-purpose
Product or component type	Suitable enclosure
Enclosure nominal height	1800 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	400 mm
Enclosure mounting	Floor-standing
Device composition	2 sliding rails 4 mounting plate quick-fixing brackets 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 1 mounting plate

Complementary

Structure type	Perforated structure with a pitch of 25 mm Vertical uprights joined with top and bottom frames Panels and doors built into the structure Formed from a single section
Door type	Plain front
Number of doors	Front: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	4 points lock, handle with 5 mm double bar insert front door
Mounting plate description	Plain
Type of gland plate	Without gland plate
Accessibility for operation	Rear Sides of enclosure Front
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws
Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Net weight	51.4 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 62208
NEMA degree of protection	NEMA 3R/12
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	195 cm
Package 1 Width	105 cm
Package 1 Length	50 cm
Package 1 Weight	132.7 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	2
Package 2 Height	195 cm
Package 2 Width	105 cm
Package 2 Length	100 cm
Package 2 Weight	265.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------