

NSYCUX350DG

Side Connected Cooling Unit, Climasys CU,
Stainless Steel, 350W, 230V, 50/60Hz, IP55



Main

Range	ClimaSys
Product name	CU
Product or component type	Cooling unit
Mounting type	Side
Installation	Indoor side
Product destination	For enclosure
Mounting mode	By screws
Supply Voltage	230 V AC at 50/60 Hz, 1 phase
Rated Power	350 W
Cooling power	350 W 50/60 Hz L35-L35 186 W 50/60 Hz L35-L50

Complementary

Height	460 mm
Width	290 mm
Depth	190 mm
[In] rated current	1.4 A
Inrush current	3.8 A
Power consumption in W	240 W at 50/60 Hz, L35-L35 270 W at 50/60 Hz, L35-L50
Energy efficiency ratio	1.4
Control type	Electronic controller
Temperature setting range	20...50 °C at 50/60 Hz
Ambient air temperature for operation	20...50 °C at 50/60 Hz inside the enclosure: 5...55 °C at 50/60 Hz outside the enclosure:
Noise level	55 dB
Pressure	28 bar
Flow rate	Internal circuit: 117 m3/h at 50/60 Hz External circuit: 166 m3/h at 50/60 Hz
Net weight	11.7 kg
Cooling gas type	R134a (0.126 kg)
Type of filter	Optional external circuit filter
Protection type	Circuit breaker protection: miniature circuit breaker (MCB)
Protection type	Thermal protection: T 15 A Short-circuit protection (magnetic):
Material	Stainless steel
Colour	Stainless steel

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Product certifications	UL IEC
Directives	2006/42/EC - machinery 2014/30/EU - electromagnetic compatibility 2011/65/EU - RoHS
Standards	EN/ISO 12100 EN 60335-1 EN 60335-2-40 EN 61000-3-2 EN 61000-3-3 EN 61000-6-2 EN 61000-6-3 EN/IEC 63000:2018 EN 14511
IP degree of protection	IP55 conforming to IEC 60529 (on the internal circuit) IP24 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	52 cm
Package 1 Width	38 cm
Package 1 Length	22.5 cm
Package 1 Weight	13 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	4
Package 2 Height	66.4 cm
Package 2 Width	120 cm
Package 2 Length	80 cm
Package 2 Weight	77 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins