



APH-03I-10-13-S

Peltier cooler module

Data sheet



| | | |
|------------------|-----------------------------|------|
| I_{max} | [A] | 3.8 |
| V_{max} | [Vdc] | 3.78 |
| $P_c \max$ | [W] | 8 |
| ΔT_{max} | [°C] | 67 |
| A | [mm] | 15 |
| A1 | [mm] | 15 |
| B | [mm] | 15 |
| H | [mm] | 3.3 |
| L | [mm] | 100 |
| Wire | UL-1332, 200°C, 300V, 20AWG | |

(At hot side temperature $T_h = 25^\circ\text{C} / 298\text{K}$, under dry N_2).

$P_c \max$ = Cooling power at $\Delta T = 0$ and $I = I_{max}$.

ΔT_{max} = Temperature difference at $I = I_{max}$ and $P_c = 0$.

Max hot side temperature $T_h = 80^\circ\text{C}$ for best long term performance.

Max mounting pressure: 1.5MPa.





Wires: UL-1332, 200°C, 300V, 20AWG



APH-03I-10-13-S

Peltier cooler module





Data sheet - At hot side temperature 25°C



APH-03I-10-13-S

Peltier cooler module

Data sheet - At hot side temperature 50°C



Data sheet - At hot side temperature 75°C

