

Part Number : 510211000 Product Description : 1.25mm Pitch, PicoBlade Receptacle Crimp Housing, Single Row, Friction Lock, 10 Circuits, Natural Series Number : 51021 Status : Active Product Category : Connector Housings

Documents & Resources

Drawings 510211000_sd.pdf

3D Models and Design Files

2D Drawing DXF 510211000.dxf 2D Drawing DXF (PDF) 510211000.pdf 3D Model 510211000_stp.zip

Specifications

Application Specification 510210000-AS-000.pdf Application Specification 510210001-AS-000.pdf Packaging Specification SPK-51021-001-001.pdf Product Specification 510210000-PS-000.pdf Product Specification 510210001-PS-000.pdf Product Specification 510210006-PS-000.pdf Product Specification 510211000-PS-000.pdf Product Specification 510211001-PS-000.pdf Product Specification 510211009-PS-000.pdf Product Specification 510211010-PS-000.pdf Product Specification 510211024-PS-000.pdf Product Specification 510211109-PS-000.pdf Product Specification 510211110-PS-000.pdf Product Specification 510211111-PS-000.pdf Product Specification 510211124-PS-000.pdf Product Specification PS-51021-009-001.pdf Product Specification PS-51021-024-001.pdf Product Specification PS-51021-025-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS Not Relevant



China RoHS	©
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2- 21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	51021
Description	1.25mm Pitch, PicoBlade Receptacle Crimp Housing, Single Row, Friction Lock, 10 Circuits, Natural
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Family	PicoBlade Connector System
Product Name	PicoBlade
UPC	800753575677

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	10
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	90.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
PicoBlade Vertical, Single Row, Through Hole Headers	<u>53047</u>
PicoBlade Right-Angle, Single Row, Through Hole Headers	<u>53048</u>
PicoBlade Right-Angle, Single Row, Surface Mount Headers	53261
PicoBlade Vertical, Single Row, Surface Mount Headers	53398
PicoBlade Single Row Plug Housings	<u>51047</u>

Use with Part(s)

	Description	Part Number
--	-------------	-------------

Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 150.00mm Length, 26 AWG, Black	/content/molex/molex-dot- com/us/en/products/product- page.html/797580006.html
Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black	/content/molex/molex-dot- com/us/en/products/product- page.html/797580014.html
Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 152.00mm Length, 28 AWG, Red	/content/molex/molex-dot- com/us/en/products/product- page.html/797581059.html
Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 304.00mm Length, 28 AWG, Red	/content/molex/molex-dot- com/us/en/products/product- page.html/797581060.html
Pre-Crimped Lead PicoBlade Female-to-Pigtail, Tin (Sn) Plating, 304.00mm Length, 28 AWG, Red	/content/molex/molex-dot- com/us/en/products/product- page.html/797581061.html
PicoBlade Female Crimp Terminals	50058
PicoBlade Female Crimp Terminals	50079
Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female	214920
Pre-Crimped Lead PicoBlade Female-to-Pigtail	214921

This document was generated on Nov 01, 2023