




Part Number : [3003612011](#)
Product Description : MX150 Mid-Voltage Mat-Sealed Female Connector Assembly, Dual Row, 4 Circuits, Keying Option A, with Connector Position Assurance, Light Blue
Series Number : [300361](#)
Status : Active
Product Category : [Connector Housings](#)



Documents & Resources

Drawings
[Drawing 3003612011_sd.pdf](#)
[Packaging Design Drawing PK-31300-903-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Connector Housings
Series	300361
Description	MX150 Mid-Voltage Mat-Sealed Female Connector Assembly, Dual Row, 4 Circuits, Keying Option A, with Connector Position Assurance, Light Blue
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	with Connector Position Assurance (CPA)
Product Family	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	196823526886

Physical

Circuits (maximum)	4
Color - Resin	Blue (Light)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	8.560/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Designed to mate with EWCAP interface 150-S-004-2-Z02 only

Use with Part(s)

Description	Part Number
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>