

MU4 technical data



Photo of example product

[Product Page](#)[Product Center](#)[Related Products](#)

Part number	MU400P6H
Product Description	MU4FSDLT5H 24YCSG 48YCSG
Input voltage range	85 - 264VAC (Single phase)
3 Outputs	1. 5V @ 2A (standby) 2. 24V @ 20A (20A max) 12.00V to 30V, 480W max. 3. 48V @ 10A (10A max) 30.00V to 60V, 480W max.
Total output power	Low line = 600W, high line = 800W
Earth leakage	300 µA
Cooling	Variable speed forward air fan
Operating temperature	-20.0°C - 70.0°C (Minimum startup temperature -40.0°C)
Max operating altitude	5000.0m
Case or mounting option	Enclosed
Unit signals and controls	Controls: PSU inhibit, fan enable, module inhibit, remote sense Signals: AC good, DC good, fan fail warning Aux: 5V/2.0A (included in outputs)

Isolation	Input to earth	Input to output	Output to earth
	1.5kVac / 1 x MOPP	4.0kVac / 2 x MOPP	1.5kVac / 1 x MOPP
Input connection	Screw		
Input fuses	All supply lines fused		
Dimensions (mm)	L:254 W:89 H:41mm (10 x 3.5 x 1.61in)		
Weight	1.03kg		
Approvals	CE, EN/IEC/UL60601-1, EN/IEC/UL60950-1, EN/IEC/UL62368-1, UKCA		
Features and benefits	• Very low audible noise. • Designed for BF medical applications. • Meets EN55032 Class B EMC. • Individual output adjustment. • PMBus option. • Fits 1U applications.		
Warranty	7 Years		
Datasheet	Datasheet		