

Part No.: LFXTAL033575



#### **Customer Part:**

## Description

Industry standard SMD crystal
Resistance welded, hermetically sealed in an inert atmosphere,
glass to metal seals on leads
Lead wires are mounted onto a plastic former to create a gull

Model HC49/4HSMX

Model Issue number
 18

## **Frequency Parameters**

■ Frequency
 ■ Frequency Tolerance
 ■ Tolerance Condition
 ■ Frequency Stability
 ■ Operating Temperature Range
 ■ Overtone Order
 7.37280MHz
 ±30.00ppm
 ±50.00ppm
 -20.00 to 70.00°C
 ■ Fundamental

Ageing ±5ppm typ per year @ 25°C

### **Electrical Parameters**

■ Load Capacitance (CL) 18.00pF

Shunt Capacitance (C0) 7pF max

Drive Level 500μW max

ESR 60.00Ω max

### **Environmental Parameters**

 Shock: 981m/s², 6ms, 3 times in each of 3 mutually perpendicular planes

 Vibration: 10Hz-60Hz, 0.75mm amplitude, 60Hz-500Hz, 98.1m/s², 30mins in 3 mutually perpendicular planes

Storage Temperature Range: -55 to 125°C

RoHS Terminations

■ RoHS Reflow Temp 260°C max for 10s max

# Compliance

RoHS Status (2015/863/EU)
 REACh Status
 MSL Rating (JDEC-STD-033):
 Not Applicable


# **Packaging Details**

Tape & reel in accordance with EIA-481
 Quantities below the standard reel size to be supplied on cut tape.


Standard Quantity: 1,000 Pieces



# Outline (mm)



### **Typical Frequency vs Temperature Curves**



#### Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1 760 668 8935

Email: info@iqdfrequencyproducts.com Web: www.iqdfrequencyproducts.com