

Inductors for power circuits Thin-film metal magnetic material **PLE** series









PLEA85D type














FEATURES

- Thin-film power inductor based on the thin-film processing techniques and metallic magnetic materials.
- Oln line with the reduced height of the chip size package (CSP), the height of the product can be reduced from 0.8mm to 0.55mm to provide a low profile power supply circuit.
- The low-loss magnetic material makes it possible to achieve low AC loss and provide a highly efficient power supply circuit in solutions that emphasize AC loss.

APPLICATION

OWearable product (wireless earphones and smart watch), small power supply module and low power consumption communication module of Bluetooth Low Energy

PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

L		LMeasuring frequency	DC resistance		Rated current*			Part No.	
					Isat		Itemp		
(μH)	Tolerance	(MHz)	(mΩ)max.	(mΩ)typ.	(A)max.	(A)typ.	(A)max.	(A)typ.	
0.47	±20%	1.0	120	100	0.7	1.0	1.0	1.5	PLEA85DCAR47M-1PT00
1.0	±20%	1.0	300	250	0.6	0.7	0.85	1.0	PLEA85DCA1R0M-1PT00
2.2	±20%	1.0	600	500	0.4	0.5	0.55	0.7	PLEA85DCA2R2M-1PT00
3.3	±20%	1.0	1200	1000	0.25	0.3	0.45	0.5	PLEA85DCA3R3M-1PT00

^{*} Rated current: smaller value of either lsat or Itemp.

Isat: When based on the inductance change rate (30% below the initial L value)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

Measurement equipment

Measurement item	Product No.	Manufacturer
L	E4991	Keysight Technologies
DC resistance	RM3542	HIOKI
Rated current Isat	E4991+16200B	Keysight Technologies

^{*} Equivalent measurement equipment may be used.

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range *	Storage temperature range **	Individual weight
-40 to +125 °C	-40 to +85 °C	2.4 ma

^{*} Operating temperature range includes self-temperature rise.






^{**} The storage temperature range is for after the assembly.



PLEA85D type

L FREQUENCY CHARACTERISTICS




Measurement equipment

Product No.	Manufacturer		
E4991	Keysight Technologies		

^{*} Equivalent measurement equipment may be used.

INDUCTANCE VS. DC BIAS CHARACTERISTICS



Measurement equipment

Product No.	Manufacturer
E4991+16200B	Keysight Technologies


^{*} Equivalent measurement equipment may be used.

(2/4)




PLEA85D type

SHAPE & DIMENSIONS




RECOMMENDED LAND PATTERN



Dimensions in mm


PACKAGING STYLE

REEL DIMENSIONS



Dimensions in mm

TAPE DIMENSIONS



Dimensions in mm

Туре	Α	В	K
PLEA85D	1.0	1.28	0.75


Taping 100 to 200min. Drawing direction 400 or over

Dimensions in mm

PACKAGE QUANTITY

Package quantity	4000 pcs/reel

RECOMMENDED REFLOW PROFILE





REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products

REMINDERS

The storage period is within 6 months. Be sure to follow the st RH or less). If the storage period elapses, the soldering of the terminal ele	
On not use or store in locations where there are conditions suc	•
Soldering corrections after mounting should be within the range of the state of the	ge of the conditions determined in the specifications.
OWhen embedding a printed circuit board where a chip is moun due to the overall distortion of the printed circuit board and pa	
Self heating (temperature increase) occurs when the power is thermal design.	turned ON, so the tolerance should be sufficient for the set
Carefully lay out the coil for the circuit board design of the nor A malfunction may occur due to magnetic interference.	n-magnetic shield type.
Ouse a wrist band to discharge static electricity in your body the	rough the grounding wire.
On not expose the products to magnets or magnetic fields.	
On not use for a purpose outside of the contents regulated in	the delivery specifications.
or quality require a more stringent level of safety or reliability, damage to society, person or property.	er equipment, personal equipment, office equipment, peration and use condition. rements of the applications listed below, whose performance and
(1) Aerospace/aviation equipment(2) Transportation equipment (cars, electric trains, ships, etc.)(3) Modical equipment	(7) Transportation control equipment (8) Public information-processing equipment (9) Military equipment

- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment

- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.