

Customer Part:



Description

- Standard 2.5 x 2.0 oscillator in a ceramic package with a hermetically sealed metal lid.
- Model IQXO-794
- Model Issue number 2

Frequency Parameters

- Frequency 8.0MHz
- Frequency Stability $\pm 25.00\text{ppm}$
- Operating Temperature Range -20.00 to 70.00°C
- Ageing $\pm 3\text{ppm}$ max per year

Electrical Parameters

- Supply Voltage $1.8\text{V} \pm 5\%$
- Current Draw 10.000mA

Output Details

- Output Compatibility HCMOS
- Drive Capability 15pF
- Rise and Fall Time 10.0ns max
- Duty Cycle $40/60\%$
- Output Voltage High: 90% of V_{S} min
Output Voltage Low: 10% of V_{S} max
- Start Up Time: 10ms max
 0.9ms typ to 90% of final amplitude (under ideal conditions @ 25°C)

Output Control

- Standby Function (pin1):
No Connection = Output Enabled
 $>70\%$ V_{S} = Output Enabled
 $<30\%$ V_{S} = Output Disabled
(when disabled output goes to high impedance state)
- Standby Current: $10\mu\text{A}$ max, $0.5\mu\text{A}$ typ @ 25°C

Noise Parameters

- Jitter (Period pk-pk): $\pm 80\text{ps}$ typ
- Jitter (Phase 12kHz to 20MHz): 1ps max
- Jitter (Period One Sigma): $\pm 10\text{ps}$ typ

Environmental Parameters


- Shock: MIL-STD-202, Method 213. Or comparable.
- Vibration: MIL-STD-883, Method 2007. Or comparable.
- Storage Temperature Range: -55 to 125°C

Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details

- Tape & reel in accordance with EIA-481
Quantities below the standard reel size to be supplied on cut tape.
Standard Quantity: 3,000 Pieces



Outline (mm)



Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1.760 668 8935

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com



Crystal Clock Oscillator Specification

Part No. + Packaging: **LFSPXO082219**

Customer Part:

Sales Office Contact Details:

UK: +44 (0)1460 270200

USA: +1.760 668 8935

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com