

BS Type 'Kx' Glassfibre Extension Thermocouple Cable / Wire



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Good temperature range but will not prevent ingress of				
	fluids. Fairly flexible but does not provide good				
	mechanical protection.				
Cable Length	5m, 10m, 25m, 50m				
Cable Type	Conductors laid flat, Glassfibre insulated with Glassfibre overall, silicone varnished throughout				
Core / Strands	1/0.315mm				
Conductor Cross Section 1/0.315	0.078				
(mm2)					
Drain Wire	No				
Insulation Material	Glassfibre insulated				
Loop Resistance 1/0.315	12.8				
(Ohms per combined metre)					
Max. Temperature	+350°C (short periods up to 400°C)				
Min. Temperature	-60°C				
+ Conductor	Nickel Chromium				
- Conductor	Nickel Aluminium				
Screen	No				
Standards Met	Colour code (cores & jacket) to former British Standard – BS1843-1952				
Thermocouple Type	KX' extension cable for extending 'K' type thermocouples				
Tolerance	Class 2				

Ordering Information

Туре	Colour Code	Cable Style	Strand Size	Length	Manufacturers Code	Farnell Order Code
Кх	BS	GLASSFIBRE FLAT PAIR	1/0.315mm	5m (16.4ft)	WK-041-D	3582309
Kx	BS	GLASSFIBRE FLAT PAIR	1/0.315mm	10m (32.8ft)	WK-041-D	3582312
Кх	BS	GLASSFIBRE FLAT PAIR	1/0.315mm	25m (82ft)	WK-041-D	3582310
Кх	BS	GLASSFIBRE FLAT PAIR	1/0.315mm	50m (164.1ft)	WK-041-D	3582311

