

IEC Type N PTFE Insulated Twin Twisted Pair Thermocouple Cable / Wire



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Resistant to oils, acids adverse agents and fluids. Good mechanical strength and flexibility.		
Cable Length	10m, 25m, 50m, 100m		
Cable Type	Twin twisted pair for extending or making simple		
	thermocouples		
Core / Strands	7/0.2mm		
Conductor Cross Section 7/0.2 (mm2)	0.219		
+ Colour	Pink		
- Colour	White		
Drain Wire	No		
Insulation Material	PTFE insulated		
Loop Resistance 7/0.2	6.2		
(Ohms per combined metre)			
Max. Temperature	+260°C		
Min. Temperature	-75°C		
+ Conductor	Nicrosil		
- Conductor	Nisil		
Screen	No		
Standards Met	Colour code (cores & jacket) to IEC-584-3		
Thermocouple Type	Ν		
Tolerance	Class 1		

Ordering Information

Туре	Colour Code	Cable Style	Strand Size	Length	Manufacturers Code	Farnell Order Code
Ν	IEC	PTFE TWIN TWISTED	7/0.2mm	10m (32.8ft)	WN-140-D	4073349
N	IEC	PTFE TWIN TWISTED	7/0.2mm	25m (82ft)	WN-140-D	4073317
N	IEC	PTFE TWIN TWISTED	7/0.2mm	50m (164.1ft)	WN-140-D	4073339
Ν	IEC	PTFE TWIN TWISTED	7/0.2mm	100m (328.1ft)	WN-140-D	4073331

