

IEC Type T Duplex (4 core) Silicone Rubber Insulated Thermocouple Cable / Wire



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Good electrical and mechanical properties, highly flexible, resistant to oils, acids and other adverse fluids. Good heat resistance to 200°C although not suitable for direct use in high pressure steam applications.			
Cable Length	10m, 25m, 50m, 100m			
Core / Strands	7/0.2mm			
Outer Colour	Brown			
+ Colour	Brown			
- Colour	White			
Drain Wire	No			
Insulation Material	Silicone rubber insulated 7/0.2mm conductors, twisted together with silicone rubber outer jacket			
Max. Temperature	+200°C			
Min. Temperature	-40°C			
Screen	No			
Standards Met	Colour code (cores & jacket) to IEC-584-3			
Thermocouple Type	Type 'T' Duplex for extending up to 2 x type 'T' thermocouples			
Tolerance	Class 2 to IEC-584			

Ordering Information

Туре	Colour Code	Cable Style	Strand Size	Length	Manufacturers Code	Farnell Order Code
Т	IEC	SILICONE RUBBER	7/0.2mm (duplex)	10m (32.8ft)	WT-400-D	4073503
Т	IEC	SILICONE RUBBER	7/0.2mm (duplex)	25m (82ft)	WT-400-D	4073309
Т	IEC	SILICONE RUBBER	7/0.2mm (duplex)	50m (164.1ft)	WT-400-D	4073328
Т	IEC	SILICONE RUBBER	7/0.2mm (duplex)	100m (328.1ft)	WT-400-D	4073336

