



<b>DATA SHEET</b>	53119000
<b>SKINTOP® GMP-GL-M</b>	valid from : 27.05.2003

The SKINTOP® GMP-GL-M, a hexagonal locknut of polyamide, glass fibre reinforced, is used where cable glands are attached but there is only a passthrough whole.  
When the cable gland is fixed in a thread, a higher protection against vibration can be attained with this locknut.



**Technical features:**

material: polyamide, glass fibre reinforced  
(UL 94 – HB)  
sizes: M 12x1,5 - M 63x1,5 in acc. to DIN 60 324  
temperature range: - 20° C up to + 80° C  
colors: RAL 9005, RAL 7001, RAL 7035

For more information please see our current catalogue.  
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: R. Drotleff	Document: DB53119000EN	page 1 of 1
--------------------------------------	------------------------	-------------