



IVS mounting rail adapter

Part no. M22-IVS
216400
EL Number 4355435
(Norway)

General specifications		
Product name		Eaton Moeller® series M22 Accessory Top-hat rail adapter
Part no.		M22-IVS
EAN		4015082164003
Product Length/Depth		35 millimetre
Product height		56 millimetre
Product width		41 millimetre
Product weight		0.017 kilogram
Compliances		CE Marked
Certifications		EN 60947-5 CSA Std. C22.2 No. 14-05 UL 508 IEC 60947-5 CSA Std. C22.2 No. 94-91 CSA CSA-C22.2 No. 14-05 CSA-C22.2 No. 94-91 UL Category Control No.: NKCR CSA File No.: 012528 UL File No.: E29184 CE CSA Class No.: 3211-03 IEC/EN 60947-5 UL
Product Tradename		M22
Product Type		Accessory
Product Sub Type		Top-hat rail adapter
General information		
Accessory/spare part type		Accessory
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		70 °C
Communication		
Connection to SmartWire-DT		No
Contacts		
Force for positive opening - min		0 N
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0 W
Rated operational current for specified heat dissipation (In)		0 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			Not applicable.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Accessories/spare parts for command devices (EC002024)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Command and alarm device (accessories) (ecl@ss13-27-37-12-92 [ACO037015])			
Type of electrical accessory/spare part			Other
Type of mechanical accessory/spare part			Other
Accessory			Yes
Spare part			No