Features/Benefits

- Positive tactile feel
- Multi-positions available
- Wide variety of termination options

Typical Applications

- Instrumentation
- · Computer peripherals
- Telecommunications equipment





Specifications

CONTACT RATING: B contact material (8X25 Models): 0.4 VA max. @ 20 V AC or DC maximum. G contact material (8X21, U8X1 Models): 1 AMP @ 120 V AC or 28 V DC or 0.4 VA max. @ 20 V AC or DC max. Note: Break-before-makecontacts. Multi-pole contacts do not make and break simultaneously. See page A-37 for additional ratings.

ELECTRICAL LIFE: 60,000 make-and-break cycles at full load.

CONTACT RESISTANCE: Below 50 mΩ typ. initial @

2-4 V DC, 100 mA, for both silver and gold plated contacts.

INSULATION RESISTANCE: $10^9\Omega$ min.

DIELECTRIC STRENGTH: 1,000 Vrms min. @ sea level.

OPERATING TEMPERATURE: 8X2X MODELS: -30°C to 75°C. U8X1 MODELS: -30°C to 65°C.

CAP INSTALLATION FORCE: 10 lbs. max. permissible.

SOLDERABILITY: Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

Materials

CASE: Glass filled nylon 6/6 or diallyl phthalate (DAP), flame retardant (UL 94V-0).

PLUNGER: Glass filled nylon or glass filled polyester (PBT)

(UL 94V-0).

CAP & FRAME: Nylon, black, standard. BUSHING: Brass or zinc, nickel plated.

HOUSING: Stainless steel.

SWITCH SUPPORT: Brass or steel, tin plated.

N.O. & N.C. CONTACTS: 8X21, U8X1 MODELS: G contact material: Coin silver, with gold plate over nickel plate. See page A-37 for additional contact materials.

8X25 MODELS: B contact material: Copper alloy, with gold plate over nickel plate. See page A-37 for additional contact materials.

COMMON CONTACT & ALL TERMINALS: Copper alloy, with gold plate over nickel plate.


TERMINAL SEAL: Epoxy.

HARDWARE: Nut & Locking Ring: Brass, nickel plated;

Lockwasher: Steel, nickel plated.


Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages A-24 thru A-37. For additional options not shown in catalog, consult Customer Service Center. All models have epoxy terminal seal and are compatible with all "bottom-wash" PCB cleaning methods.





Dimensions are shown: IN (mm) Dimensions subject to change



MOM. = Momentary

*U811 thru U841 model numbers with all options (except R, R2 terminations) when ordered with G or L contact material


8X25 models must be ordered with B or K contact material. 8X21 and U8X1 models must be ordered with G or L contact material.



Third Angle Projection

SWITCH FUNCTION

			SWITCH FUNCTION		CONNECTED TERMINALS		
			POS. 1	POS. 2	POS. 1	POS. 2	
NO.		UL/CSA* MODEL	1	•	1	•	
POLES	MODEL NO.	NO.	C&K ma oppos	arking on ite side	C&K ma oppos	rking on ite side	SCHEMATIC
	8421	U841	ON	MOM.	1-3,4-6,7-9,10-12	1-2,4-5,7-8,10-11	1 • 4 • (COMM) 7 • 10 •
4P							



MOM. = Momentary


* U811 thru U841 model numbers _® **N ©** with all options (except R, R2 terminations) when ordered with G or L contact material.

8X25 models must be ordered with B or K contact material.
8X21 and U8X1 models must be ordered with G or L contact material.

ACTUATOR—SNAP-IN FRONT MOUNT




J80 SNAP-IN



NOTE: No frame color choice required.

J81 SNAP-IN WITH FRAME



NOTE: Available with C, W-W4, Z or Z3 terminations and SPDT and DPDT models only.

** Increase this dim. to .620/.625 (15,75/15,88) for .091/.125 (2,31/3,18) thk. panels.

Third Angle Projection

Dimensions are shown: IN (mm) Dimensions subject to change



Other colors available, consult Customer Service Center. Cap and Frame Finish: matte.

NOTE: Caps and frames available separately, see pages A-38 and A-39.





ACTUATOR—SNAP-IN FRONT MOUNT


J83

SNAP-IN WITH FRAME AND FLUSH CAP











J82 SNAP-IN WITH FRAME FOR LED







* Increase this dim. to .620/.625 (15,75/15,88) for .091/.125 (2,31/3,18) thk. panels.


LED not included. For LED information, see page A-39.


J84 SNAP-IN WITH FRAME FOR LED, FLUSH CAP



For LED information, see page A-39.

LED not included.





* Increase this dim. to .620/.625 (15,75/15,88) for .091/.125 (2,31/3,18) thk. panels.

CAP AND FRAME COLOR
(STD.) BLACK
WHITE
RED
ORANGE
YELLOW
GREEN
BLUE

GRAY

Other colors available, consult Customer Service Center Cap and Frame Finish: matte

Available with C, W-W4, Z or Z3 terminations and SPDT and DPDT models only.

NOTE: Caps and frames available separately, see pages A-38 and A-39.




Third Angle Projection




ACTUATOR—SNAP-IN FRONT MOUNT



J85 SNAP-IN WITH FRAME AND LED





* Increase this dim. to .620/.625 (15,75/15,88) for .091/.125 (2,31/3,18) thk. panels.



8121J85ZGE223 **SPST**

Available with C, W-W4, Z or Z3 terminations and SPDT models only. For LED information see page A-39.

NOTE: Caps & frames available separately, see pages A-38 and A-39.


OPTION CODE	CAP AND FRAME COLOR
2	(STD.) BLACK
1	WHITE
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
9	GRAY


OPTION CODE	LED COLOR
3	(STD.) RED
5	YELLOW
6	GREEN

For LED information see page A-39.

ACTUATOR—PC MOUNT

PC WITH V-BRACKET AND LED






OPTION CODE	CAP AND FRAME COLOR
2	(STD.) BLACK
1	WHITE
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
9	GRAY

NOTE: Caps available separately, see page A-38. Available with V3 terminations and SPDT models only.

PC MOUNTING



OPTION CODE	LED COLOR
3	(STD.) RED
5	YELLOW
6	GREEN

For LED information see page A-39.




8121J95V3GE23 **SPST**





PLUNGER




NONE


NO PLUNGER CHOICE REQUIRED (JXX ACTUATORS)

AVAILABLE BUSHINGS	DIM. 'A' FOR C, W-W4, Z & Z3 TERMINATIONS	DIM. 'A' FOR A, A2, A3, A4, A6, AV1-AV4, AW-AW4, R & R2 TERMINATIONS	DIM. 'A' FOR V3-V61 TERMINATIONS
D, D9	.244 (6,20)	.228 (5,79)	.224 (5,69)
Н, Н9	.218 (5,54)	.202 (5,13)	.198 (5,03)
Y, Y9	.203 (5,16)	.187 (4,75)	.183 (4,65)
Y3	(5,54)	(5,13)	(5,03)
Y4	.185 (4,70)	.169 (4,29)	.165 (4,19)
D2, D8	N/A	.232 (5,89)	.228 (5,79)
D3	N/A	.162 (4,11)	.158 (4,01)

PLUNGER



M SNAP-FITTING PLUNGER



AVAILABLE BUSHINGS	DIM. 'B' FOR C, W-W4, Z & Z3 TERMINATIONS	DIM. 'B' FOR A, A2, A3, A4, A6, AV1-AV4, AW-AW4, R & R2 TERMINATIONS	DIM. 'B' FOR V3-V61 TERMINATIONS
Y, Y9	.178 (4,52)	.162 (4,11)	.158 (4,01)
Y4	.090 (2,29)	.074 (1,88)	.070 (1,78)

AVAILABLE BUSHINGS	DIM. 'C' FOR C, W-W4, Z & Z3 TERMINATIONS	DIM. 'C' FOR A, A2, A3, A4, A6, AV1-AV4, AW-AW4, R & R2 TERMINATIONS	DIM. 'C' FOR V3-V61 TERMINATIONS
D, D9	.297 (7,54)	.281 (7,14)	.277 (7,04)
Н, Н9	.267 (6,78)	.251 (6,38)	.247 (6,27)
Y, Y9	.259 (6,58)	.243 (6,17)	.239 (6,07)
Y3	(6,78)	(6,37)	(6,27)
Y4	.259 (6,58)	.243 (6,17)	.239 (6,07)
D2, D8	N/A	.273 (6,93)	.269 (6,83)
D3	N/A	.361 (9,17)	.357 (9,07)

N/A = NOT AVAILABLE

NOTE: When selecting plunger option, bushing selection must also be made, see next page. No plunger option is required when any JXX actuator option is selected. Additional plunger lengths are available on SPDT and DPDT models, consult Customer Service Center Not all plunger lengths sufficient for use with caps, see page A-38.

BUSHING

NONE

NO BUSHING CHOICE REQUIRED (JXX ACTUATORS)

D .280" HIGH THREADED, KEYWAY

(STD.) .280" HIGH UNTHREADED. KFYWAY

H (STD.).250" HIGH THREADED, FLAT H9 .250" HIGH UNTHREADED, FLAT

Y .350" HIGH THREADED, KEYWAY


Y9 .350" HIGH UNTHREADED, KEYWAY












1/4-40 UNS-2A MFG. OPTION-RELIEF OR IMPERFECT THD. .040 .020



D9 bushing standard with A-A6, R, R2 AV1-AV3 terminations


H bushing standard with C, W-W4, Z or Z3 terminations. H, H9 bushings not available on single pole models with A3-A6, R, R2 terminations.

Will withstand 12 in./lbs. of torque with no distortion.




Dimensions are shown: IN (mm) Dimensions subject to change






NOTE: No bushing option choice required when JXX actuator option is selected. When selecting bushing option, plunger selection must also be made, see previous page. Plunger lengths vary with bushing and termination options selected.



NOTE: Two mounting nuts, locking ring and lockwasher supplied standard with threaded bushings.





Dimensions are shown: IN (mm)


(STD.) RIGHT ANGLE, PC THRU-HOLE



8121SD9AGE **SPDT**







.185 TYP. (4,70) N.O. N.C. (a) 3

SECTION A-A


Terminal Nos. For Reference Only.

Part Number 8121SH9AGE

A3 RIGHT ANGLE, SNAP-IN, PC THRU-HOLE









Not available with JXX actuators and I seal. Terminal bend radii and lead-in manufacturing option


(STD.) RIGHT ANGLE, PC THRU-HOLE



8221SD9AGE **DPDT**









RIGHT ANGLE, SNAP-IN, PC THRU-HOLE







Not available with JXX actuators and I seal option. Terminal bend radii and lead-in manufacturing option




Cannon



Dimensions subject to change


TERMINATIONS ----

A (STD.) RIGHT ANGLE, PC THRU-HOLE




Not available with JXX actuators and I seal option. Terminal bend radii and lead-in manufacturing option.

A2 RIGHT ANGLE, PC THRU-HOLE



Not available with JXX actuators, I seal option. Terminal bend radii and lead-in manufacturing option.

A4 RIGHT ANGLE, PC THRU-HOLE, REVERSED TERMINALS



Not available with JXX actuators, D3, H, H9, Y3, Y4 bushings and I seal Terminal bend radii and lead-in manufacturing option.

The A4 and R2 termination options are functionally identical and fit the same PC mounting pattern. The switches, however, are shifted relative to the mounting holes. The PC pattern must clear the switch support legs. Unlike the R2, the A4 option is available with UL/CSA.




Dimensions are shown: IN (mm) Dimensions subject to change



TERMINATIONS


A6



Not available with JXX actuators, D3, H, H9, Y3, Y4 bushings and I seal Terminal bend radii and lead-in manufacturing option.


The A6 and R termination options are functionally identical and fit the same PC mounting pattern, The switches, however, are shifted relative to the mounting holes. The PC pattern must clear the switch support legs. Unlike the R, the A6 option is available with UL/CSA.

RIGHT ANGLE WITH PCB




Not available with JXX actuators, D3, H, H9, Y3, Y4 bushings, I seal option. R termination not UL/CSA approved.

RIGHT ANGLE WITH PCB, REVERSED TERMINALS




Not available with JXX actuators, D3, H, H9, Y3, Y4 bushings, I seal option. R2 termination not UL/CSA approved




Snap-acting Momentary Pushbutton Switches













8121SD9AV2GE **SPDT**

AV₃ VERTICAL RIGHT ANGLE, SNAP-IN,, PC THRU-HOLE, .150" PITCH

.070 TYP.


AV1 VERTICAL RIGHT ANGLE, EXTENDED, PC THRU-HOLE, .150" PITCH






Not available with JXX actuators and I seal. Terminal bend radii and lead-in manufacturing option.


AV₂ (STD.) VERTICAL RIGHT ANGLE, PC THRU-HOLE,



.048 TYP.




AV1







8221SD9AV2GE **DPDT**

AV3 VERTICAL RIGHT ANGLE, SNAP-IN, PC THRU-HOLE, .150" PITCH



VERTICAL RIGHT ANGLE, EXTENDED, PC THRU-HOLE, .150" PITCH







Third Angle Projection Dimensions are shown: IN (mm) Dimensions subject to change


Not available with JXX actuators and I seal. Terminal bend radii and lead-in manufacturing option.





















Not available with JXX actuators and I seal.



Not available with JXX actuators and I seal.

V2, V7, V8 VERTICAL MOUNT, V-BRACKET







.555 (14,10)

.630 (16,00)

.953 (24,21)

٧7

۷8

V2

۷7

۷8

.630 (16,00)

.953 (24,21)

8421SD3__GE **4PDT**

OPTION CODE	DIM 'A'
V2	.555 (14,10)
V7	.630 (16,00)
V8	.953 (24,21)



Dimensions are shown: IN (mm) Dimensions subject to change



Not available with JXX actuators and I seal.


Pushbutton


TERMINATIONS

VERTICAL MOUNT, V-BRACKET

VERTICAL MOUNT, V-BRACKET, SNAP-IN

V3, V4, V9






OPTION CODE	DIM 'A'
V3, V31	.460 (11,68)
V4	.630 (16,00)
V9	1.150 (29,21)

Not available with J8X actuators and I seal


V3, V4, V9 VERTICAL MOUNT, V-BRACKET

V31 VERTICAL MOUNT, V-BRACKET, SNAP-IN



C&K MARKING ON OPPOSITE SIDE

.030x.050 TYP.




OPTION CODE	DIM 'A'
V3, V31	.460 (11,68)
V4	.630 (16,00)
V9	1.150 (29,21)

Not available with J8X actuators and I seal


V4, V9 VERTICAL MOUNT, V-BRACKET






.180 (4,57)

.158 (4,01)





OPTION CODE	DIM 'A'	
V4	.630 (16,00)	
V9	1.150 (29,21)	

Not available with JXX actuators and I seal.





Cannon



TERMINATIONS ----

V4, V9 VERTICAL MOUNT, V-BRACKET







OPTION CODE	DIM 'A'	
V4	.630 (16,00)	
V9	1.150 (29,21)	

4PDT

Not available with JXX actuators and I seal.

CONTACT MATERIAL

OPTION CODE	CONTACT MATERIAL	TERMINAL PLATING	RATINGS		
B (STD.)	COLD 1	GOLD ¹	LOW LEVEL/DRY CIRCUIT		
K	GOLD ¹	TIN-LEAD ⁴		8X25 MODELS ONLY: 0.4 VA MAX. @ 20 V AC OR DC MAX.	
G (STD.)	GOLD OVER SILVER ^{2,3}	GOLD ³	LOW LEVEL (DDV CIDCUIT OF DOWER	8X21, U8X1 MODELS ONLY: 0.4 VA MAX @ 20 V AC OR DC MAX. OR	
L		TIN-LEAD ⁴	LOW LEVEL/DRY CIRCUIT OR POWER	1 AMP @ 120 V AC OR 28 V DC.	

CONTACT MATERIAL/APPLICATION RECOMMENDATIONS-SEE SECTION N.

- 2 N.O. AND N.C. CONTACTS: Coin silver, with gold plate over nickel plate.
- ³ COMMON CONTACTS & ALL TERMINALS: Copper alloy, with gold plate over nickel plate.
- ⁴ TERMINALS: Copper alloy, with tin-lead alloy over nickel plate.

U811-U841 models $_{\circ}$ with all options (except R, R2 terminations) when ordered with mandatory G or L contact material.

B or K contact material must be ordered with 8X25 models.

G or L contact material must be ordered with 8X21, U8X1 models.


K or L contact material not available with Z, Z3 terminations.

SEAL ---

E (STD.) EPOXY SEAL

EPOXY POTTED BASE





NO. POLES	DIM 'A'
SP	.410 (10,41)
DP	.440 (11,18)
3P	.505 (12,83)
4P	.505 (12,83)

NOTE: Available with C, W-W4, Z, Z3 terminations only.




Third Angle Projection

Dimensions are shown: IN (mm) Dimensions subject to change



¹ ALL CONTACTS & TERMINALS: Copper alloy, with gold plate over nickel plate.

Snap-acting Momentary Pushbutton Switches



PART NO. 708901000 WHITE 708902000 BLACK 708903000 RED 708904000 ORANGE 708905000 YELLOW 708906000 GREEN 708907000

BI UF

GRAY


708909000 Material: Nylon Finish: Gloss

AVAILABLE HARDWARE .375 DIA

Сар (9,53ø) .250 (6,35) .120 (3.05)

PART NO. 752701000 WHITE 752702000 BLACK 752703000 RED 752704000 ORANGE 752705000 YELLOW 752706000 GREEN 752707000 BI LIF

752709000 Material: Nylon Finish: Gloss




PART NO. 801801000 WHITE 801802000 BLACK 801803000 RED 801804000 ORANGE 801805000 YELLOW 801806000 GREEN

801809000 Material: Nylon Finish: Gloss

801807000

Cap, Snap-fitting plunger




PART NO. 894001000 WHITE 894002000 894003000 894004000 ORANGE 894005000 YELLOW 894006000 GREEN 894007000 BLUE 894009000

Material: Nylon Finish: Gloss

Cap, Snap-fitting plunger

GRAY




PART NO. 894101000 WHITE 894102000 894103000 894104000 ORANGE 894105000 YFLLOW 894106000 GREEN 894107000 BLUE 894109000

Material: Nylon Finish: Gloss

Cap, J80, J81, J82, J83 & J84 options only

BLUE



PART NO. 484601000 WHITE 484602000 BLACK 484603000 484604000 ORANGE 484605000 YELLOW 484606000 GREEN 484607000 BLUE 484609000

Material: Nylon

Finish: Gloss

798201000 WHITE 798202263 BLACK 798203000 798204000 ORANGE 798205000 YFLLOW 798206000 **GREEN** 798207000 BLUE 798209000 GRAY Material: Nylon

Finish: Matte

PART NO.

Frame



PART NO.

615601000 WHITE 615602263 BLACK 615603000 RED 615605000 YELLOW 615606000 GREEN 615609000 GRAY

Material: Nylon




PART NO.

613301000 WHITE 613302263 BLACK 613303000 RED 613305000 YELLOW 613306000 GREEN 613309000 GRAY

Material: Nylon

Cannon

Cap, J85 & J95 options only



PART NO. PART NO. 459701000 459701000 WHITE 459702000 459702000 BLACK 459703000 459703000 RED 459704000 459704000 ORANGE 459705000 459705000 YELLOW 459706000 459706000 GREEN 459707000 459707000 459709000 459709000 GRAY Material: Nylon Material: Nylon Finish: Gloss Finish: Matte

Fits Z3 Termination female connector



PART NO. 530100000 NOTE: Additional nuts, locking rings and lockwashers available separately, see section N.

Other cap & frame colors available, consult Customer Service Center.



Available in loose pieces

AVAILABLE HARDWARE


Frames snap into panel opening and are independent from switch mounting. Accurate positioning of the PC mounted switch relative to the panel opening is necessary to provide proper clearance between actuator and frame. Available in two basic styles and four panel thicknesses .047-.125 in. Material: Nylon. Finish: Matte.






.047" (1,19) PANEL THK.	.062" (1,57) PANEL THK.	.090" (2,29) PANEL THK.	.125" (3,18) PANEL THK.	
PART NO.	PART NO.	PART NO.	PART NO.	
432501000	432601000	432701000	432801000 WHITE	
432502263	432602263	432702263	432802263 BLACK	
432503000	432603000	432703000	432803000 RED	
432505000	432605000	432705000	432805000 YELLOW	
432506000	432606000	432706000	432806000 GREEN	
432509000	432609000	432709000	432809000 GRAY	

PANEL MOUNTING



Panel Inserts

Above frames (part nos. 432XXXXXXX) are also available with insert which accepts LED for indicator light assembly. Order insert separately from frame. Blank insert panel (without hole for LED) also available. **LED not included.**



PANEL INSERT WITH HOLE FOR LED	BLANK PANEL INSERT WITHOUT HOLE FOR LED
PART NO.	PART NO.
894901000	476601000 WHITE
894902000	476602000 BLACK
894903000	476603000 RED
894905000	476605000 YELLOW
894906000	476606000 GREEN
894909000	476609000 GRAY

Special colors, custom markings available, consult Customer Service Center.

LED INFORMATION

SWITCHES WITH LED SUPPLIED: J85, J95 OPTIONS:

Rectangular LEDs are supplied on 8020 Series pushbutton switches with J85 and J95 options. These LEDs are factory installed and are not replaceable. The following specifications apply:

			TYP.	TYP.	MAX RAT	NGS AT 25°C AMBIENT T	EMPERATURE
OPTION CODE	COLOR	TYP. INTENSITY	FORWARD VOLTAGE	FORWARD CURRENT	FORWARD VOLTAGE	CONTINUOUS FORWARD CURRENT	POWER DISSIPATION
6	Green	1.0 mcd		20 mA		50 mA	125 mW
3	Red*	0.5 mcd	2.1 V	10 mA	2.5 V	30 mA	75 mW
5	Yellow	4.0 mcd		20 mA		50 mA	125 mW

Flat denotes cathode. 200 DIA. 77P. (0,63)

.230 DIA. (5,08°)

.230 DIA. (3,04°)

.230 DIA. (19,05)

Suggested LED for J82 & J84 options.

Dimensions for reference only.

Process Information: Soldering to LED leads must be completed within 5 seconds at 500°F (260°C) maximum.

Caution: Circuit elements must limit forward current of LED to 50mA max. continuous.

* Extra-bright red LED available (typ. intensity 4.5 mcd), consult Customer Service Center.

LEDs are not supplied with J82, J84 options. LED snaps into switch frame surrounding actuator and is wired externally.

