







Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	to 32VDC
Duty Rating	200A
Overload	500A-180sec. 1000A-30sec.
Sealing	IP 67/ IEC 529
Vibration	4G / 50-2000Hz
Shock G-Level	6G / 11ms
Weight	~155g / 0.34 Pound
Temperature Range	-40°C to +85°C
Wire Section (at nominal Load)	min. 70mm ²
Mounting Position	optional
Switch Lever	not removeable
Max. Torque (Main Contacts)	12-13Nm

Circuit




For this drawing we reserve the copyright
in accordance with DIN ISO 16016

	Date	Name
Create	08.01.2019	Mielk
Edited	10.10.2019	Seege
Check	11.10.2019	Grind



Scale
1:1

General Tolerances
DIN ISO 2768 cL



Drawing No:

35-210-051-R-901

NSN: