







Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	to 32VDC
Duty Rating	2x200A
Overload	2x500A-180sec.
	2x1000A-30sec.
	2x2500A-5sec.
Sealing	IP 67/ IEC 529
Vibration	4G / 50-2000Hz
Shock G-Level	6G / 11ms
Weight	~360g / 0.79 pound
Temperature Range	-40°C to +85°C
Wire Section (at nominal Load)	min. 70mm ²
Mounting Position	optional
Switch Lever	not removeable
Max. Torque (Main Contacts)	15-20Nm

For this drawing we reserve the copyright in accordance with DIN ISO 16016

	Date	Name
Create	15.10.2007	Grind
Edited	11.06.2019	Seege
Check	24.06.2019	Grind



Scale
1:2

General Tolerances
DIN ISO 2768 cL



Drawing No:

35-221-131-R

NSN: