







Circuit



Technical Data:

Case Material	PA GF black
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	up to 32VDC
Duty Rating	200A
Overload	500A-180sec.
.....	1000A-30sec.
Sealing	IP 67/ IEC 529
Vibration	4G / 50-2000Hz
Shock G-Level	6G / 11ms
Weight	~140g / 0.31 Pound
Temperature Range	-40°C to +85°C
Wire Section (at nominal Load)	min. 70mm ²
Mounting Position	optional
Switch Lever	removeable
Max. Torque (Main Contacts)	12-13Nm

	Date	Name	mm	Scale	Drawing No:
Drawn	08.03.2012	Seege	1:1		35-210-000-R
Check	22.02.2018	Grind	General Tolerances		NSN:
			DIN ISO 2768 cL		

