


Sta-Kon[®]

Non-Insulated Terminals

210-353



These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire. Wire range identification is stamped on the tongue of each terminal.

Most standard bulk catalog numbers can be put on Mylar Tape for reel fed applications (i.e. 12050 tool and applicator dies). See page Q1149.

Please put the suffix M for Mylar Tape RA2573M.

(Bulk number 1000 and 500 packages.)

Stock Thickness:

A & B = .03

BC = .05

C = .04

Non-Insulated Ring


Cat. No.	Pkg. Qty.	Wire Range	Bolt Hole	Wt./Lbs. Per 1000	Dimensions			
					A	B	C	M
A18-4	100	22-16	#4	.75	.31	.27		
A18-6	100	22-16	#6	.72	.29	.27		
A85	1000	22-16	#6	.72	.29	.27		
A18-8	100	22-16	#8	.75	.31	.27		
A86	1000	22-16	#8	.75	.31	.27		
A18-10	100	22-16	#10	.75	.31	.27		
A87	1000	22-16	#10	.75	.31	.27		
A18-14	100	22-16	#14	.92	.39	.37		
A71	1000	22-16	#14	.92	.39	.37		
A72	1000	22-16	#14	.92	.39	.37		
A73	1000	22-16	#14	.92	.39	.37		
A18-12	100	22-16	#12	.99	.44	.35		
A75	1000	22-16	#12	1.06	.72	.38	.70	
A75	1000	22-16	#12	1.06	.72	.38	.70	
B14-4	100	18-14	#4	.72	.26	.27	.59	
B132	1000	18-14	#4	.72	.26	.27	.59	
B14-6	100	18-14	#6	.75	.31	.27	.59	
B133	1000	18-14	#6	.75	.31	.27	.59	
B14-8	100	18-14	#8	.75	.31	.27	.59	
B86	1000	18-14	#8	.75	.31	.27	.59	
B14-10	100	18-14	#10	.75	.31	.27	.59	
B87	1000	18-14	#10	.75	.31	.27	.59	
B14-14	100	18-14	#14	.93	.39	.38	.59	
B71	1000	18-14	#14	.93	.39	.38	.59	
B14-516	100	18-14	#14	.93	.39	.38	.59	
B72	1000	18-14	#14	.93	.39	.38	.59	
B14-38	100	18-14	#14	.96	.54	.38	.59	
B73	1000	18-14	#14	.96	.54	.38	.59	
B14-12	100	18-14	#12	1.06	.72	.38	.70	
B75	1000	18-14	#12	1.06	.72	.38	.70	
B85	1000	18-14	#8	.75	.31	.27	.59	
B134	1000	18-14	#8	.72	.26	.27	.59	
BC14-6	50	heavy duty 16-14	#6	4	.81	.29	.68	
BC85	500	use C tooling	#6	4	.81	.29	.68	
BC14-8	50	heavy duty 16-14	#8	4	.87	.39	.68	
BC86	500	use C tooling	#8	4	.87	.39	.68	
BC14-10	50	heavy duty 16-14	#10	5	.87	.39	.68	
BC87	500	use C tooling	#10	5	.87	.39	.68	
BC14-14	50	heavy duty 16-14	#14	5	.93	.39	.68	
BC71	500	use C tooling	#14	5	.93	.39	.68	
BC14-516	50	heavy duty 16-14	#14	5	1.04	.54	.77	
BC72	500	use C tooling	#14	5	1.04	.54	.77	
BC14-38	50	heavy duty 16-14	#14	5	1.09	.63	.77	
BC79	500	use C tooling	#14	5	1.09	.63	.77	
BC14-12	50	heavy duty 16-14	#12	5	1.32	.76	.94	
BC75	500	use C tooling	#12	5	1.32	.76	.94	
C10-6	50	12-10	#6	4	.82	.31	.27	
C33	500	12-10	#6	4	.82	.31	.27	
C10-8	50	12-10	#8	4	.82	.31	.27	
C77	500	12-10	#8	4	.82	.31	.27	
C10-10	50	12-10	#10	4	.85	.33	.27	
C26	500	12-10	#10	4	.85	.33	.27	
C36	1000	12-10	#10	4	.85	.33	.27	
C10-14	50	12-10	#14	4	.82	.31	.27	
C71	500	12-10	#14	4	.91	.39	.27	
C10-516	50	12-10	#14	4	.98	.41	.27	
C70	500	12-10	#14	4	.98	.41	.27	
C72	1000	12-10	#14	4	.98	.41	.27	
C10-38	50	12-10	#14	4	1.10	.45	.27	
C73	500	12-10	#14	4	1.10	.45	.27	
C10-12	50	12-10	#12	4	1.10	.45	.27	
C75	500	12-10	#12	4	1.21	.72	.38	
C75	500	12-10	#12	4	1.21	.72	.38	

U.L. Listed E9809
 Installing tools: WT111M, WT112M, WT110M,
 ERG-2002, WT1300, WT2000, WT3155A

Thomas & Betts

Sta-Kon[®]

Locking Fork Terminals



Stock thickness same as ring terminal of same size.

Non-Insulated Locking Fork



Cat. No.	Pkg. Qty.	Wire Range	Bolt Hole	Wt./Lbs. Per 1000	Dimensions			
					A	B	C	M
A18-6FL	100	22-16	#6	4%	.75	.25	.27	.59
A221	1000	22-16	#6	4%	.75	.25	.27	.59
A18-8FL	100	22-16	#8	4%	.75	.29	.27	.59
A224	1000	22-16	#8	4%	.75	.29	.27	.59
A18-10FL	100	22-16	#10	4%	.75	.29	.27	.59
A225	1000	22-16	#10	4%	.75	.29	.27	.59
B14-6FL	100	18-14	#6	4%	.75	.25	.27	.59
B220	1000	18-14	#6	4%	.75	.25	.27	.59
B14-8FL	100	18-14	#8	4%	.75	.29	.27	.59
B223	1000	18-14	#8	4%	.75	.29	.27	.59
B14-10FL	100	18-14	#10	4%	.75	.29	.27	.59
B225	1000	18-14	#10	4%	.75	.29	.27	.59
C10-6FL	50	12-10	#6	7%	.85	.31	.27	.66
C220	500	12-10	#6	7%	.85	.31	.27	.66
C10-8FL	50	12-10	#8	7%	.85	.37	.27	.66
C221	500	12-10	#8	7%	.85	.37	.27	.66
C10-10FL	50	12-10	#10	7%	.85	.37	.27	.66
C222	500	12-10	#10	7%	.85	.37	.27	.66
C10-14FL	50	12-10	1/4"	7%	.85	.49	.27	.66

U.L. Listed E9809

U.S. Pat. 3,590,387

Installing tools: WT110M, WT111M, WT112M, WT2000, ERG-2002, WT1300, WTS155A (B&C)

Most standard bulk catalog numbers can be put on Mylar Tape for reel fed applications (i.e. 12050 tool and application dies). See page O1149.

Please put the suffix M for Mylar Tape RA2573M. (Bulk number 1000 and 500 packages.)

Thomas & Betts



250 Series—Female Disconnects—continued

①



RA18-250A
nylon open top
insulated 90° flag
installing tools—
WT145C, WT2000,
ERG-2001, ERG-2003,
WT1455, WT112M

②



A18-250
non-insulated
installing tools—WT111M,
WT1110M, WT2000,
ERG-2002, WT1300,
WT112M

③





B14-250F
non-insulated/insulation
grip installing
tool—WT110M

④



A18-250A
non-insulated 90° flag
installing tools—
WT110M, WT111M,
WT2000, ERG-2002,
WT1300, WT112M



Cat. No.	Pkg. Qty.	Wire Range	Max. Ins.	Tab Size	Wt./Lbs. Per 1000	Dimensions	
						A	B
① RA18-250A	50	22-18	.170	.250 x .032	4	.80	.71
RA2577F	500	22-18	.170	.250 x .032	4	.80	.71
RB14-250A	50	16-14	.190	.250 x .032	5	.80	.72
RB2577F	500	16-14	.190	.250 x .032	5	.80	.72
RC10-250A	50	12-10	.245	.250 x .032	6	.80	.88
RC2577F	500	12-10	.245	.250 x .032	6	.80	.88
② A18-250	100	22-18	—	.250 x .032	3	.73	.31
A250	1000	22-18	—	.250 x .032	3	.73	.31
B14-250	100	16-14	—	.250 x .032	3	.73	.31
B250	1000	16-14	—	.250 x .032	3	.73	.31
C10-250F	50	12-10	—	.250 x .032	4	.73	.31
C250	500	12-10	—	.250 x .032	4	.73	.31
③ B14-250F	100	16-14	—	.250 x .032	5	.87	.31
B250G	1000	16-14	—	.250 x .032	5	.87	.31
④ A18-250A	50	22-18	—	.250 x .032	3	.58	.61
A252G	500	22-18	—	.250 x .032	3	.58	.61
B14-250A	50	16-14	—	.250 x .032	3	.58	.62
B252G	500	16-14	—	.250 x .032	3	.58	.62
C10-250A	50	12-10	—	.250 x .032	4	.64	.63
C252G	500	12-10	—	.250 x .032	4	.64	.63

U.L. Listed E66716

Most standard bulk catalog numbers can be put on Mylar Tape for reel fed applications (i.e. 12050 tool and application dies). See page Q1149.

Please put the suffix M for Mylar Tape RA2573M. (Bulk number 1000 and 500 packages.)

250 Series—Piggy Back Disconnects—Nylon Insulated

Cat. No.	Pkg. Qty.	Wire Range	Max. Ins.	Tab Size	Wt./Lbs. Per 1000	Dimensions		
						A	B	C
RA18-250FP	100	22-18	.136	.250 x .032	3	.87	.30	.43
RA250P	1000	22-18	.136	.250 x .032	3	.87	.30	.43
RB14-250FP	100	16-14	.163	.250 x .032	3	.87	.30	.43
RB250P	1000	16-14	.163	.250 x .032	3	.87	.30	.43

For stacking applications
Installing Tool—WT112M

