



The DNA of tech.™

Product Termination Notification



Product Group: SIL/Mon Nov 27, 2023/PTN-SIL-052-2023-REV-0

Conversion to Copper (Cu) Wire – SQ3427EV

For further information, please contact your regional Vishay office.

CONTACT INFORMATION

Americas

Vishay Siliconix
2565 Junction Ave
-
San Jose CA United States 95134
Phone: (408) 988-8000
Fax:
business-america@vishay.com

Europe

Vishay Electronic GmbH
Dr.-Felix-Zandman-Platz 1
-
Selb Germany 95100
Phone: 49-9287-71 0
Fax: 49-9287-70435
business-europe@vishay.com

Asia

Vishay Intertechnology Asia Pte. Ltd
37A Tampines Street 92 #07-01
-
Singapore Singapore 528886
Phone: 65 6788 6668
Fax: 65 6788 0988
business-asia@vishay.com

Description of Change: The affected part number listed in this notification will be converted to a Copper wire material set. The new ordering code is SQ3427CEV-T1_GE3, which has the exact same product performance and fit as SQ3427EV. There will be no change to the wafer fab or assembly location (Note: parts with _BE3 suffix will be consolidated to a single assembly location at Simconix). There will be no changes to the parameters on the datasheet (reference: SQ3427CEV Doc # 62369 Rev.B).

Reason for Change: Standardization of materials

Expected Influence on Quality/Reliability/Performance: None

Part Numbers/Series/Families Affected: SQ3427EV-T1_GE3, SQ3427EV-T1_BE3,

Vishay Brand(S): Vishay Siliconix

Time Schedule:

Last Time Buy Date: Mon Jun 3, 2024

Last Time Ship Date: Tue Dec 3, 2024

Sample Availability: Qualified samples of replacement product are available on request

Product Identification: SQ3427CEV-T1_GE3


Qualification Data: AEC Q101 qualification data of replacement product is available. Qualification PPAP is available now.

This PTN is considered approved, without further notification, unless we receive specific customer concerns before Mon Jun 3, 2024 or as specified by contract.

Issued By: Lance Gurrola, automostechsupport@vishay.com



Automotive P-Channel 60 V (D-S) 175 °C MOSFET




FEATURES

- TrenchFET® power MOSFET
- AEC-Q101 qualified
- 100 % R_g and UIS tested
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE



PRODUCT SUMMARY

V_{DS} (V)	-60
$R_{DS(on)}$ (Ω) at $V_{GS} = -10$ V	0.095
$R_{DS(on)}$ (Ω) at $V_{GS} = -4.5$ V	0.135
I_D (A)	-5.3
Configuration	Single

Marking Code: 9Q

ORDERING INFORMATION

Package	TSOP-6
Lead (Pb)-free and halogen-free	SQ3427CEV (for detailed order number please see www.vishay.com/doc?79771)

ABSOLUTE MAXIMUM RATINGS ($T_C = 25$ °C, unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-Source Voltage	V_{DS}	-60	V
Gate-Source Voltage	V_{GS}	± 20	
Continuous Drain Current	I_D	$T_C = 25$ °C	A
		$T_C = 125$ °C	
Continuous Source Current (Diode Conduction)	I_S	-6.3	
Pulsed Drain Current ^a	I_{DM}	-21	
Single Pulse Avalanche Current	I_{AS}	-21	
Single Pulse Avalanche Energy	E_{AS}	22	mJ
Maximum Power Dissipation	P_D	$T_C = 25$ °C	W
		$T_C = 125$ °C	
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 to +175	°C

THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	LIMIT	UNIT
Junction-to-Ambient	R_{thJA}	110	°C/W
Junction-to-Foot (Drain)	R_{thJF}	30	

Notes

- a. Pulse test; pulse width ≤ 300 μ s, duty cycle ≤ 2 %.
b. When mounted on 1" square PCB (FR4 material).



SPECIFICATIONS (T _C = 25 °C, unless otherwise noted)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-Source Breakdown Voltage	V _{DS}	V _{GS} = 0, I _D = -250 μA		-60	-	-	V
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = -250 μA		-1.5	-2	-2.5	
Gate-Source Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V		-		± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V	V _{DS} = -60 V	-	-	-1	μA
		V _{GS} = 0 V	V _{DS} = -60 V, T _J = 125 °C	-	-	-50	
		V _{GS} = 0 V	V _{DS} = -60 V, T _J = 175 °C	-	-	-150	
On-State Drain Current ^a	I _{D(on)}	V _{GS} = -10 V	V _{DS} ≤ -5 V	-10	-	-	A
Drain-Source On-State Resistance ^a	R _{DS(on)}	V _{GS} = -10 V	I _D = -4.5 A	-	0.079	0.095	Ω
		V _{GS} = -10 V	I _D = -4.5 A, T _J = 125 °C	-	-	0.148	
		V _{GS} = -10 V	I _D = -4.5 A, T _J = 175 °C	-	-	0.178	
		V _{GS} = -4.5 V	I _D = -3.5 A	-	0.112	0.135	
Forward Transconductance ^a	g _{fs}	V _{DS} = -15 V, I _D = -4 A		-	9	-	S
Dynamic ^b							
Input Capacitance	C _{iss}	V _{GS} = 0 V	V _{DS} = -30 V, f = 1 MHz	-	726	1000	pF
Output Capacitance	C _{oss}			-	91	120	
Reverse Transfer Capacitance	C _{rss}			-	56	80	
Total Gate Charge ^c	Q _g	V _{GS} = -10 V	V _{DS} = -30 V, I _D = -5 A	-	16.9	22	nC
Gate-Source Charge ^c	Q _{gs}			-	2.9	-	
Gate-Drain Charge ^c	Q _{gd}			-	4.1	-	
Gate Resistance	R _g	f = 1 MHz		2.5	5	7.5	Ω
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = -30 V, R _L = 6 Ω I _D ≡ -5 A, V _{GEN} = -10 V, R _g = 1 Ω		-	8	12	ns
Rise Time ^c	t _r			-	24	35	
Turn-Off Delay Time ^c	t _{d(off)}			-	25	38	
Fall Time ^c	t _f			-	33	50	
Source-Drain Diode Ratings and Characteristics ^b							
Pulsed Current ^a	I _{SM}			-	-	-21	A
Forward Voltage	V _{SD}	I _F = -1.6 A, V _{GS} = 0 V		-	-0.8	-1.2	V
Body diode reverse recovery time	t _{rr}	I _F = -1.7 A, di/dt = 100 A/μs		-	23	46	ns
Body diode reverse recovery charge	Q _{rr}			-	27	54	nC
Reverse recovery fall time	t _a			-	20	-	
Reverse recovery rise time	t _b			-	3	-	ns
Body diode peak reverse recovery current	I _{RM(REC)}			-	-2.86	-	A


Notes

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.
c. Independent of operating temperature.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




On-Resistance vs. Drain Current and Gate Voltage




Transfer Characteristics



Transfer Characteristics




Capacitance




Transconductance




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Gate Charge




On-Resistance vs. Gate-to-Source Voltage




On-Resistance vs. Junction Temperature



Threshold Voltage




Source-Drain Diode Forward Voltage




Drain-to-Source Voltage vs. Junction Temperature



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Safe Operating Area, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Ambient



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Foot

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?62369.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.