Product datasheet

page 1 of 1 date 10/20/00

7704NH



Description

22 AWG solid bare copper, Foam flame retardant Pe insulated, 2 pair, Beldfoil Aluminium Polyester shield, 24 AWG drain wire, LSNH jacket

,		
Dimensions		
Nom. insulation Thickness	0.45	mm
Nom. diameter over insulation	1.32	mm
Nom. Jacket thickness	0.6	mm
Nom. outer diameter	6.5	mm
Electrical characteristics		
Max. operating voltage	300	V Rms
Max. Continuos current per conductor @ 25 deg. C	2.5	A
Nom. Capacitance between conductors of a pair @ 1	46	nF/km
Nom. capacitance conductor to shield @ 1 kHz	80	nF/km
Nom. Conductor DC resistance @ 20 Deg. C	55	Ohm/km
Nom. Shield DC resistance @ 20 Deg. C	17	Ohm/km
Nom. Impedance @ 1 MHz	100	Ohm
Nom. Attenuation		
@772kHz 1.9 dB/100m @ 1 MHz 2.1dB/100m @ 4 MHz 4.3 dB/100m @ 10M MHz 8 9 dB/100m @ 20 MHz 10 2 db/100m	[Hz 7.2 dB/100r	n @ 16

MHz 8.9 dB/100m @ 20 MHz 10.2 db/100m

Physical characteristics

Temperature rating	-15 to +80	Deg. C
Insulation material	Foam Flame retardant Pe	
Jacket material (color)	LSNH (White)	
Type shield and % coverage	Aluminium polyester 100%	
Max. pulling tension	50	N
Min. bend radius	80	mm
Applicable specifications	BS 7655 Section 6.1 Table 1 LTS 3	
Flame resistance	IEC 332-1	

Color code

White-Blue & Blue-White / White-orange & orange-White

Application

Instrumentation and computer cables for Data transmission applications (label contains Ce marking)