
# Keysight Technologies 41800A Active Probe, 5 Hz to 500 MHz Reliable In-Circuit Signal Analysis

Technical Overview







The Keysight Technologies, Inc. 41800A active probe provides high input impedance from 5 Hz to 500 MHz. The 41800A is a valuable tool when used with a network and spectrum analyzer for circuit signal analysis. The 41800A improves your circuit design and evaluation for audio, video, HF, and VHF bands. The low input capacitance offers probing with negligible circuit loading, making it effective for precise in-circuit measurements.

# For Both Spectrum and Network Analysis

The 41800A can be used with a spectrum analyzer to evaluate the quality of circuits by measuring spurious level, harmonics, and noise. The active probe can also be used with a network analyzer to perform gain, phase, and group-delay measurements at the circuit-level.

# Retractable Metal Sleeve for Protection

In addition to excellent performance, the 41800A also has a design to protect the probe tip. The probe has a retractable metal sleeve which protects the probe tip from a physical damage when not used and also from electro-static discharge (ESD) damage.

# Compatible with Keysight Network and Spectrum Analyzers

The 41800A is directly compatible with Keysight network and spectrum analyzers shown in the table below. These Keysight analyzers have the probe power supplied from the front panel. In addition, you can use the Keysight 11899A probe power supply with other analyzers that don't have a compatible power supply for the 41800A.

# Network/Spectrum/Impedance Analyzer

4395A, 4396B

## Spectrum Analyzer

8590 Series

## Network Analyzer

E5100A

# Specifications

(Terminated with Keysight part number 11880-60001 type-N adapter)

Donal width:	
Bandwidth:	5 Hz to 500 MHz
Probe gain:	0 dB ± 0.5 dB @ 50 MHz
Input R, C (typical):	100 kW, 3 pF (probe alone)
	1 MW, 1 pF (with 10:1, 100:1 divider)
Frequency response relative to 50 MHz:	+1/-2 dB @ < 50 Hz
	±1 dB @ 50 Hz to 200 MHz
	+1.5/-2 dB @ > 200 MHz
Average noise level (typical):	10 nV/ Hz @ ≥ 300 kHz
	+3 dB/Oct @ <300 kHz
2nd harmonic distortion (typical):	< -50 dBc @ -20 dBm (250 MHz) input
3rd order intermodulation	< -70 dBc @ -26 dBm two signals input
distortion (typical):	(400 MHz, 400.5 MHz)
1 dB gain compression:	> +3 dBm input @ 500 MHz
Maximum allowable input (DC + AC):	±40 V
Output connector:	50 W type-N male
Power:	+15 V/85 mA, -12.6 V/65 mA
Weight:	0.3 kg (probe alone)
	2 kg (including accesssories)
Length:	Approximatly 1.2 m
Operating temperature humidity:	0 °C to 55 °C, RH ≤ 95% (40 °C)
Accessories furnished:	Type BNC male adapter, 10:1, 100:1 dividers, Hook tip, 2.5 inch ground lead, 30 mil, 12 mil
	spare probe tips, spanner tip assembly, probe tip nut driver, operating note, carrying case

# Optional Accessories

Keysight 11899A probe power supply Keysight part number 11880-60001 type-N male adapter

# **Option Ordering Information**

41800A active probe Option 41800A-UK6:

Commercial calibration certificate with test data

#### myKeysight

## myKeysight

#### www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

#### www.axiestandard.org



AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.

#### www.lxistandard.org



LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.

#### www.pxisa.org



PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.

#### Three-Year Warranty



## www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.

#### Keysight Assurance Plans



#### www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.

# www.keysight.com/go/quality



Keysight Technologies, Inc. DEKRA Certified ISO 9001:2008 Quality Management System

#### Keysight Infoline

# www.keysight.com/find/service

#### Keysight Infoline

Keysight's insight to best in class information management. Free access to your Keysight equipment company reports and e-library.

# Keysight Channel Partners

#### www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

#### **Americas**

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

#### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

#### Europe & Middle East

Europe a middle Eust	
Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)

For other unlisted countries: www.keysight.com/find/contactus (BP-04-23-15)

United Kingdom

0800 0260637

