

### Main

Device short name	TF
Enclosure type	Open box

### Complementary

Depth	5.81 in (147.57 mm)
Device composition	Top fuse disconnecter
Electrical connection	Screw clamp terminal
Fuse type	0.41 x 1.50 in CC top
Height	7.46 in (189.48 mm)
Material	Copper winding
Mounting support	panel
Phase	1 phase
Primary voltage	600 V 575 V 550 V
Rated power in VA	1500 VA
Secondary voltage	110/115/120 V
Temperature rise	115 °C
Width	7.06 in (179.32 mm)

### Environment

Insulation temperature	356 °F (180 °C)
Product certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239 CE
Standards	UL 508 NEC 450

### Ordering and shipping details

Category	16203 - 9070 TF (NOT T) 250-1000VA
Discount Schedule	CP8
GTIN	00785901755128
Returnability	No
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------