





#### Features

- Wide input range 180 ~ 528VAC
- · Constant Current mode output
- · Metal housing with Class I design
- · Built-in active PFC function
- IP67 / IP65 design for indoor or outdoor installations
- Function options: output adjustable via potentiometer;
   3 in 1 dimming (dim-to-off); Smart timer dimming
- · Typical lifetime>50000 hours
- 5 years warranty

# IP65 IP67 🕝 [fil c Type HL us F©


### Applications

- · LED street lighting
- · LED high-bay lighting
- Parking space lighting
- · LED fishing lamp
- Type "HL" for use in Class I, Division 2 hazardous (Classified) location.

#### Description

HVGC-320 series is a 320W LED AC/DC LED power supply featuring the constant current mode and high voltage output. HVGC-320 operates from 180~528VAC and offers models with different rated current ranging between 700mA and 3500mA. Thanks to the high efficiency up to 93.5%, with the fanless design, the entire series is able to operate for -40°C ~ +90°C case temperature under free air convection. The design of metal housing and IP67/IP65 ingress protection level allows this series to fit both indoor and outdoor applications. HVGC-320 is equipped with various function options, such as dimming methodologies, so as to provide the optimal design flexibility for LED lighting system.

### **■** Model Encoding



Type	IP Level	Function	Note
Α	IP65	Io adjustable through built-in potentiometer.	In Stock
В	IP67	3 in 1 dimming function (0~10Vdc, 10V PWM signal and resistance)	In Stock
AB	IP65	Io adjustable through built-in potentiometer & 3 in 1 dimming function (0~10Vdc, 10V PWM signal and resistance)	In Stock
Dx	IP67	Built-in Smart timer dimming function by user request.	By request
D2	IP67	Built-in Smart timer dimming and programmable function.	By request

# 320W Constant Current Mode LED Driver


## **SPECIFICATION**

MODEL		HVGC-320-700	HVGC-320-1050	HVGC-320-1400	HVGC-320-1750	HVGC-320-2100	HVGC-320-2800	HVGC-320-3500	
	RATED CURRENT	700mA	1050mA	1400mA	1750mA	2100mA	2800mA	3500mA	
	RATED POWER	300W	320W	320W	320W	320W	320W	320W	
	CONSTANT CURRENT REGION Note.2		152.4 ~ 304.8V	114.3 ~ 228.6V	91.4~182.8V	76.2 ~ 152.4V	57 ~ 114.3V	45.7 ~ 91.4V	
	OPEN CIRCUIT VOLTAGE (max.)		311V	234V	187V	156V	118V	94V	
OUTPUT	Of EN ONCOTT VOLTAGE (IIIax.)		AB-Type only (via bi	1		130 V	1100	344	
OUIFUI	CURRENT ADJ. RANGE	350~700mA	525~1050mA	700~1400mA	875~1750mA	1050~2100mA	1400~2800mA	1750~3500mA	
	CURRENT DIRRI E			700~1400IIIA	075~1750IIIA	1030°2100IIIA	1400°2000IIIA	1750~5500IIIA	
	CURRENT RIPPLE	5.0% max. @rated current							
	CURRENT TOLERANCE	±5% 500me/230VAC 347VAC 480VAC							
	SET UP TIME Note.4								
	VOLTAGE RANGE Note.3	180 ~ 528VAC 254VDC ~ 747VDC							
	EDEQUENOV DANCE	(Please refer to "STATIC CHARACTERISTIC" section)							
	FREQUENCY RANGE	47 ~ 63Hz							
	POWER FACTOR (Typ.)				AC, PF≥0.93/480V	AC @full load			
		`	POWER FACTOR (F	,	•				
	TOTAL HARMONIC DISTORTION	, , ,			C, @ load ≥ 60%/48	BOVAC)			
INPUT		`	TOTAL HARMONI	,	· · · · ·				
	EFFICIENCY (Typ.)	93.5%	93.5%	93.5%	93.5%	93.5%	93.5%	93%	
	AC CURRENT (Typ.)	1.1A / 347VAC	0.8A / 480VAC						
	INRUSH CURRENT(Typ.)	COLD START 50A	A(twidth=920µs meas	sured at 50% Ipeak) a	at 480VAC; Per NEN	//A 410			
	MAX. NO. of PSUs on 16A CIRCUIT BREAKER	2 unit(circuit breaker of type B) / 4 units(circuit breaker of type C) at 480VAC							
	LEAKAGE CURRENT	<0.75mA/480VAC							
	SHORT CIRCUIT	Constant current limiting, recovers automatically after fault condition is removed							
		445 ~ 455V	320 ~ 351V	240 ~ 263V	192 ~ 210V	160 ~ 175V	120 ~ 131V	96 ~ 105V	
PROTECTION	OVER VOLTAGE	Shut down o/p vo	Itage with re-power	r on to recovery	1	1	'	·	
	OVER TEMPERATURE	Shut down and latch off o/p voltage, re-power on to recover							
	WORKING TEMP.					section)			
	MAX. CASE TEMP.	Tcase=-40 ~ +90°C (Please refer to "OUTPUT LOAD vs TEMPERATURE" section)  Tcase=+90°C							
	WORKING HUMIDITY	20 ~ 95% RH non-condensing							
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH							
	TEMP. COEFFICIENT								
	VIBRATION	±0.03%/°C (0 ~ 60°C)  10 ~ 500Hz, 5G 12min./1cycle, period for 72min. each along X, Y, Z axes							
	SAFETY STANDARDS					167 approved			
	WITHSTAND VOLTAGE	UL8750 (type"HL"), CSA C22.2 No. 250.13-12, EAC TP TC 004, IP65 or IP67 approved							
SAFETY &		I/P-O/P:3.75KVAC							
EMC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG; O/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH							
	EMC EMISSION	Compliance to FCC Part 15 Subpart B, EAC TP TC 020							
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61547, light industry level (surge immunity Line-Earth 4KV, Line-Line 2KV), criteria A, EAC TP TC 020							
	MTBF	141.2K hrs min. MIL-HDBK-217F (25°C)							
OTHERS	DIMENSION	262*90*43.8mm (	,						
	PACKING	2Kg; 8pcs/17Kg/0.92CUFT							
NOTE	1. All parameters NOT specially mentioned are measured at 347VAC input, rated current and 25°C of ambient temperature.								
	<ol> <li>Please refer to "DRIVING METHODS OF LED MODULE".</li> <li>De-rating may be needed under low input voltages. Please refer to "STATIC CHARACTERISTIC" sections for details.</li> </ol>								
	4. Length of set up time is measured at first cold start. Turning ON/OFF the power supply may lead to increase of the set up time.								
	5. The driver is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the								
	complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.								
	6. This series meets the typical life expectancy of >50,000 hours of operation when Tcase, particularly (tc) point (or TMP, per DLC), is about 80 °C or less.								
	7. Please refer to the warranty	statement on ME	AN WELL's websi	te at http://www.me	eanwell.com.				
	8. The ambient temperature de	erating of 3.5°C/10	000m with fanless	models and of $5^{\circ}$ C	/1000m with fan m	nodels for operating	g altitude higher tha	an 2000m(6500ft).	




#### **■** Block Diagram

PFC fosc : 45KHz PWM fosc : 50KHz



#### **■** DRIVING METHODS OF LED MODULE

 $\frak{\%}$  This series works in constant current mode to directly drive the LEDs.




Typical output current normalized by rated current (%)


In the constant current region, the highest voltage at the output of the driver depends on the configuration of the end systems.

Should there be any compatibility issues, please contact MEAN WELL.






- Direct connecting to LEDs is suggested. It is not suitable to be used with additional drivers.
- Dimming source current from power supply: 100μA (typ.)
- O Applying additive 0 ~ 10VDC




"DO NOT connect "DIM- to -V"

O Applying additive 10V PWM signal (frequency range 100Hz ~ 3KHz):





"DO NOT connect "DIM- to -V"

O Applying additive resistance:



"DO NOT connect "DIM- to -V"





100%
90%
80%
70%
60%
30%
20%
Short 10KIN 20KIN 30KIN 40KIN 50KIN 50KIN 80KIN 70KIN 80KIN 90KIN 100KIN 10KIN 10KIN

Note: 1. Min. dimming level is about 5% and the output current is not defined when 0% < Iout < 5%.


2. The output current could drop down to 0% when dimming input is about 0kΩ or 0Vdc, or 10V PWM signal with 0% duty cycle.



#### **X** Smart timer dimming function (for Dxx-Type by User definition)

MEAN WELL Smart timer dimming primarily provides the adaptive proportion dimming profile for the output constant current level to perform up to 14 consecutive hours. 3 dimming profiles hereunder are defined accounting for the most frequently seen applications. If other options may be needed, please contact MEAN WELL for details.

Ex: O D01-Type: the profile recommended for residential lighting




Set up for D01-Type in Smart timer dimming software program:

	T1	T2	Т3	T4
TIME**	06:00	07:00	11:00	
LEVEL**	100%	70%	50%	70%

Operating Time(HH:MM)

- \*\*: TIME matches Operating Time in the diagram whereas LEVEL matches Dimming Level.
  - Example: If a residential lighting application adopts D01-Type, when turning on the power supply at 6:00pm, for instance:
- [1] The power supply will switch to the constant current level at 100% starting from 6:00pm.
- [2] The power supply will switch to the constant current level at 70% in turn, starting from 0:00am, which is 06:00 after the power supply turns on.
- [3] The power supply will switch to the constant current level at 50% in turn, starting from 1:00am, which is 07:00 after the power supply turns on.
- [4] The power supply will switch to the constant current level at 70% in turn, starting from 5:00am, which is 11:00 after the power supply turns on. The constant current level remains till 8:00am, which is 14:00 after the power supply turns on.

#### Ex: O D02-Type: the profile recommended for street lighting



Set up for D02-Type in Smart timer dimming software program:

	T1	T2	Т3	T4	T5
TIME**	01:00	03:00	8:00	11:00	
LEVEL**	50%	80%	100%	60%	80%


\*\*: TIME matches Operating Time in the diagram whereas LEVEL matches Dimming Level.

Example: If a street lighting application adopts D02-Type, when turning on the power supply at 5:00pm, for instance:

- [1] The power supply will switch to the constant current level at 50% starting from 5:00pm.
- [2] The power supply will switch to the constant current level at 80% in turn, starting from 6:00pm, which is 01:00 after the power supply turns on.
- [3] The power supply will switch to the constant current level at 100% in turn, starting from 8:00pm, which is 03:00 after the power supply turns on.
- [4] The power supply will switch to the constant current level at 60% in turn, starting from 1:00am, which is 08:00 after the power supply turns on.
- [5] The power supply will switch to the constant current level at 80% in turn, starting from 4:00am, which is 11:00 after the power supply turns on. The constant current level remains till 6:30am, which is 14:00 after the power supply turns on.

#### 320W Constant Current Mode LED Driver

Ex: O D03-Type: the profile recommended for tunnel lighting



Set up for D03-Type in Smart timer dimming software program:

	T1	T2	Т3
TIME**	01:30	11:00	
LEVEL**	70%	100%	70%


Example: If a tunnel lighting application adopts D03-Type, when turning on the power supply at 4:30pm, for instance:

- [1] The power supply will switch to the constant current level at 70% starting from 4:30pm.
- [2] The power supply will switch to the constant current level at 100% in turn, starting from 6:00pm, which is 01:30 after the power supply turns on.
- [3] The power supply will switch to the constant current level at 70% in turn, starting from 5:00am, which is 11:00 after the power supply turns on.

The constant current level remains till 6:30am, which is 14:00 after the power supply turns on.

<sup>\*\*:</sup> TIME matches Operating Time in the diagram whereas LEVEL matches Dimming Level.







# ■ LIFE TIME

