

Evaluating the LT3078 5A, Ultra-Low Noise, High PSRR, 55 mV Dropout Ultra-Fast Linear Regulator

FEATURES

- ▶ Input voltage range: 0.6 V to 5.5 V
- ▶ BIAS voltage range: 2.375 V to 5.5 V
- Jumpers program output voltage according to selection matrix: 0.5 V to 4.2 V
- Maximum output current: 5 A
- BNC connectors for noise and PSRR measurement
- Jumper and resistor combinations select either 5.5 A or 2.5 A output current limit and commensurate monitoring or disable programmed current limit and monitoring
- Jumper turns regulator on or off
- Terminals provide output current, temperature, and output regulation status monitoring
- ▶ Jumper to margin output voltage ±2.5%
- The VIOC pin of the LT3078 manages power dissipation and PSRR
- $\blacktriangleright\,$ Banana jacks minimize V_{IN} and V_{OUT} connection voltage drops

EVALUATION BOARD PHOTOGRAPH

- VO+, VO-, and VI+ terminals for regulation and dropout monitoring
- Configurable load-transient circuit for load response testing
- Thermally enhanced, 22-lead, 3 mm × 4 mm x 0.95 mm, LQFN package

EVALUATION KIT CONTENTS

▶ EVAL-LT3078-AZ evaluation board

EQUIPMENT NEEDED

- ▶ DC power supplies
- Multimeters for voltage and current measurements
- Electronic or resistive load

DOCUMENTS NEEDED

LT3078 data sheet




Figure 1. EVAL-LT3078-AZ Evaluation Board Photograph

TABLE OF CONTENTS

Features	1
Evaluation Kit Contents	1
Equipment Needed	1
Documents Needed	1
Evaluation Board Photograph	1
General Description	3
Performance Summary	4
Quick Start Procedure	

REVISION HISTORY

10/2023—Revision 0: Initial Version

Printed Circuit Board (PCB) Layout	6
Best PSRR Performance: PCB Layout for	
Input Traces	6
PCB Layout for the C3 Output Capacitor	6
Evaluation Board Schematic	8
Ordering Information	9
Bill of Materials	

GENERAL DESCRIPTION

The EVAL-LT3078-AZ evaluation board features the LT3078, a 5 A, ultra-low noise, high power-supply rejection ratio (PSRR), 55 mV dropout ultra-fast linear regulator. The input voltage (VIN) range for the VIN power is from 0.6 V to 5.5 V. There are jumpers to set a 3-bit trilevel code that determines the output voltage (VOUT) at preprogrammed levels that range from 0.5 V to 4.2 V. The maximum output current is 5 A. The EVAL-LT3078-AZ requires an external BIAS voltage (VBIAS) that is at least 1.2 V higher than VOUT and is between 2.375 V and 5.5 V.

The LT3078 of the EVAL-LT3078-AZ requires few external components, therefore, simplifying circuit design. External component choice with careful printed circuit board (PCB) design helps to optimize noise, PSRR, load-transient response, and V_{OUT} regulation performance. The LT3078 requires capacitors for the internal reference, power input, BIASF pin, and the power output. The internal reference is bypassed with a 16 V, 0805 sized, 4.7 μ F capacitor to reduce output noise and program the soft-start. Larger capacitor case sizes and higher voltage ratings decrease 1/f noise for otherwise comparable capacitors. The 10 μ F x2 capacitor at the circuit output was chosen for high-frequency PSRR performance and to optimize VOUT response during load transients.

The capacitor that bypasses the V_{IN} power for the LT3078 and the corresponding VIN PCB layout can affect PSRR (for additional information, see the Best PSRR Performance: PCB Layout for Input Traces section). The EVAL-LT3078-AZ decouples the VIN power with a 47 μ F capacitor. Less VIN capacitance can improve PSRR at high frequencies (for the minimum capacitor value required for VIN, see the LT3078 data sheet). Note that a bulk 220 μ F tantalum polymer capacitor further reduces VIN variation during load transients and reduces input voltage ringing that can be caused by inductive input power leads. The PCB has a footprint for an optional Subminiature Version A (SMA) connector that allows a shielded VIN power connection to the PCB edge, if required.

The EVAL-LT3078-AZ bypasses the BIASF pin with a 2.2 µF capacitor instead of the VBIAS supply input. Because the BIASF pin is isolated from VBIAS by a resistance that is internal to the LT3078, there is less PSRR degradation when BIASF is bypassed compared to when VBIAS is bypassed. Otherwise, the effect on PSRR of the VIN and VBIAS bypass capacitors is similar.

The EVAL-LT3078-AZ has resistors that allow a CURRENT LIMIT jumper to select output current limits of either 2.5 A or 5.5 A. The CURRENT LIMIT jumper can also disable external current-limit programming by shorting the IMON pin to ground. An IMON terminal is available for current monitoring. The IMON voltage is the product

of the resistance that externally programs current limit and the IMON pin current that is 1/5000 of the output current. Externally programmed current limit occurs when the IMON voltage is 1 V.

A POWER jumper (JP1) is available on the EVAL-LT3078-AZ to either connect the EN pin to VBIAS to turn the output on or to ground to disable the output. A TEMP terminal is also available for die temperature monitoring. There is a PG terminal that is pulled up to VBIAS by a 51 k Ω resistor and pulled down by the open-drain, negative channel metal-oxide semiconductor (NMOS) PG pin output for indication of regulator output status and other fault modes. The voltage input-to-output control (VIOC) terminal allows connections for automatically controlling a preregulation voltage. In addition, a MARG jumper can margin the output voltage to either ±2.5%.

Banana jacks minimize voltage drops on VIN and VOUT connections. Bayonet Neill-Concelman (BNC) connectors provide low noise connections to power VIN, VBIAS, and VOUT. The EVAL-LT3078-AZ PCB design uses a split-capacitor technique to Kelvin connect the ground terminal of the REF capacitor to the ground terminal of the output capacitor, and the SENSE pin to the positive terminal of the output capacitor. The VO+, VO-, and VI+ terminals Kelvin connect to VIN and VOUT and are the optimum place to observe output voltage regulation and dropout voltage performance. There are test points for BIASF and REF voltages.

The EVAL-LT3078-AZ includes a load-transient circuit for load response testing. A 2512 size power resistor must be installed with a resistance that achieves the required transient current, but all the remaining circuit components are provided including a 10 k Ω gate pull-down resistor, a 4.7 nF Miller capacitor and a high-current NMOS. Additionally, a banana jack makes it possible to return an external DC load through the same 0.02 Ω sense resistor that is the return for the transient current so both can be monitored together.

The EVAL-LT3078-AZ has placeholders identified on the schematic as optional DNI components that make it convenient to add capacitance (for more information, see Figure 8).

Full specifications on the LT3078 are available in the LT3078 data sheet available from Analog Devices, Inc., and must be consulted with this user guide when using the EVAL-LT3078-AZ evaluation board. The LT3078 of the EVAL-LT3078-AZ features a thermally enhanced, 22-lead, 3 mm x 4 mm x 0.95 mm LQFN package. Proper board layout is essential for maximum thermal performance.

Design files are available on the EVAL-LT3078-AZ evaluation board website page.

PERFORMANCE SUMMARY

Specifications are at $T_A = 25^{\circ}$ C, unless otherwise noted.

Table 1. Performance Summary

Parameter	Symbol	Test Conditions/Comments	Min	Тур	Max	Unit
INPUT VOLTAGE	V _{IN}					
Minimum					0.6	V
Maximum		I _{OUT} = 300 mA	5.5			V
		V _{OUT} = 1.5 V, I _{OUT} = 5 A	1.9 ¹			V
BIAS VOLTAGE	V _{BIAS}					
Minimum		V _{BIAS} ≥ V _{OUT} + 1.2 V			2.375	V
Maximum			5.5			V
OUTPUT VOLTAGE	V _{OUT}	V_{OUT} = 0.5 V, 50 mA ≤ I_{OUT} ≤ 5 A, V_{IN} = 0.8 V	0.492	0.500	0.508	V
		V_{OUT} = 1.2 V, 10 mA ≤ I_{OUT} ≤ 5 A, V_{IN} = 1.5 V	1.182	1.200	1.218	V
		V_{OUT} = 3.3 V, 10 mA ≤ I_{OUT} ≤ 5 A, V_{IN} = 3.6 V	3.250	3.300	3.35	V
		V_{OUT} = 4.2 V, 10 mA ≤ I_{OUT} ≤ 5 A, V_{IN} = 4.5 V	4.137	4.200	4.263	V
OUTPUT CURRENT	IOUT					
Maximum			5			A
Minimum		V _{OUT} < 0.8 V			50	mA
		V _{OUT} ≥ 0.8 V			10	mA
Limit		IMON resistor (R_{IMON}) = 2 k Ω (2.5 A jumper position)	2.35	2.5	2.65	A
		R_{IMON} = 909 Ω (5.5 A jumper position)	5.33	5.5	5.67	A
BIAS PIN NAP MODE CURRENT	I _{BIAS}	V _{BIAS} = 5.5 V, EN = 0 V, R1 = open			10	μA
IN PIN NAP MODE CURRENT	I _{IN}	V _{IN} = 5.5 V, EN = 0 V			500	μA

¹ The maximum power dissipation and, consequently, the maximum input voltage for an output that is programmed to 1.5 V with a 5 A load is set by the 60°C temperature rise of the LT3078 on the evaluation board. Higher input voltages can be reached if larger copper area or forced-air cooling is applied. In addition, consider the effect of ambient temperature and the maximum junction temperature that may occur. For more information, see the LT3078 data sheet.

QUICK START PROCEDURE

To use the EVAL-LT3078-AZ to evaluate the performance of the LT3078, and for the proper measurement equipment setup, see Figure 2 and do the following steps:

- With the input supplies off and turned down and the load turned down, make all the connections shown in Figure 2. Ensure that the VO2, VO1, and VO0 jumpers to set VOUT are in the proper positions for the required VOUT according to the V_{OUT} selection matrix table in the LT3078 data sheet. In addition, ensure that the POWER jumper (JP1) is in the **ON** position, the CURRENT LIMIT jumper (JP5) is in the **5.5A** position, and the MARG jumper (JP6) is in the **OPEN** position.
- 2. Turn on the input and bias supplies and increase the input supply so it is at least 200 mV above the programmed output voltage. Adjust VBIAS so it is between 2.375 V and 5.5 V and at least 1.2 V higher than the programmed VOUT for proper operation. Note that when setting the input and bias voltages, a VIN or VBIAS that is too close to the programmed VOUT (too low) can cause dropout operation and a loss of VOUT regulation. Also, a VIN that is too high above the output can increase power dissipation to an unacceptable level.
- 3. Increase the load to the required IOUT. Readjust the input supply so it is still at least 200 mV above the programmed output voltage. Verify that VOUT is the expected voltage programmed by the jumpers. Note that if VOUT is lower than expected, the load may be set too high. Temporarily disconnect the load to ensure that it is not set too high.
- 4. When the proper VOUT is established, adjust the input voltages and load within the operating ranges and observe the VOUT regulation and other parameters. For load response testing details, see the next section.
- For measuring output noise and PSRR, refer to the Application Note AN-83, Performance Verification of Low Noise, Low Dropout Regulators and Application Note AN-159, Measuring 2 nV//Hz Noise and 120 dB Supply Rejection on Linear Regulators. Note that J3, J4, and J5 are BNC connectors that are used for noise and PSRR measurements.
- 6. Note that the CURRENT LIMIT jumper can additionally select a 2.5 A current limit or the INTERNAL current limit that the LT3078 provides. Monitor the output current at the IMON terminal when the 2.5 A or 5.5 A current limits are selected.
- 7. Use the MARG jumper to margin the output voltage higher or lower.
- **8.** Monitor power good and temperature at the PG and TEMP terminals, respectively.
- **9.** For the usage of the VIOC terminal, refer to the LT3078 data sheet .

The EVAL-LT3078-AZ includes a load-transient circuit for load response testing. Take the following steps to perform load response testing using the load-transient circuit.

1. Install 2512 size power resistor R4 with a resistance that achieves the required transient current. Do not exceed the surge

current rating of the resistor. Keep the resistor within its power dissipation limits by limiting the time duration that it conducts.

- 2. For the proper load response testing equipment setup, see Figure 3. Return the external DC load current to the 0.02Ω sense resistor R5 via the Q1_S banana jack so the transient current and DC load current can both be monitored together using the Q1_S and GND test points.
- 3. Drive the gate of the high-current NMOS Q1 using the Q1_G and GND test points. Usually a pulse generator with a 0 V to 5 V level output is adequate to drive the NMOS gate. The pulse generator output voltage levels, its transition times and the value of the Miller capacitor C16 all affect the load-transient current rise and fall times.




Figure 2. Proper Measurement Equipment Setup for the EVAL-LT3078-AZ




Figure 3. Proper Load Response Testing Equipment Setup for the EVAL-LT3078-AZ

PRINTED CIRCUIT BOARD (PCB) LAYOUT

BEST PSRR PERFORMANCE: PCB LAYOUT FOR INPUT TRACES

For applications using the LT3078 for post-regulating switching converters, placing a capacitor directly at the LT3078 input results in AC current (at the switching frequency) to flow near the LT3078. Without careful attention to the PCB layout, this relatively high-frequency switching current generates an electromagnetic field (EMF) that couples to the LT3078 output, degrading its effective PSRR. While highly dependent on the PCB, the switching preregulator, the input capacitor size, among other factors, the PSRR can easily degrade at high frequencies. This degradation is present even if the LT3078 is desoldered from the board because it effectively degrades the PSRR of the PCB itself. While negligible for conventional low PSRR low dropout (LDO) regulators, the high PSRR of the LT3078 requires careful attention to higher-order parasitics to realize the full performance offered by the regulator.

The EVAL-LT3078-AZ alleviates this degradation in PSRR by using a specialized layout technique. On Layer 3, the input trace (VIN) is highlighted in red (for more information, see Figure 4), with the return path (GND) highlighted on Layer 4 together with the CIN1 input capacitor (for more information, see Figure 5). When an AC voltage is applied to the input of the EVAL-LT3078-AZ, AC current flows on the path formed through CIN1 by the input and ground traces. Without the proper PCB layout, the AC current that flows on this path can generate EMFs that do not completely cancel and couple to the C3 output capacitor and related traces, which makes the PSRR appear worse than it actually is. With the input trace directly above the return path, the EMFs are in opposite directions, and consequently, cancel each other out. Ensure that these traces exactly overlap each other to maximize the cancellation effect and thus provide the maximum PSRR offered by the regulator.




Figure 4. Layer 3 of EVAL-LT3078-AZ




Figure 5. Layer 4 of EVAL-LT3078-AZ

PCB LAYOUT FOR THE C3 OUTPUT CAPACITOR

As mentioned in the General Description section, the EVAL-LT3078-AZ PCB design uses a split-capacitor technique to Kelvin connect the ground terminal of the REF capacitor to the ground terminal of the C3 output capacitor and the SENSE pin to the positive terminal of the output capacitor (for more information, see Figure 6 and Figure 7). This Kelvin connection regulates the output voltage at the output capacitor, which in turn, optimizes noise, PSRR, load transient, and regulation performance that is all measured at the output capacitor. The split-capacitor technique is useful in this case because it makes it possible to relocate the regulation point, if required. Regulation of the output voltage at a new location requires leaving the C3 output-capacitor location open and wiring the split-capacitor pads corresponding to the REF capacitor ground terminal and SENSE to the new output capacitor location. Additional capacitance located from SENSE to the REF ground between the regulation point and the LT3078 decreases stability. The split-capacitor technique itself does not enhance LT3078 stability because of the type of pass transistor, even though the unity-gain bandwidth of the LT3078 bandwidth is relatively high and close to the self-resonance frequency of the output capacitor.




Figure 6. REF Capacitor C1 and Output Capacitor C3 Connections for Best Noise, PSRR, Load Transient, and Regulation Performance

PRINTED CIRCUIT BOARD (PCB) LAYOUT




Figure 7. Split Pads for the C3 Output Capacitor on the Top Layer of EVAL-LT3078-AZ, Connect the Ground Terminal of the C1 REF Capacitor to the Ground Terminal of C3 and the SENSE Pin to the Positive Terminal of C3

EVALUATION BOARD SCHEMATIC




Figure 8. EVAL-LT3078-AZ Evaluation Board Schematic

ORDERING INFORMATION

BILL OF MATERIALS

Table 2. Bill of Materials for EVAL-LT3078-AZ

Item	Quantity ¹	Reference Designator	Part Description	Manufacturer, Part Number
Required Circuit Components				
1	1	C1	$4.7\ \mu F$ capacitor, X7R, 16 V, 10%, 0805, soft termination	Murata, GCJ21BR71C475KA01L
2	1	C2	2.2 µF capacitor, X7R, 10 V, 10%, 0603	Murata, GRM188R71A225KE15D
3	2	C3, C4	10 µF capacitors, X7S, 25 V, 10%, 1206	Murata, GCM31CC71E106KA03L
4	1	CIN1	47 µF capacitor, X5R, 10 V, 10%, 1206	Murata, GRM31CR61A476KE15L
5	1	U1	5 A, ultra-low noise, high PSRR, 55 mV dropout, ultra-fast linear regulator	Analog Devices, Inc., LT3078AV#PBF
Optional Evaluation Board Components				
1	1	C5	220 μF capacitor, tantalum polymer, 10 V, 20%, 7343, 40 m Ω ESR	AVX, TCJD227M010R0040
2		C7, C8, C9, C10, C11, C12, C14, C15, CIN2	Capacitors, 1206, optional	Optional
3		C6, C13	Capacitors, 0603, optional	Optional
4	1	C16	4700 pF capacitor, X7R, 16 V, 10%, 0603	Kemet, C0603C472K4RACTU
5	1	Q1	Transistor, N-Channel, 30 V, 75 A	Onsemi, FDMC8010
6	1	R1	51 kΩ resistor, 5%, 1/10 W, 0603, AEC- Q200	Vishay, CRCW060351K0JNEA
7	1	R2	909 Ω resistor, 1%, 1/10 W, 0603, AEC- Q200	Vishay, CRCW0603909RFKEA
8	1	R3	2 kΩ resistor, 1%, 1/10 W, 0603, AEC- Q200	Vishay, CRCW06032K00FKEA
9		R4	Resistor, 2512, optional	Optional
10	1	R5	0.02 Ω resistor, 1%, 1 W, 2010	Vishay, WSLT2010R0200FEB18
11	1	R6	10 kΩ resistor, 5%, 1/10 W, 0603	Yageo, RC0603JR-0710KL
Hardware				
1	8	E1 to E8	Test points, turret, 0.094" PBF	Mill-Max, 2501-2-00-80-00-00-07-0
2	5	J1, J2, J6, J7, J9	Connectors, banana jack, female, through-hole, non-insulated, swage, 0.218"	Keystone, 575-4
3	3	J3 to J5	Connectors, RF, BNC, receptacle, jack, 5-pin, straight, through-hole, 50 Ω	Amphenol RF, 112404
4	1	JP1	Connector, header, male, 1 x 3, 2 mm, vertical, straight, through-hole	Wurth Elecktronik, 62000311121
5	4	JP2 to JP4, JP6	Connectors, header, male, 1 x 4, 2 mm, vertical, straight, through-hole	Wurth Elecktronik, 62000411121
6	1	JP5	Connector, header, male, 2 × 3, 2 mm, vertical, straight, through-hole	Wurth Elecktronik, 62000621121
7	4	MP1 to MP4	Standoffs, nylon, snap-on, 1/2 inch	Wurth Elecktronik, 702935000
8	6	XJP1 to XJP6	Connector shunt, female, 2-position, 2 mm	Wurth Elecktronik, 60800213421

¹ Blank cell is for optional components.

NOTES



ESD Caution

ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

Legal Terms and Conditions

By using the evaluation board discussed herein (together with any tools, components documentation or support materials, the "Evaluation Board"), you are agreeing to be bound by the terms and conditions set forth below ("Agreement") unless you have purchased the Evaluation Board, in which case the Analog Devices Standard Terms and Conditions of Sale shall govern. Do not use the Evaluation Board until you have read and agreed to the Agreement. Your use of the Evaluation Board shall signify your acceptance of the Agreement. This Agreement is made by and between you ("Customer") and Analog Devices, Inc. ("ADI"), with its principal place of business at Subject to the terms and conditions of the Agreement, ADI hereby grants to Customer a free, limited, personal, temporary, non-exclusive, non-sublicensable, non-transferable license to use the Evaluation Board FOR EVALUATION PURPOSES ONLY. Customer understands and agrees that the Evaluation Board is provided for the sole and exclusive purpose referenced above, and agrees not to use the Evaluation Board for any other purpose. Furthermore, the license granted is expressly made subject to the following additional limitations: Customer shall not (i) rent, lease, display, sell, transfer, assign, sublicense, or distribute the Evaluation Board; and (ii) permit any Third Party to access the Evaluation Board. As used herein, the term "Third Party" includes any entity other than ADI, Customer, their employees, affiliates and in-house consultants. The Evaluation Board is NOT sold to Customer; all rights not expressly granted herein, including ownership of the Evaluation Board, are reserved by ADI. CONFIDENTIALITY. This Agreement and the Evaluation Board shall all be considered the confidential and proprietary information of ADI. Customer may not disclose or transfer any portion of the Evaluation Board to any other party for any reason. Upon discontinuation of use of the Evaluation Board or termination of this Agreement, Customer agrees to promptly return the Evaluation Board to ADI. ADDITIONAL RESTRICTIONS. Customer may not disassemble, decompile or reverse engineer chips on the Evaluation Board. Customer shall inform ADI of any occurred damages or any modifications or alterations it makes to the Evaluation Board, including but not limited to soldering or any other activity that affects the material content of the Evaluation Board. Modifications to the Evaluation Board must comply with applicable law, including but not limited to the RoHS Directive. TERMINATION. ADI may terminate this Agreement at any time upon giving written notice to Customer. Customer agrees to return to ADI the Evaluation Board at that time. LIMITATION OF LIABILITY. THE EVALUATION BOARD PROVIDED HEREUNDER IS PROVIDED "AS IS" AND ADI MAKES NO WARRANTIES OR REPRESENTATIONS OF ANY KIND WITH RESPECT TO IT. ADI SPECIFICALLY DISCLAIMS ANY REPRESENTATIONS, ENDORSEMENTS, GUARANTEES, OR WARRANTIES, EXPRESS OR IMPLIED, RELATED TO THE EVALUATION BOARD INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, TITLE, FITNESS FOR A PARTICULAR PURPOSE OR NONINFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS. IN NO EVENT WILL ADI AND ITS LICENSORS BE LIABLE FOR ANY INCIDENTAL, SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES RESULTING FROM CUSTOMER'S POSSESSION OR USE OF THE EVALUATION BOARD, INCLUDING BUT NOT LIMITED TO LOST PROFITS, DELAY COSTS, LABOR COSTS OR LOSS OF GOODWILL. ADI'S TOTAL LIABILITY FROM ANY AND ALL CAUSES SHALL BE LIMITED TO THE AMOUNT OF ONE HUNDRED US DOLLARS (\$100.00). EXPORT. Customer agrees that it will not directly or indirectly export the Evaluation Board to another country, and that it will comply with all applicable United States federal laws and regulations relating to exports. GOVERNING LAW. This Agreement shall be governed by and construed in accordance with the substantive laws of the Commonwealth of Massachusetts (excluding conflict of law rules). Any legal action regarding this Agreement will be heard in the state or federal courts having jurisdiction in Suffolk County, Massachusetts, and Customer hereby submits to the personal jurisdiction and venue of such courts. The United Nations Convention on Contracts for the International Sale of Goods shall not apply to this Agreement and is expressly disclaimed.



©2023 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. One Analog Way, Wilmington, MA 01887-2356, U.S.A.