



### CHTA/CHTB24

High Temperature 150°C Series

25Amp - 400/600/800V - TRIAC

#### Applications

- Heat Regulation
  - Ovens
  - Coffee Makers
  - Cookers
- Light Dimming
- Control of Inductive Loads
  - Motors
  - Transformers

- > Superior Commutating Performance at High Temperature  $(di/dt)_c = 25A/ms$  @  $(dv/dt)_c = 50V/\mu s$
- > Ideal for Most Demanding Applications
- > Alternistor/No Snubber Type
- > IGT 50 mA Max.
- > VDRM/VRMM 400, 600, 800V

#### Absolute Maximum Ratings

	CONDITIONS	SYMBOL	RATING
RMS On-State Current (full sine wave)	$T_c = 125^\circ C$ $T_c = 100^\circ C$	TO-220AB TO-220AB Iso $I_{T(RMS)}$	25A
Non Repetitive Surge Peak On-State Current (Full Cycle, $T_j$ Initial = $25^\circ C$ )	F = 50 Hz F = 60 Hz	$I_{TSM}$	285A 300A
$I^2t$ Value for fusing	$t_p = 10$ ms	$I^2t$	400A <sup>2</sup> s
Critical rate of rise of on-state current $I_G = 2 \times I_{GT}$ , $t_r < 100$ ns, $T_j = 150^\circ C$		di/dt	100A/ $\mu s$
Peak Gate Current @ $T_j = 150^\circ C$	$t_p = 20$ $\mu s$	$I_{GM}$	4A
Average Gate Power Dissipation @ $T_j = 150^\circ C$		PG(AV)	1W
Storage Temperature Range		$T_{stg}$	-40 to +150°C
Operating Junction Temperature Range		$T_j$	-40 to +150°C
Isolation Voltage (CHTA Series only)		$V_{ISO}$	2500 $V_{RMS}$

#### Electrical Characteristics


$I_{GT}$ MAX @ $V_D = 12$ V, $R_L = 33\Omega$ <sup>NOTE 1</sup>	QI-II-III	50mA
$V_{GT}$ MAX @ $V_D = 12$ V, $R_L = 33\Omega$	QI-II-III	1.3V
$V_{GD}$ MIN @ $V_D = V_{DRM}$ , $R_L = 3.3k\Omega$ $T_j = 150^\circ C$	QI-II-III	0.15V
$I_H$ MAX @ $I_T = 500$ mA <sup>NOTE 2</sup>		75mA
$I_L$ MAX @ $I_G = 1.2 I_{GT}$	QI-II-III	90mA
dv/dt MIN @ $V_D = 67\% V_{DRM}$ (gate open) <sup>NOTE 2</sup> $T_j = 150^\circ C$		500V/ $\mu s$
(di/dt) <sub>c</sub> MIN without snubber <sup>NOTES 2 &amp; 4</sup> $T_j = 150^\circ C$		25A/ms

#### Static Characteristics


$V_T$ MAX @ $I_{TM} = 35A$ , $t_p = 380\mu s$ <sup>NOTE 2</sup> $T_j = 25^\circ C$		1.5V
$V_{to}$ MAX @ Threshold Voltage <sup>NOTE 2</sup> $T_j = 150^\circ C$		0.8V
$R_d$ MAX @ Dynamic Resistance <sup>NOTE 2</sup> $T_j = 150^\circ C$		19m $\Omega$
$I_{DRM}$ MAX @ $V_{DRM} = V_{RRM}$ $T_j = 25^\circ C$		5 $\mu A$
$I_{RRM}$ MAX @ $V_{DRM} = V_{RRM}$ $T_j = 150^\circ C$		8.5mA

#### GENERAL NOTES

1. Minimum IGT is guaranteed at 5% of IGT max.
2. For both polarities of A2 referenced to A1
3. All parameters at 25 degrees C unless otherwise specified.
4. Commutating dv/dt = 50V/ $\mu s$ , (exponential to 200Vpk)



TO-220AB Isolated (CHTA24)




TO-220AB Non-Isolated (CHTB24)




### Thermal Resistances

		SYMBOL	RATING
Junction to Case (AC)	TO-220AB	$R_{th(j-c)}$	0.8°C/W
Junction to Case (AC)	TO-220AB Isolated	$R_{th(j-c)}$	1.7°C/W
Junction to Ambient	TO-220AB	$R_{th(j-a)}$	60°C/W
Junction to Ambient	TO-220AB Isolated	$R_{th(j-a)}$	60°C/W

### Part Number Designation



Weight: 2.3g (0.08 oz)



### Dimensions

REF.	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	15.24		15.75	0.6		0.62
B		3.23			0.127	
C	12.78		13.79	0.503		0.543
D	9.96		10.36	0.392		0.408
E	0.69		0.94	0.027		0.037
F	1.22		1.32	0.048		0.052
G	4.62		4.83	0.182		0.19
H	0.46		0.61	0.018		0.024
I	2.49		2.84	0.098		0.112
J	2.39		2.69	0.094		0.106
K	6.48		6.88	0.255		0.271
L	3.78		3.89	0.149		0.153
M	15.49	16	16.51	0.61	0.63	0.65
N	2.59		2.9	0.102		0.114
O	0.99		1.55	0.039		0.061
P	0.99		1.55	0.039		0.061
Q		2.67			0.105	




Fig. 1: Power dissipation versus RMS on-state current (full cycle).




Fig. 2: RMS on-state current versus case temperature (full cycle)




Fig. 3: On-state current versus on-state voltage (instantaneous values)




Fig. 4: Non-repetitive surge peak on-state current versus number of cycles.

### ISO9001 Certified

### Approvals

UL - Pending

### USA

Sales Support (877) 502-5500

Tech Support (877) 702-7700

Fax (619) 710-8540

Email: sales@crydom.com

Crydom Corp

2320 Paseo de las Americas, Suite 201

San Diego, CA 92154

### EUROPE - UK

Telephone +44 (0) 1202 365070

Fax +44 (0) 1202 365090

Email: intsales@crydom.com

Crydom International Ltd.

7 Cobham Road

Ferndown Industrial Estate

Wimborne, Dorset BH21 7PE

### Germany

Telephone +49 (0) 180 3000 506

### ASIA - Thailand

Telephone +66 (0)2 665 2517

Fax +66 (0)2 665 2588

Crydom Asia

18/8 Fico Place 12th Floor

Soi Sukhumvit 21 (Asoke)

Klongtoey Nua, Wattana

Bangkok, Thailand 10110