

Insulated enclosure, HxWxD=120x80x95mm, +mounting rail

Part no. CI-K1-95-TS
206881

EL Number (Norway) 4138000

General specifications		
Product name		Eaton Moeller® series CI-K Insulated enclosure
Part no.		CI-K1-95-TS
EAN		4015082068813
Product Length/Depth		137 millimetre
Product height		95 millimetre
Product width		80 millimetre
Product weight		0.178 kilogram
Certifications		UL94: HB UL94: V0/1.5 mm thickness IEC 60068-2-11 DIN EN 62208 IEC/EN 60529
Product Tradename		CI-K
Product Type		Insulated enclosure
Product Sub Type		None
Catalog Notes		Lamp indicator L-... can be mounted in base knock-out M20/M25
Features & Functions		
Enclosure color		Light gray, Operator (RAL 7035) Black (RAL 9005) Light gray, Cover (RAL 7035)
Enclosure material		1 Ω x 10 ¹³ (Surface resistance to IEC 60093) Plastic
Features		UV resistance beneath protective shield Halogen free
Fitted with:		Push-through cable entry diaphragm Mounting rail to IEC/EN 60715
Knockouts		Push-through cable entry diaphragm Metric cable entry knockouts at the top, bottom and back plate
General information		
Cover material		Glass-fiber reinforced polycarbonate
Degree of protection		IP65 NEMA Other
Degree of protection (front side)		IP65
Dielectric strength		30 kV/mm, according to IEC 60243-1
Flammability characteristics		960 °C/1 mm thickness (base, cover; glow wire to VDE 0471 Part 2) 650 °C/1 mm thick (push-through membrane and seal material) to VDE 0471 Part 2)
Model		Surface mounting
Mounting depth		72 mm
Mounting weight capacity - max		0.5 kg
Product category		Empty enclosures
Suitable for		Emergency stop
Surface treatment		Resistant to corrosion
Track resistance		CTI 175 (base, to IEC 60112) CTI 175 (cover, to IEC 60112)
Type		Basic enclosure
Water consumption		0.29 % (According to DIN EN ISO 62)
Ambient conditions, mechanical		
Environmental resistance		Resistant against alkalis Partly resistant to greases Resistant against salt solutions Chemical resistant (Push-through membrane (CI-K1/CI-K2) and sealing material) Not resistant to benzene Partly resistant to acids (> 10%) Resistant against mineral oil Partly resistant to benzene

			Resistant against acids (< 10%) Not resistant to alkalis Partly resistant to alcohol Resistant against alcohol Resistant against benzene Resistant against gasoline Not resistant to Mineral oil Resistant against greases Chemical resistant (Base, Cover)
Impact resistance			IK04 (according to EN 50102)
Temperature resistance			-40 - 80 °C (gasket) -40 - 120 °C (enclosure)
Climatic environmental conditions			
Ambient operating temperature - min			-25 °C
Ambient operating temperature - max			70 °C
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Design verification			
Equipment heat dissipation, current-dependent P _{vid}			0 W
Radiated heat dissipation with separate mounting			10 W (at an ambient temperature of 20 °C)
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Please enquire
10.2.5 Lifting			Not applicable.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of assemblies			Meets the product standard's requirements.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Meets the product standard's requirements.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Empty enclosure for switchgear (EC000712)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Empty housing for switch devices (ec1@ss10.0.1-27-37-13-01 [AKN343014])			
Material housing			Plastic
Width		mm	80
Height		mm	95
Depth		mm	137
With transparent cover			No
Suitable for emergency stop			Yes
Model			Surface mounting
Degree of protection (IP)			IP65
Degree of protection (NEMA)			Other