



# RFID/NFC COIL ANT, SMT, 13.56MHZ

Part Number: L000641-01

**L000641-01** is an SMT mount NFC (Near Field Communications) antenna designed for high-performance two-way read/write operations at 13.56MHz.

One of the smallest NFC antennas on the market, that takes only 20% of the PCB size compared with antennas routed on the PCB, but still performing about 35mm as reading distance. The unique size and SMT mounting makes this antenna the perfect choice for space-constrained applications.

#### **FEATURES & BENEFITS**

- Frequency 13.56MHz
- Universal antenna module assembly
- Antenna type Coil on ferrite core for increased performance
- Higher reading distance than competition
- Fully Pick & Place and SMT capable


### **SPECIFICATIONS**

Frequency Range	13.56 MHz	
Self inductance (La)	4.7 uH	
DCR	0.25 Ohm	
Read Distance	35 mm	
Size	7.8 mm x 7 mm x 5 mm	
Weight	0.85g	
Mounting	Surface mount	
Operating Temperature	-40 to +85°C	
Storage Temperature	-40 to +85°C	
Hazardous Materials	A certificate of conformance is available from the product page on TE website.	




# **TEST SETUP**


#### EVB MB1414 board






# **DIMENSIONS**






top view



## **FOOTPRINT**



Marking shall be start from electrode side.

Marking color : Black

Dimensions: mm Diagram is not to scale




## **REFLOW SOLDERING TEMPERATURE**

Phase	Profile Features	Pb-Free Assembly (SnAgCu)
PREHEAT	<ul><li>Temperature Min (Tsmin)</li><li>Temperature Max (Tsmax)</li><li>Time (Ts) from (Tsmin to Tsmax)</li></ul>	150°C 200°C 60-120 seconds
RAMP-UP	Avg. Ramp-Up Rate (Tsmax to TP)	3°C / second (max)
REFLOW	<ul><li>Temperature (TL)</li><li>Total Time above TL (t L)</li></ul>	217°C 60-150 seconds
PEAK	<ul><li>Temperature (TP)</li><li>Time (tp)</li></ul>	260°C 20-30 seconds
RAMP-DOWN	Rate	6°C / second max
Time from 25°C to Peak Temperature		8 minutes max
Composition of solder paste		96.5Sn/3Ag/0.5Cu
Solder paste model		SHENMAO PF606-P26


Note: All temperature measure points are on the top surface of the component, if the temperature exceeds recommended levels, it can cause damage to the component or the surface to peel.


The graphic shows temperature profile for component assembly process in reflow ovens






## **PACKAGING**





<sup>\*</sup>Tape and reel packing with plastic bag.

<sup>\*1000</sup> pcs/ Reel



350mm 350mm

2 reels in one inner box = 2000 pcs

2 inner boxes in one outer box = 4000 pcs

#### RFID/NFC COIL ANT, SMT, 13.56MHZ

Standard Antenna Solutions



#### TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 +49 (0) 6251-133-1999 Germany: +44 (0) 800-267666 UK: France: +33 (0) 1-3420-8686 Netherlands: +31 (0) 73-6246-999 +86 (0) 400-820-6015 China:

For phone numbers in other countries, go to te.com/support-center

#### te.com

TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2023 TE Connectivity Ltd. family of companies All Rights Reserved.

08/2023