AMP | AMP CPC

TE Internal #: 182658-1

Cable Clamp Kit, Thermoplastic, Black, Shell Size 11, .329 in [8.3

mm] Cable Entry, UL 94V-0, AMP CPC

View on TE.com >



Connectors > Connector Accessories > Connector Strain Relief > CPC Cable Clamps, Available in EMEA











Strain Relief Accessory Type: Cable Clamp Kit

Primary Product Material: Thermoplastic

Primary Product Color: Black

Compatible With Connector Shell Size: 11
Cable Entry Diameter: 8.3 mm [.329 in]

All CPC Cable Clamps, Available in EMEA (5)

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
Body Features	
Primary Product Material	Thermoplastic
Primary Product Color	Black
Mechanical Attachment	
Thread Size	5/8-24 UNEF-2B
Housing Features	
Compatible With Connector Shape	Circular
Body Orientation	Straight
Dimensions	
Cable Entry Diameter	8.3 mm[.329 in]

Operation/Application



Compatible With Connector Shell Size	11
Shielded	No
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Individual
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





Also in the Series | AMP CPC



Circular Power Connectors(458)



Connector Backshells(2)



Connector Caps & Covers(16)



Connector Contacts(6)



Connector Hardware(12)



Connector Seals & Cavity Plugs(36)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)



Customers Also Bought

















Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_182658-1_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_182658-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_182658-1_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English