

Part Number: 733910070

Product Description: 50 Ohms, SMA PCB Jack Receptacle, Vertical, with Standoffs, 80 Pieces

Per Tray

Series Number: 73391

Status: Active

Product Category : RF / Coaxial Connectors



#### **Documents & Resources**

### **Drawings**

Drawing 733910070\_sd.pdf

**3D Models and Design Files**3D Model 733910070\_stp.zip

### **Product Environment Compliance**

#### Compliance

| GADSL/IMDS         | Not Relevant                                     |
|--------------------|--|
| China RoHS         | <b>®</b>   |
| EU ELV             | Not Relevant                                     |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                   |
| REACH SVHC         | Contains Lead per D(2023)3788-DC (14 Jun 2023)   |
| EU RoHS            | Compliant with Exemption 6(c) per<br>EU 2015/863 |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## **Part Details**

### General

| Status         | Active   |
|----------------|--|
| Category       | RF / Coaxial Connectors  |
| Series         | 73391  |
| Description    | 50 Ohms, SMA PCB Jack Receptacle,<br>Vertical, with Standoffs, 80 Pieces<br>Per Tray |
| Product Family | SMA RF Connectors  |
| Product Name   | SMA  |
| Style          | РСВ  |
| Туре           | Subminiature   |
| UPC            | 800753926158   |

### Electrical

| Frequency       | 18 GHz                      |
|-----------------|-----------------------------|
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 500 Vrms@Sea Level |

# Physical

| Gender                      | Jack         |
|-----------------------------|--------------|
| Keying to Mating Part       | None         |
| Net Weight                  | 1.474/g      |
| Orientation                 | Straight     |
| Packaging Type              | Tray         |
| Panel Mount                 | No           |
| Panel Mount Method          | N/A          |
| PCB Mounting                | Through Hole |
| PCB Thickness - Recommended | 3.00mm       |
| Reverse Polar               | No           |
| Wire/Cable Type             | N/A          |

## Solder Process Data

| Max-Duration                 | 10       |
|------------------------------|----------|
| Lead-Free Process Capability | SMC&WAVE |
| Max-Cycle                    | 2        |
| Max-Temp                     | 260      |

This document was generated on Jan 23, 2024