

# Product data sheet

Specifications



## CONTROL STATION 600VAC 5A T-B FORWARD REVERSE

9001BG206

Product availability : Stock - Normally stocked in distribution facility

### Main

Range of Product	Harmony 9001B
Product or Component Type	Complete control station
Device short name	9001BG

### Complementary

Control station composition	2 push-buttons FORWARD-REVERSE
Contacts type and composition	2 NO
Connections - terminals	Screw clamp terminal
[Ie] rated operational current	5 A 600 V
Device mounting	Surface
Type of Installation	Indoor

### Environment

NEMA degree of protection	NEMA 1
Product Certifications	UL listed file E42259 CCN NKCR CSA LR25490 class 3211 03 CE
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	21421-9001 B (NOT BW70 - BW80)
Discount Schedule	CS1
GTIN	785901794172
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)

Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	9.44 oz (267.62 g)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------

**9001BG206**

The image contains four technical drawings of the 1000 Series 1/2-3/4 Condenser Unit, showing front, side, and top views with dimensions in inches and millimeters.

**Top View (Top Left):** Shows the unit from above. Dimensions include a width of 2.06 (52) inches, a mounting hole diameter of 0.19 (5) inches, and a distance of 0.47 (12) inches from the top edge to the center of the mounting holes. The distance between the centers of the mounting holes is 2.76 (70) inches. The distance from the center of the mounting holes to the center of the condenser coil is 3.69 (94) inches. The distance from the center of the condenser coil to the center of the fan is 0.72 (18) inches. The distance from the center of the fan to the center of the condenser coil is 1.38 (35) inches. The distance from the center of the condenser coil to the center of the fan is 0.48 (12) inches. The distance from the center of the fan to the center of the condenser coil is 0.34 (9) inches.

**Side View (Top Right):** Shows the unit from the side. Dimensions include a height of 4.45 (113) inches, a distance of 0.45 (12) inches from the top edge to the center of the mounting holes, a distance of 4.09 (104) inches from the center of the mounting holes to the center of the condenser coil, and a distance of 5.00 (127) inches from the center of the condenser coil to the center of the fan. The distance from the center of the fan to the center of the condenser coil is 0.72 (16) inches. The distance from the center of the condenser coil to the center of the fan is 1.38 (35) inches. The distance from the center of the fan to the center of the condenser coil is 0.48 (12) inches. The distance from the center of the condenser coil to the center of the fan is 0.34 (9) inches.

**Front View (Bottom Left):** Shows the unit from the front. Dimensions include a width of 2.06 (52) inches, a mounting hole diameter of 0.19 (5) inches, and a distance of 0.17 (4) inches from the top edge to the center of the mounting holes. The distance between the centers of the mounting holes is 2.53 (64) inches. The distance from the center of the mounting holes to the center of the condenser coil is 0.88 (22) inches. The distance from the center of the condenser coil to the center of the fan is 0.72 (18) inches. The distance from the center of the fan to the center of the condenser coil is 1.38 (35) inches. The distance from the center of the condenser coil to the center of the fan is 0.48 (12) inches. The distance from the center of the fan to the center of the condenser coil is 0.34 (9) inches.

**Front View (Bottom Right):** Shows the unit from the front. Dimensions include a width of 2.06 (52) inches, a mounting hole diameter of 0.19 (5) inches, and a distance of 0.17 (4) inches from the top edge to the center of the mounting holes. The distance between the centers of the mounting holes is 2.53 (64) inches. The distance from the center of the mounting holes to the center of the condenser coil is 0.88 (22) inches. The distance from the center of the condenser coil to the center of the fan is 0.72 (18) inches. The distance from the center of the fan to the center of the condenser coil is 1.38 (35) inches. The distance from the center of the condenser coil to the center of the fan is 0.48 (12) inches. The distance from the center of the fan to the center of the condenser coil is 0.34 (9) inches.