Enabling the Electronics Revolution

PS2P-CON

Touchless Concentric Rotary Hall-Effect Position Sensor



KEY FEATURES



True touchless operation

Without any internal or external gears or linkages the sensor is easily assembled and calibrated and free from wear and tear over lifetime.



Unlimited mechanical life

The separation of electronics and magnet module allows for a virtually unlimited lifetime independent of number of revolutions.



Made for harsh environments

IP69K sealing, high operating temperature range as well as shock and vibration resistance allow the use in the most demanding environments.



Compact and low profile package

Without the need for a shaft the sensor is provided in a exceptionally compact and low profile package that fits in space contraint applications.



Adaptable to your requirements

Custom mechanical design, programmable transfer function and switch outputs as well as different output protocols and redundancy levels available.

DESCRIPTION

Piher Sensing Systems' PS2P-CON rotary position sensor delivers true touchless sensing for harsh industrial and vehicle environments in a low profile and robust magnetic design.

Magnet and sensor module are placed in separate housings without the need for any gears, bearings or linkages and can be placed anywhere on the pivoting shaft. This allows for easy mounting, thereby delivering additional cost reduction on the production line. Furthermore, without wear and tear of radial forces product reliability and lifetime are increased significantly.

The PS2P-CON measures changes in angular position relative to the sensor by detecting the movement of a diametrically magnetized magnet that is located in a separate housing and is only sensitive to the flux density co-planar with the IC surface.

The PS2P series is complemented by touchless linear (PS2P-LIN) and variable air gap arc (PS2P-ARC) position sensors. All sensors of the series are absolute sensors and will deliver the same level of precision and stability throughout their lifetime as on the first day they are installed - despite extremes of vibration, shock, temperature and contamination.

APPLICATIONS

Off-Highway

- Bucket position
- ▶ Pedal / throttle position
- ► Hitch position
- Bus suspension / kneeling position
- Transmission systems

Automotive

- Gear selector
- Transmission systems

Home & Building Automation

- ► HVAC damper actuator monitoring Marine
- ► Trim / tilt position

Industrial

- ▶ Robotic / hydraulic arm position
- ► Valve monitoring
- ▶ IoT modules
- ► Vacuum circuit breaker monitoring

Amphenol Sensors

Touchless Concentric Rotary Hall-Effect Position Sensor

MECHANICAL SPECIFICATIONS					
	With magnet M001	With magnet M006			
Life	Virtually unlimited				
Nominal air gap	3mm, between plastic parts	1mm, between plastic parts			
Maximum air gap	5mm, higher on request	1.5mm, higher on request			
Maximum allowed radial offset	um allowed radial offset ±3mm Contact Piher Sensing Systems				

ELECTRICAL SPECIFICATIONS Linearity¹ ±1% absolute (±0.5% upon request) Angular range Programmable from 15 to 360 degrees Analog (Ratiometric), PWM, CAN Open, CAN SAE J1939 Output protocol Serial Protocol (SPI) upon request Simple Output Redundant Full-redundant On request Switch Output Analog, PWM, CAN Up to 12 bit Resolution SPI Up to 14 bit 5V ±10% Analog and PWM 7V to 15V Supply voltage² CAN 7V to 32V Typ 8.5 mA Single version Supply current Redundant version Typ 17 mA CAN version Typ 47 mA Voltage protection ±10V Self-diagnostic features Yes

¹ Ferromagnetic materials close to the sensor (i.e. shaft, mounting surface) may affect the sensor's linearity. ² Voltages up to 25V possible on request.

ENVIRONMENTAL SPECIFICATIONS

-40° to +125°C
50g
5Hz to 2000 Hz; 20g; A _{max} 0,75 mm
IP67, IP69К
CE ²


¹Other specifications available ²CE-approval applies to analogic models with M001 magnet

EMI/EMC Testing					
Characteristic	Standard	Level			
Radiated emissions	CISPR 16-2-3 class B	30 MHz to 230 MHz, max. 30dB (μV/m) 230 MHz to 1000 MHz, max. 37dB (μV/m)			
ESD on housing and connections	EN 61000-4-2:2009	±4 kV contact ±8 kV air			
Burst (on supply lines / signal lines)	EN 61000-4-4:2012	±1kV			
Surge (on supply lines / signal lines)	EN 61000-4-5:2014	±1kV			
Immunity HF radiated (80 2000 MHz)	EN 61000-4-3:2006	10 V/m			
Immunity HF conducted (0,15 80MHz)	EN 61000-4-6:2014	10 Vemk			
Immunity magnetic field (50 Hz)	EN 61000-4-8:2010	30 A/m			

PIHER sensing systems


Page 2 of 5 **Amphenol Sensors**

Touchless Concentric Rotary Hall-Effect Position Sensor



Magnet shown on 0° position. Drawings may not be to scale. Number and function of wires pictured in this datasheet may vary according to output configuration.

Touchless Concentric Rotary Hall-Effect Position Sensor




1 The analog output is ratiometric, proportional: - for supply voltage "5V" to input voltage; - for supply voltage "RE" to 5V.

2 Other output functions available, please check availability. Enter CXXXX as long as the new output function is not defined.

3 Models with ERA < 40° available on request

4 Voltages up to 25V possible on request 5 Leave empty if not applicable. Default frequency is 200 Hz


OUTPUT FUNCTIONS




Custom output functions on request.

Touchless Concentric Rotary Hall-Effect Position Sensor

OUTPUT VOLTAGE DEPENDING ON MAGNET POSITION PS2P-CON-CE-M006-1A0-C0000-ERA360-05 CW 90%





Custom output functions with up to 4 programmable points on request.

CONNECTION SCHEME

Color	Simple Redundant			Full-redundant	CAN	
	5V	7V to 15V	5V	7V to 15V	<u> </u>	<u> </u>
Brown	Power supply	Power supply	Power supply	Power supply	Power supply 1	Power supply
Blue	Ground	Ground	Ground	Ground	Ground 1	Ground
Black	Signal output	Signal output	Signal output 1	Signal output 1	Ground 2	CAN High
White	n/a	n/a	Signal output 2	Signal output 2	Signal output 2	CAN Low
Red	n/a	n/a	n/a	n/a	Power supply 2	n/a
Yellow	n/a	n/a	n/a	n/a	Signal output 1	n/a
Grey	n/a	Not used	n/a	Not used	n/a	n/a

More instructions of use on www.piher.net. Connector assembly available on request







Please always use the latest updated datasheets and 3D models published on our website.

Disclaimer

Uscanner: The product information in this catalog is for reference purposes. Please consult for the most up to date and accurate design information. Piher Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Piher"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein. Piher disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which are high the there conducts.

by law. The product specifications do not expand or otherwise modify Priner's terms and conducts or sate, including both to state and a poly to the seprenducts. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Priner. The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Priher products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Priher for any damages arising or resulting from such use or sale. Please contact authorized Priher personnel to obtain written terms and conditions regarding products designed for such applications. Product marks and markings noted herein may be trademarks of their respective owners. Information contained in and/or attached to this catalog may be subject to export contained in this document complies with all relevant export control regulations. If you are in any doubt about the export chart interplication apply to this information, please contact the sender immediately. For any Priher Exports, Note: All products / technologies are EAR99 Classified commodities. Exports from the United States are in accordance with the Export Administration Regulations. Diversion contrary to US law is prohibited. ation





CONTACT

Piher Sensing Systems Polígono Industrial Municipal Vial T2, N°22 31500 Tudela Spain

sales@piher.net

Europe:	+34 948 820 450
Americas:	+1 636 251 0855
Asia Pacific:	+65 9641 8886

Page 5 of 5 **Amphenol Sensors**