

Product data sheet

Specifications



Contact block, Harmony XAC, single contact, spring return, emergency stop push button, 3NO

XENT1991

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XAC
Product or Component Type	Contact block
Component name	XENT
Electrical circuit type	Control circuit Power circuit
Contact block application	Emergency stop push-button
Contact block type	Single
Type of operator	Spring return
Product Compatibility	XACD
Contacts type and composition	3 NC
Contact operation	Slow-break

Complementary

Connections - terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Mechanical durability	3000000 cycles
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	400 V 3)IEC 60947-1
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1
Short-circuit protection	6 A fuse protection cartridge aM
Rated operational power in W	3000 W AC-23B 400 V
Terminals description ISO n°1	(31-32)NC (11-12)NC (21-22)NC
Net Weight	0.09 lb(US) (0.04 kg)

Environment

Standards	EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14
-----------	---

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	70 gn IEC 60068-2-27
Overvoltage category	Class II IEC 61140

Ordering and shipping details

Category	22466-PUSHBUTTON, ACCESSORIES
Discount Schedule	CS2
GTIN	3389110609103
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.42 in (3.6 cm)
Package 1 Width	2.09 in (5.3 cm)
Package 1 Length	2.32 in (5.9 cm)
Package 1 Weight	1.48 oz (42.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	30
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.22 lb(US) (1.462 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)