1650 Series Multifunction Installation Testers





Fluke 1653



Fluke 1652



Fluke 1651







BS7671 16th Edition IEE Wiring Regulations IEC 60364.6.61, HD 384

Included Accessories

TP165X Remote Control Probe
TL165X STD Standard Test Lead Set
C1600 Hard Carrying Case
Mains Test Cord
Padded Carrying Strap
Quick Reference Guide
6 AA Cell batteries

Ordering Information

Fluke 1651 Multifunction Installation Tester Fluke 1652 Multifunction Installation Tester Fluke 1653 Multifunction Installation Tester

The future of installation testing is here

The Fluke 1650 Series testers verify the safety of electrical installations in domestic, commercial and industrial applications. They can ensure that fixed wiring is safe and correctly installed to meet the requirements of IEC 60364,

HD 384 and all relevant local standards. The unique ergonomic design, low weight and padded neck-strap to free your hands, make operating a Fluke 1650 multifuction tester a pleasure. With easy-to-operate controls and large display with exceptionally wide viewing angle, it's also comfortable and safe to use.

• Easy: simply turn the knob, press the button and see the results

- Efficient: measure loop impedance without tripping RCDs, eliminating the need to bypass them
- Rugged: withstands a one-meter drop for demanding field use
- Safe: slim probe with test button keeps your eyes on the panel while probing hard to reach points
- Comfortable: compact and lightweight (less than 1.2 kg) for all day testing
- Compliant: meets all relevant standards including EN 61557 and VDE 0413

Rotary knob labeling is available in six versions. Select from English, French, German, Italian, Spanish or a user-friendly Symbols version.

Features

Measurement functions	1651	1652	1653
Voltage & Frequency	•	•	•
Wiring polarity	•	•	•
Insulation Resistance	500, 1000 V	250, 500, 1000 V	50, 100, 250 500, 1000 V
Continuity	•	•	•
Loop & Line Resistance	•	•	•
PFC/PSC (short-circuit current)	•	•	•
RCD tripping time	•	•	•
RCD tripping current level		ramp test	ramp test
Automatic RCD test sequence		•	•
Test of pulse sensitive RCD's		•	•
Earth Resistance			•
Phase Sequence Indicator			•
Other features			
Self-test	•	•	•
EN 61557*/VDE 0413 compliant	•	•	•
Illuminated Display	•	•	•
Line voltage indicator	•	•	•
Battery indicator and battery test function	•	•	•
Memory, Interface			
Memory (500 measurements)			•
Computer interface			•
Time stamp (with FlukeView® Forms)			•
Software			option

* 1651: sections 1, 2, 3, 4, 6, 10 1652: sections 1, 2, 3, 4, 6, 10 1653: sections 1, 2, 3, 4, 5, 6, 7, 10

Recommended Accessories







MTC77 (Europe) Mains Test Cord



ES165X (1653) Earth Spike Test Kit



FVF-SC2 (1653)

1650 Series Multifunction Installation Testers

FLUKE ®

The future of installation testing is here

Specifications



Slim probe design

Thanks to its slim probe with integral test button, you can safely make one-handed measurements on hard to reach points, while keeping your eyes on the panel.



Professional reports

Up to 500 test results can be stored in the 1653 installation tester. The data stored for each measurement consists of the test function, user selectable test conditions and unique references. Model 1653 has an IR port and adaptor to enable the results to be uploaded to a computer for preparing professional reports using (optional) FlukeView® Forms software.



Complete kit

All 1650 models are equipped with detachable leads that can be replaced in case of damage or loss. A durable hard case will protect your instrument in tough field conditions. A probe with built-in test button comes with every instrument.

								•	
AC Voltage Measure	ement								
Range	Resolu	tion	Accuracy		Input 1	Impedar	ıce	0v	erload Protection
			50 Hz - 60 Hz						
500 V	0.1	V	0.8% + 3		3.3 MΩ			660 Vrms	
Continuity Testing									
Range (autoranging	_		Test Currer	nt	Open Circuit Voltage		Accuracy		
20 Ω	0.01	Ω			> 4 V		± (1.5%+3 digits)		
200 Ω	0.1 9		> 200 mA						
2000 Ω	1 Ω								
Insulation Resistan									
Model	Test Voltage		Insulation stance Range	Re	solution	Test	Curre	ent	Accuracy
1653	50 V	10	$k\Omega$ to 50 $M\Omega$	С	0.01 MΩ 1 mA @ 50 l		kΩ	± (3%+ 3 digits)	
1653	100 V) kΩ to 20 MΩ MΩ to 100 MΩ		0.01 MΩ 1 mA @ 100 0.1 MΩ		kΩ	± (3%+ 3 digits) ± (3%+ 3 digits)	
1653, 1652	250 V		0 kΩ to 20 MΩ MΩ to 200 MΩ		0.01 MΩ 0.1 MΩ			kΩ	± (1.5%+ 3 digits)
1653, 1652, 1651	500 V	20	$20 \text{ M}\Omega$ to $200 \text{ M}\Omega$ 0.		0.01 MΩ 0.1 MΩ 1 MΩ	1 mA @ 500 kΩ		kΩ	± (1.5%+ 3 digits) + 10%
1653, 1652, 1651	1000 V		100 kΩ to 200 MΩ		A @ 1 N	ľΩ	± (1.5%+ 3 digits) + 10%		
Loop Impedance M	easurement								
Range			Resol	ution					Accuracy
20 Ω			0.01 Ω						
200 Ω			0.1 Ω			± (3% + 10 digits)			
2000 Ω			1	1 Ω					
PFC. PSC Test									
Range 0 to 50 kA									
Resolution and Units		$I_{\rm K}$ < 1000 A						1 A	
		$I_{K} \ge 1000 \text{ A}$ 0.1 kA							
Accuracy Determined by accuracy of loop resistance and mains voltage measurements									
RCD Testing									
	CD Type			1651		1	652		1653
¹AC	² G			•			•		•
AC		3S		•			•		•
4A		G S					•		•
¹ AC – responds to AC ² G – General, no delay ³ S – Time delay ⁴ A – Responds to pulsed signal									
Tripping Time Test (AT)									

Tripping Time Test (\(\Delta T \)					
Current Settings	Multiplier	Test Current Accuracy	Trip Time Accuracy		
10, 30, 100, 300, 500, 1000 mA	X 1/2	± 0% - 10%	± (1% Reading + 1 digit)		
10, 30, 100, 300, 500, 1000 mA	x 1	± 10% - 0%	± (1% Reading + 1 digit)		
10. 30 mA	x 5	± 10%	± (1% Reading + 1 digit)		

Tripping Current (Ramp) Test – Fluke 1653 and 1652 only					
Current Range	Step size	Dwe	ll time	Trip Current	
		Type G	Type S	Measurement Accuracy	
50% to 110% of	10% of I A N	300 ms/step	500 ms/step	± 5%	
RCD's rated current					

Earth Resistance Test (R_E) – Fluke	nce Test (R _E) — Fluke 1653 only				
Range	Resolution	Accuracy			
200 Ω	0.1 Ω	± (2%+ 5 digits)			
2000 Ω	1 Ω	± (3.5%+ 10 digits)			

Battery type: Alkaline supplied. usable with 1.2 V NiCD or NiMH rechargeable batteries **Size (HxWxD):** 100 mm x 250 mm x 125 mm

Weight: 1.17 kg Three Years Warranty