

Product data sheet

Specifications



Harmony XVB, Fixing base for modular tower lights, plastic, Ø70, 80mm aluminium support tube + black fixing plate

XVBZ02A

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XVB
Accessory / separate part designation	Fixing base
Accessory / separate part category	Mounting and fixing accessories
Accessory / separate part destination	Beacons and indicator banks Ø 70 mm

Complementary

Accessory / Separate Part Type	Fixing base
Product Compatibility	XVBL. XVBC.
Kit composition	Ø 25 mm aluminium support tube Black plastic fixing plate
Height under base unit	3.15 in (80 mm)
Color	Aluminum
Net Weight	0.24 lb(US) (0.11 kg)

Ordering and shipping details

Category	22616-XVE OPTIMUM STACKLIGHTS
Discount Schedule	XV
GTIN	3389110673524
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7.000 cm)
Package 1 Width	2.76 in (7.000 cm)

Package 1 Length	5.12 in (13.000 cm)
Package 1 Weight	3.03 oz (86.000 g)
Unit Type of Package 2	S04
Number of Units in Package 2	100
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	20.61 lb(US) (9.347 kg)


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty


Warranty	18 months
----------	-----------

Dimensions and Mounting



Height under base unit	
b in mm	b in in.
80	3.15

Panel Cut-Out



Recommended replacement(s)