

Product data sheet

Specifications



Isolating switch, Harmony XAC, single block XEN T, for control circuit

XENT1192

Product availability : Stock - Normally stocked in distribution facility

Main

| | |
|-------------------------------|----------------------------|
| Range of Product | Harmony XAC |
| Product or Component Type | Isolating switch |
| Component name | XENT |
| Electrical circuit type | Control circuit |
| Contact block application | Emergency stop push-button |
| Contact block type | Single |
| Product Compatibility | XACA |
| Contacts type and composition | 3 NC |
| Mounting of block | Front mounting |
| Contact operation | Slow-break |

Complementary

| | |
|--|---|
| Connections - terminals | Screw clamp terminals, 1 x 0.5...1 x 2.5 mm ² without cable end Screw clamp terminals, 1 x 0.5...2 x 1.5 mm ² with cable end |
| Mechanical durability | 1000000 cycles |
| Contact code designation | A600 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A IEC 60947-5-1 appendix A |
| [Ithe] conventional enclosed thermal current | 10 A |
| [Ui] rated insulation voltage | 400 V 3)IEC 60947-1 |
| [Uimp] rated impulse withstand voltage | 6 kV IEC 60947-1 |
| Maximum resistance across terminals | 25 MOhm |
| Operating force | 14 N |
| Short-circuit protection | 10 A fuse protection cartridge gG |
| Rated operational power in W | 40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C |
| Net Weight | 0.11 lb(US) (0.05 kg) |

Environment

| | |
|---------------------------------------|--|
| Standards | CSA C22.2 No 14 UL 508 EN/IEC 60947-5-1 EN/IEC 60204-32 |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C) |
| Ambient Air Temperature for Storage | -40...158 °F (-40...70 °C) |
| Vibration resistance | 15 gn 10...500 Hz)IEC 60068-2-6 |
| Shock resistance | 100 gn IEC 60068-2-27 |
| Electrical shock protection class | Class II IEC 61140 |

Ordering and shipping details

| | |
|-------------------|-------------------------------|
| Category | 22466-PUSHBUTTON, ACCESSORIES |
| Discount Schedule | CS2 |
| GTIN | 3389110426915 |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.42 in (3.6 cm) |
| Package 1 Width | 1.85 in (4.7 cm) |
| Package 1 Length | 3.98 in (10.1 cm) |
| Package 1 Weight | 2.36 oz (67.0 g) |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 45 |
| Package 2 Height | 5.91 in (15.0 cm) |
| Package 2 Width | 5.91 in (15.0 cm) |
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 7.03 lb(US) (3.189 kg) |

Offer Sustainability

| | |
|----------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration |
| RoHS exemption information | Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

Warranty18 months

Recommended replacement(s)