

Maximum rating 200 A, high-stability, high-accuracy, wideband DC to 10 MHz, high-CMRR, high-performance fluxgate technology, pass-through type







Features

- 2 ppm linearity
- \checkmark 5 ppm offset
- \checkmark Voltage output
- ✓ CT coil structure for broadband and superior frequency characteristics
- Built-in plated shield for excellent noise \checkmark resistance (high CMRR)
- Aperture ϕ 24mm for cables and bus-bars
- \checkmark The Power Analyzer PW8001 automatically recognizes the current sensor's information (phase shift data, sensor model name, rated current, serial number) when connected.

Applications

- Automotive (e.g. xEV R&D and manufacturing)
- Renewable energy (power conditioner R&D and \checkmark manufacturing)
- √ Efficiency measurement of high-efficiency energy converters
- ✓ Analysis of industrial inverter motors
- ✓ **Calibration of shunt resistors**
- \checkmark Measurement of minute superimposed current in battery systems
- Industrial drones
- For feedback control in medical devices (MRI, CT, X-ray)

Specification highlights	Symbol	Unit	Min.	Тур.	Max.
Nominal primary DC current	I _{PN} DC	А	-200		200
Nominal primary AC current	I _{PN} AC	Arms			200
Measurement range	I _{PM}	А	-220		220
Nominal output voltage	V _{out}	V	-2		2
Primary/secondary ratio	Ratio	V/A	0.01	0.01	0.01
Linearity error	٤L	ppm		±2	
Offset error	٤٥	ppm		±5	
DC amplitude error	٤ _G	ppm		±7	
Bandwidth (±3dB)	f	MHz		10	
Withstand voltage (1 mA, 50/60 Hz for 1 minute)	Ud	kV			7.4
Power supply voltage	Uc	V	±11.5		±15
Operating temperature range	T _A	°C	-40		85
Output cable length	L _{cable}	m		CT6873: 3m CT6873-01: 10m	



Electrical specifications at T_A = 23°C ±5°C, supply voltage (by using external PSU) = ±12 V unless otherwise stated

Electrical specifications at TA	- 25 C ±5	c, supply voltage	(by doing	5 CALCING	11 307 -	112 V unicos otherwise stated
Parameter	Symbol	Unit	Min.	Тур.	Max.	Comment
Nominal primary DC current	IPN DC	А	-200		200	Refer to "Figure 1. Frequency derating"
Nominal primary AC current	IPN AC	Arms			200	Refer to "Figure 1. Frequency derating"
Measurement range	IPM	А	-220		220	Refer to "Figure 1. Frequency derating"
Maximum input current	I _{MAX}	Apeak	-420		420	Not exceeding derating curve shown in Figure 1 However, it is allowable for up to 20 ms at 40°C or less
Nominal output voltage	Vout	V	-2		2	
Primary/secondary ratio	Ratio	V/A	0.01	0.01	0.01	
Bandwidth (-3dB)	f	MHz		10		Refer to "Figure 2. Frequency characteristics"
Output resistance		Ω	40	50	60	
Linearity error	٤∟	ppm		±2		Refer to "Figure 3. Linearity error characteristics"
Offset error	εο	ppm		±5		
DC amplitude error	ε _g	ppm		±7		
AC amplitude error 10 Hz - 500 Hz 500 Hz - 3 kHz 3 kHz - 30 kHz 30 kHz - 100 kHz 100 kHz - 400 kHz 400 kHz - 1 MHz	٤ _G	%		± 0.005 ± 0.01 ± 0.1 ± 0.4 ± 1 ± 3		
Output noise	noise	μVrms			300	Measurement bandwidth: DC to 1 MHz
Effects of temperature Amplitude sensitivity Offset voltage		ppm of reading/°C ppm of full scale/°C	-15 -0.1		15 0.1	Within the range of -40°C to 18°C or 28°C to 85°C
Effects of magnetization		mA			1	Input equivalent, after 200 A DC is inputted
Common mode rejection ratio DC to 1 kHz 1 kHz to 10 kHz 10 kHz to 100 kHz 100 kHz to 1 MHz	CMRR	dB	150 140 120 100			(Effect on output voltage/common-mode voltage) Refer to "Figure 4. CMRR characteristics"
Effects of conductor position DC 50/60 Hz 1 kHz 10 kHz 100 kHz		% of reading	-0.004 -0.005 -0.04 -0.04 -1.2		0.004 0.005 0.04 0.04 1.2	When wire of outer diameter 10 mm is used
Effects of external magnetic field		mA			2	Input equivalent, under a magnetic field of 400 A/m, DC
					25	Input equivalent, under a magnetic field of 400 A/m, 60 Hz
Effects of radiated radio-frequency electromagnetic field		% of full scale			0.5	10 V/m
Effects of conducted radio- frequency electromagnetic field		% of full scale			0.1	10 V
Fluxgate excitation frequency	f _{Exc}	kHz		10.4		
Power supply voltages	Uc	V	±11.5		±15	
Positive current consumption	Ips	mA			250	DC + 400 A with ±12V
Negative current consumption	Ins	mA			-250	DC - 400 A with ±12V

Isolation specifications

Parameter	Unit	Value	Comment
Rated insulation RMS voltage, basic insulation	V	1000	IEC 61010-1 conditions
Rated insulation RMS voltage, reinforced insulation	V	1000	• over voltage CAT III • pollution degree 2
RMS voltage for AC isolation test, 50/60 Hz, 1 minute	kV	7.4	Between primary and secondary (and shield) Sensed current: 1 mA
Clearance	mm	23.4	Shortest distance through air
Creepage distance	mm	23.4	Shortest path along device body
Comparative tracking index (CTI)	V	< 250	Performance level category (PLC) = 3
Standards	Safety: EN 61010 EMC: EN 61326		

All information correct as of December 24, 2021.
Company names and product names appearing in this catalog are trademarks or registered trademarks of various companies.
All specifications are subject to change without notice.



Environmental and mechanical characteristics

Parameter	Symbol	Unit	Min.	Тур.	Max.	Comment	
Operating environment (altitude)		m			2000	Indoor use, pollution degree 2	
Ambient operating temperature range	TA	°C	-40		85		
Ambient storage temperature range	T _{Ast}	°C	-40		85		
Relative humidity	RH	%			80	Non-condensing	
Protection against mechanical impacts			IK07			Energy level: 2 J, test height defined in EN 61010 Safety requirements: 400 mm	
Measurable conductor diameter	Dmeas	mm			24		
Dimensions	W H D	mm		70 100 53		Refer to "Figure 5. Dimensions"	
Output cable length CT6873 CT6873-01	L _{cable}	m		3 10			
Mounting hole diameter	D _{mout}	mm		φ 4.8		M4 screw, recommended tightening torque: 1.2 Nm to 1.5 Nm	
Weight CT6873 CT6873-01	m	g		370 690			

Measurement accuracy (total accuracy including uncertainty in calibration system etc.)

Electrical specifications at $T_A = 23^{\circ}C \pm 5^{\circ}C$, supply voltage (by using external PSU) = ± 12 V unless otherwise stated

Frequency	Amp	Phase	
[Hz]	[±% of reading]	[±% of full scale]	[±°]
DC	0.03	0.002	_
DC < f < 16	0.1	0.01	0.1
16 ≤ f < 45	0.05	0.01	0.08
45 ≤ f ≤ 66	0.03	0.007	0.05
66 < f ≤ 100	0.04	0.01	0.1
100 < f ≤ 500	0.05	0.01	0.15
500 < f ≤ 3 k	0.1	0.01	0.4
3 k < f ≤ 5 k	0.2	0.02	0.4
5 k < f ≤ 10 k	0.2	0.02	0.5
$10 \text{ k} < f \le 1 \text{ M}$	0.018 x f	0.05	0.04 x f + 0.1
Frequency range	10 MHz (±	_	

• The variable f in accuracy equations is expressed in kHz.

• Accuracy of amplitude and phase is specified with 110% of full scale input or less and not exceeding derating curve in Figure 1. Accuracy in range of DC < f < 10 Hz are design values.

• Add ±0.01% of reading to amplitude accuracy when input is 100% to 110% of full scale.

• For the CT6873-01, add the following values to accuracy in the range of 1 kHz < f \leq 1 MHz. Amplitude accuracy: ±(0.005 × f [kHz])% of reading


Phase accuracy: ±(0.015 × f [kHz])°

Definition of on accuracy (total accuracy including uncertainty in calibration system etc.)

Reading (displayed value) error: Indicates the value displayed by the instrument. Limit values for reading errors are expressed as a percentage of the reading ("% of reading" or "% rdg.").

Range error: Indicates the instrument's range. Limit values for range errors are expressed as a percentage of the range ("% of range").

Full scale (rated current) error: Indicates the rated current. Limit values for full-scale errors are expressed as a percentage of full scale ("% of full scale" or "% f.s."). Calibration: The accuracy of HIOKI products includes all factors that affect the measurement results, such as calibration system errors, ambient temperature, and secular change, as "uncertainty".



HIOKI is accredited as an official ISO/IEC 17025 calibrator.

All information correct as of December 24, 2021

Company names and product names appearing in this catalog are trademarks or registered trademarks of various companies
All specifications are subject to change without notice.



Specific accuracy calculation example

How to measure the current of DC 100 A of a conductor with a diameter of ϕ 20 mm or less with high accuracy. Guaranteed specifications at $T_A = 23^{\circ}C \pm 5^{\circ}C$

Measuring instrument configuration	СТ6873, СТ6873-01	CT9555	L9217 + 9704	DM7276			
External view			*				
Range (connection)	200 A (2000 mV)	Front OUTPUT terminal (BNC terminal)	\checkmark	1000 mV			
Output voltage	100 A × 2000 mV / 200 A = 1000 mV –						
Error (reading)	0.03%	_	_	0.0011%			
Error (full scale)	0.002%	_	_	3 μV			
Total error	$1000 \text{ mV} \times (0.03 + 0.0011)\% + 2000 \text{ mV} \times 0.002\% + (3 \ \mu\text{V} \times 10^{-3}) \text{ mV} = 0.354 \text{ mV}$						
Total error (input equivalent)	0.354 mV / 2000 mV × 200A = 0.0354 A						
Error range	100 A ± 0.0354 A ⇔ 99.9646 A to 100.0354 A						


Definition of linearity error

Linearity error ϵ_L : Indicates that the output (current or voltage) changes linearly in response to the input current.

A regression line is attained by measuring the output voltage in the sequence below in 40 A intervals:

+200 A $\rightarrow\,$ 0 A $\rightarrow\,$ -200 A $\rightarrow\,$ 0 A $\rightarrow\,$ +200 A

It is defined as the difference between the regression line calculated from the above measurements and the measurement points.



Definition of offset error

Offset error ε_0 : Specified by the ratio of the average value (μ) of the measured values of the offset voltage and the rated current (Imax) of each current sensor.

$$\varepsilon_0 = \mu / \text{Imax} \text{ [ppm]}$$

Definition of amplitude error

Amplitude error ε_{G} : An index showing the degree of flatness of the frequency characteristics of gain. DC error is defined as "linearity error + offset error."

AC error is defined as deviation from the 55 Hz measurement point.


$$\varepsilon_{\text{G DC}} = \varepsilon_{\text{L}} + \varepsilon_{0}$$
 [ppm]

$$\varepsilon_{GAC} = \frac{Gain (f) - Gain (55 Hz)}{Gain (55 Hz)} \times 100$$
 [%]




CT6873, CT6873-01 AC/DC CURRENT SENSOR

Figure 1. Frequency derating










Enter the following values (representative values) when performing phase compensation on the PW6001 or PW3390. When connecting to the PW8001, it will be set automatically.

CT6873: 100 kHz, -0.75° CT6873-01: 100 kHz, -2.10°









Figure 5. Dimensions


Top view





CT6873, CT6873-01 **AC/DC CURRENT SENSOR**

Figure 6. Pin assignment (when not using the sensor units CT9555, CT9556, or CT9557)



All information correct as of December 24, 2021.

Company names and product names appearing in this catalog are trademarks or registered trademarks of various companies.
All specifications are subject to change without notice.



Links

- 1. Web site AC/DC CURRENT SENSOR CT6873 | HIOKI
- 2. Accuracy calculation tools <u>POWER ANALYZER PW8001 & CT</u> <u>POWER ANALYZER PW6001 & CT</u> <u>POWER ANALYZER PW3390 & CT</u>

Files and information such as the Power Analyzer accuracy calculation tools are updated regularly. Instead of downloading them once and using them for a long time, download them from the download link just before using them.