




CAP OPTIONS	TOGGLE SWITCHES	TACTILE SWITCHES	SNAP ACTION SWITCHES	SLIDE SWITCHES	ROTARY SWITCHES	ROCKER SWITCHES	PUSHBUTTON SWITCHES	NAVIGATION SWITCHES	KEYLOCK SWITCHES	DIP SWITCHES	DETECTOR SWITCHES	ANTI-VANDAL SWITCHES
----------------	--------------------	---------------------	-------------------------	-------------------	--------------------	--------------------	------------------------	------------------------	---------------------	-----------------	----------------------	-------------------------



RoHS

FEATURES & BENEFITS

- Up to 100,000 cycle life expectancy
- Tape and Reel packaging
- Surface mount design
- Actuator options
- Actuation force options
- Termination options

PART NUMBER CONFIGURATOR

Termination

9

G - Gull Wing
J - J-bend

Specifications subject to change without notice 10.20.2022






E♦SWITCH®

800.867.2717



1

TL3304 SERIES TACT SWITCH

BODY DIMENSIONS



ACTUATOR	"L"
N	2.60
A	3.40






ALL TERMINALS MUST BE CO-PLANAR
WITHIN 0.10 [.004] TOTAL





TL3304 SERIES TACT SWITCH

BODY DIMENSIONS TAPE AND REEL



ACTUATOR	"L"
N	2.60
A	3.40



ALL TERMINALS MUST BE CO-PLANAR
W/IN 0.10 [.004] TOTAL



E-SWITCH®



www.e-switch.com

800.867.2717

3

TL3304 SERIES TACT SWITCH

BODY DIMENSIONS TAPE AND REEL



E-SWITCH®

www.e-switch.com



800.867.2717

4

ANTI-VANDAL
DETECTOR
DIP
KEYLOCK
NAVIGATION
PUSHBUTTON
ROCKER
ROTARY
SLIDE
SNAP ACTION
TACTILE
TOGGLE
CAP
OPTIONS

TL3304 SERIES TACT SWITCH

BODY DIMENSIONS TAPE AND REEL



E-SWITCH®



www.e-switch.com

800.867.2717

5

TL3304 SERIES TACT SWITCH

BODY DIMENSIONS TAPE AND REEL



E-SWITCH®

www.e-switch.com

800.867.2717

6

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

RECOMMENDED SOLDER PROCESS

Most contamination problems can be prevented by exercising care during the cleaning and soldering process. Care should be taken not to immerse or spray unsealed switches during flux removal. Contact E-Switch for specific soldering recommendations and specifications not shown. Generalized soldering procedures are outlined below.

“TYPICAL” SMT REFLOW (Pb and Pb-Free)

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Average Ramp-Up Rate ($T_{s_{max}}$ to T_p)	3 °C/second max.	3 °C/second max.
Preheat		
-Temperature Min ($T_{s_{min}}$)	100 °C	150 °C
-Temperature Max ($T_{s_{max}}$)	150 °C	200 °C
-Time ($t_{s_{min}}$ to $t_{s_{max}}$)	60-120 seconds	60-180 seconds
Time Maintained above:		
-Temperature (T_L)	183 °C	217 °C
-Time (t_L)	60-150 seconds	60-150 seconds
Time within 5 °C of actual Peak Temperature (t_p)	10-30 seconds	20-40 seconds
Ramp-Down Rate	6 °C/second max.	6 °C/second max.
Time 25 °C to Peak Temperature	6 minutes max.	8 minutes max.

Note 1: All temperatures refer to topside of the package, measured on the package surface.

