3-1447221-3 - ACTIVE

#### AMP | SUPERSEAL 1.0mm

TE Internal #: 3-1447221-3 Automotive Terminals, Socket, Pin Diameter 1 mm [.039 in], 18 – 16 AWG Wire Size, .75 – 1.25 mm<sup>2</sup> Wire Size, Sealable, Family Seal, SUPERSEAL 1.0mm

#### View on TE.com >

Terminals & Splices > Automotive Terminals > SUPERSEAL Connector Contacts: 1.0 mm



Terminal Type: Socket Mating Pin Diameter: 1 mm [.039 in ] Terminal Transmits: 0 – 24 A (Low Power) Wire Size: .75 – 1.25 mm<sup>2</sup>

All SUPERSEAL Connector Contacts: 1.0 mm (6)



#### Features

#### **Product Type Features**

Receptacle Style	180°
Sealable	Yes
Primary Locking Feature	Clean Body
Body Features	
Terminal Seal Type	Family Seal
Contact Features	
Contact Size	1mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	15 A
Crimp Type	F-Crimp
Terminal Type	Socket
Mating Pin Diameter	1 mm[.039 in]

Automotive Terminals, Socket, Pin Diameter 1 mm [.039 in], 18 – 16 AWG Wire Size, . 75 – 1.25 mm² Wire Size, Sealable, Family Seal, SUPERSEAL 1.0mm



Interface Plating	Gold (Au)
Termination Features	
Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire
Dimensions	
Compatible Insulation Diameter Range	1.6 – 2.2 mm[.063 – .087 in]
Wire Size	.75 – 1.25 mm²
Wire Size Search	16 AWG, 17 AWG, 18 AWG
Usage Conditions	
Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C[176 °F][185 °F][194 ° F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-30 – 130 °C[-22 – 266 °F]
Operation/Application	
Compatible With Wire Base Material	Copper
Packaging Features	
Packaging Quantity	7000
Packaging Method	Reel
Other	
Terminal Transmits	0 – 24 A (Low Power)
Product Compliance For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC

Automotive Terminals, Socket, Pin Diameter 1 mm [.039 in], 18 – 16 AWG Wire Size, . 75 – 1.25 mm<sup>2</sup> Wire Size, Sealable, Family Seal, SUPERSEAL 1.0mm



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# **Compatible Parts**



TE Part # CAT-SU763-CH8172 SUPERSEAL Connector Housings: 1.0 mm



TE Part # 1454509-1 SAHT SUPER SEAL 19-16 ASSY



TE Part # 1976144-1 SDE COMMERCIAL HAND TOOL




TE Part # 1376886-1 3900281-442=S/S PLUG ASSY 44P



Also in the Series | SUPERSEAL 1.0mm

Automotive Terminals, Socket, Pin Diameter 1 mm [.039 in], 18 – 16 AWG Wire Size, . 75 – 1.25 mm² Wire Size, Sealable, Family Seal, SUPERSEAL 1.0mm





# Customers Also Bought



INSULATION CRIMPER       RECEPT ASSY.2 HOLE. TYPE 2. AS       REC CONN         DOUBLE DE       LOW BRKT	N CVR,39POS,AMP MCP 2.8, HSD CABLE ASSEMBLY
TE Part #2424195-3TE Part #2424195-5HSD CABLE ASSEMBLYHSD CABLE ASSEMBLY	

# Documents

Product Drawings S/S REC CONTACT ASSY, AU, 0.75~1.25

English

**CAD** Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-1447221-3\_C.2d\_dxf.zip

Automotive Terminals, Socket, Pin Diameter 1 mm [.039 in], 18 – 16 AWG Wire Size, . 75 – 1.25 mm<sup>2</sup> Wire Size, Sealable, Family Seal, SUPERSEAL 1.0mm



English

Customer View Model ENG\_CVM\_CVM\_3-1447221-3\_C.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_3-1447221-3\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

**Product Specifications** 

**Application Specification** 

English

Receptacle Contact, Super Seal Connector

Japanese

**Application Specification** 

Japanese

Super Seal Connector

Japanese

#### Application Specification

Japanese

**Application Specification** 

Japanese

**Application Specification** 

English

# Instruction Sheets SUPER SEAL CONNECTOR RECEPTACLE CONTACT HAND CRIMPING TOOL

Japanese

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

English

SUPER SEAL CONNECTOR PLUG HOUSING CONNECTOR

English